



USB

# Solid State SP2T Switch

## USB-1SP2T-183

50Ω 0.1 to 18 GHz

### THE BIG DEAL

- Super wide bandwidth, solid-state design
- High isolation, 60 dB @ 18 GHz
- USB control and automation
- Daisy-chain control of up to 25 switches

### APPLICATIONS

- RF signal routing / switch matrices
- Satellite communications up to Ku band
- Military radio, radar & electronic warfare
- Microwave radio / cellular infrastructure
- Test & measurement systems



Generic photo used for illustration purposes only

Model No.	USB-1SP2T-183
Case Style	NR3244
Connectors	2.92 mm (female) (Compatible with SMA and 3.5 mm)

DOWNLOAD

SOFTWARE PACKAGE

Refer to our website for compliance methodologies and qualifications



### PRODUCT OVERVIEW

Mini-Circuits' USB-1SP2T-183 is a fast switching solid-state SP2T covering an ultra-wide bandwidth, from 0.1 to 18 GHz. The solid-state design features an impressive combination of high isolation, low insertion loss and good linearity across the entire band. The switch is supplied in a low profile package with precision 2.92 mm RF connectors.

The daisy-chain control interface with "dynamic addressing" simplifies control integration, allowing multiple switches to be combined into a Master / Slave chain. Simply connect, then power on and the whole chain of up to 25 compatible switches can be controlled independently through a single USB and software interface.

Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

### KEY FEATURES

Feature	Advantages
Fast switching sequences	Program automated switching sequences to run with extremely fast transitions and no external control.
High performance	Solid-state design combining high isolation with low insertion loss from 0.1 to 18 GHz.
Dynamic daisy-chain control	Control up to 25 switches through a single USB interface.
USB control	USB HID interface provides easy compatibility with a wide range of software setups and programming environments.
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments.

#### Trademarks:

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.



**USB**

# Solid State SP2T Switch

**USB-1SP2T-183**

Mini-Circuits

**ELECTRICAL SPECIFICATIONS AT 0 TO 50°C**

Parameter	Ports	Condition (GHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	-	0.1		18	GHz
Insertion Loss	COM to any active port	0.1 - 6	-	1.50	2.80	dB
		6 - 10	-	2.00	3.20	
		10 - 15	-	2.35	3.80	
		15 - 18	-	2.80	4.00	
Isolation	Between ports J1 & J2	0.1 - 6	50	70	-	dB
		6 - 10	50	70	-	
		10 - 15	50	65	-	
		15 - 18	50	65	-	
	COM to any terminated port (including disconnected state)	0.1 - 6	50	65	-	
		6 - 10	50	65	-	
		10 - 15	50	60	-	
		15 - 18	50	60	-	
Return Loss	COM port (in all active states)	0.1 - 6	-	19	-	dB
		6 - 10	-	19	-	
		10 - 15	-	17.5	-	
		15 - 18	-	15.5	-	
	Any port connected to COM	0.1 - 6	-	21	-	
		6 - 10	-	21	-	
		10 - 15	-	15.5	-	
		15 - 18	-	15.5	-	
	Any terminated port	0.1 - 6	-	23	-	
		6 - 10	-	21	-	
		10 - 15	-	19	-	
		15 - 18	-	17.5	-	
Power Input @1 dB Compression <sup>1</sup>	COM to any active port	0.1 - 18	-	27	-	dBm
IP3 <sup>2,3</sup>	COM to any active port	0.5 - 18	-	50	-	dBm
Transition Time <sup>4</sup>	-	-	-	5	20	ns
Minimum Dwell Time <sup>5</sup>	High speed mode	-	-	10	-	µs
Switching Time (USB) <sup>6</sup>	-	-	-	2	-	ms
Supply Voltage (Vcc)	USB port	-	4.75	5	5.25	V <sub>DC</sub>
Supply Current (Icc) <sup>7</sup>		-	-	80	120	mA
Current Pass-through <sup>8</sup>	-	-	-	-	500	mA
Operating RF Input Power <sup>1</sup>	Between COM & active port	Hot switching	-	-	+18	dBm
	Between COM & active port	Cold switching	-	-	+24	
	Into any termination	-	-	-	+24	

1. Max power at hot switching derates linearly from +18 dBm @ 600 MHz to +17 dBm @100 MHz, at all other conditions it derates linearly from +24 dBm @ 600 MHz to +17 dBm @100 MHz.

2. IP3 may degrade below 500 MHz to about +45 dBm.

3. IP3 tested with 1 MHz span between signals, +8 dBm per tone.

4. Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

5. Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

6. Switching time (USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

7. USB current draw for a single unit with no slave units.

8. Pass through current is the maximum supply current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. See page 5 for details.





USB

# Solid State SP2T Switch

## USB-1SP2T-183

### ABSOLUTE MAXIMUM RATINGS

Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 60°C
DC supply voltage max.	6V
DC voltage @ RF Ports	20 V


Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

### CONNECTIONS

Port Name	Connector Type
RF Ports (COM, 1 & 2)	2.92 mm female
USB	USB type-C receptacle
Serial In (Digital Control 2 port)	Digital Snap Fit Connector <sup>9</sup>
Serial Out (Digital Control 1 port)	Digital Snap Fit Connector <sup>9</sup>

9. Mating connector is Hirose ST40X-10S-CV(30).

### BLOCK DIAGRAM






USB

# Solid State SP2T Switch

## USB-1SP2T-183

### OUTLINE DRAWING (NR3244)



### OUTLINE DIMENSIONS ( INCH / mm )


A	B	C	D	E	F	G	H	J	K	weight
2.30	2.00	0.575	0.10	2.25	2.50	2.05	0.106	0.50	0.65	grams
58.42	50.80	14.610	2.54	57.15	63.50	52.07	2.690	12.70	16.51	100





### CONNECTING MULTIPLE MODULES (DAISY CHAIN)

The USB-1SP2T-183 model is designed to connect up to 25 modules in series (daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 24 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC act as a master and all other as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module.

Power will be supplied from the PC via the master module up to a maximum of 500 mA. Generally, additional power supply will be needed to keep total current below 500 mA. All power supplies should be connected to the module via the module's USB port. Connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

**Note:** Different module types may have different current consumption which will change the number of units which can be connected before an additional power supply is needed.




USB

# Solid State SP2T Switch


USB-1SP2T-183

## TYPICAL PERFORMANCE CURVES


Insertion Loss over Temperature (J1 Active)




Insertion Loss J1 - J2 Active




Isolation Com to J1 (J2 Active)



Isolation Com to J2 (J1 Active)



Isolation J1 to J2 (J1 Active)






USB

# Solid State SP2T Switch


USB-1SP2T-183

## TYPICAL PERFORMANCE CURVES (CONTINUED)


Return Loss @ COM over Temperature (J1 Active)




Return Loss @ J1 over Temperature (J1 Active)




Return Loss @ J1 over Temperature (J1 Terminated)



Return Loss @ J2 over Temperature (J2 Active)



Return Loss @ J2 over Temperature (J2 Terminated)





### SOFTWARE SPECIFICATIONS

#### SOFTWARE & DOCUMENTATION DOWNLOAD:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from: <https://www.minicircuits.com/softwaredownload/solidstate.html>
- Please contact [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com) for support

#### MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID or Daisy Chain dynamic addressing	
System Requirements	GUI	Windows 7 or later
	USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 7 or later
	Daisy Chain dynamic addressing	An additional Mini-Circuits model supporting dynamic addressing
Hardware	Intel i3 (or equivalent) or later	

#### APPLICATION PROGRAMMING INTERFACE (API)

##### USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments

##### USB SUPPORT (LINUX):


- Direct USB programming using a series of USB interrupt codes
- Full programming instructions and examples available for a wide range of programming environments / languages.






### GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB
- Run GUI in "demo mode" to evaluate software without a hardware connection



- View and set switch states at the click of a button
- Control up to 25 units from a single USB control
- Configure and run timed switching sequences





USB

# Solid State SP2T Switch


## USB-1SP2T-183

Mini-Circuits

### ORDERING INFORMATION

Please contact Mini-Circuits' Test Solutions department for price and availability: [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com)

Model	Description
USB-1SP2T-183	USB RF SP2T switch

Included Accessories	Part No.	Description
	USB-CBL-AC-3+	3.3 ft (1.0 m) USB cable: USB type A (Male) to USB type C (Male)

### OPTIONAL ACCESSORIES

USB-CBL-AC-3+	3.3 ft (1.0 m) USB Cable: USB type A (Male) to USB type C (Male)
CBL-1.5FT-MMD+	1.5 ft (0.45 m) cable assembly for serial control Daisy Chain with snap fit connectors
USB-AC/DC-5	AC/DC +5V power adaptor with USB connector <sup>10, 11</sup>

10. The power adaptor may be used to provide additional power via USB port when connecting several units in daisy chain.

11. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed please contact [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com)

### NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
50	0.73	0.73	1.15	1.15	1.15	1.11	1.11
250	0.83	0.83	1.09	1.09	1.10	1.09	1.09
500	0.91	0.92	1.09	1.09	1.10	1.10	1.10
750	0.99	0.99	1.08	1.08	1.10	1.12	1.12
1000	1.06	1.07	1.07	1.07	1.09	1.12	1.12
1250	1.09	1.10	1.07	1.07	1.06	1.13	1.13
1500	1.12	1.13	1.08	1.09	1.05	1.13	1.13
1750	1.17	1.18	1.10	1.12	1.06	1.13	1.13
2000	1.20	1.22	1.12	1.14	1.06	1.11	1.11
2250	1.23	1.24	1.15	1.17	1.08	1.10	1.10
2500	1.26	1.28	1.15	1.17	1.08	1.09	1.08
2750	1.29	1.31	1.17	1.19	1.09	1.08	1.07
3000	1.32	1.34	1.17	1.18	1.08	1.07	1.05
3500	1.37	1.38	1.18	1.19	1.08	1.04	1.02
4000	1.41	1.42	1.20	1.19	1.09	1.02	1.01
4500	1.45	1.46	1.18	1.16	1.08	1.03	1.04
5000	1.49	1.50	1.12	1.11	1.11	1.07	1.08
5500	1.54	1.56	1.10	1.13	1.20	1.11	1.11
6000	1.62	1.64	1.16	1.20	1.27	1.13	1.13
6500	1.67	1.69	1.19	1.22	1.28	1.13	1.13
7000	1.71	1.72	1.17	1.18	1.21	1.10	1.10
7500	1.74	1.75	1.12	1.11	1.15	1.07	1.06
8000	1.77	1.78	1.07	1.05	1.13	1.04	1.02
8500	1.81	1.82	1.05	1.01	1.15	1.05	1.03
9000	1.85	1.86	1.05	1.05	1.17	1.06	1.05
9500	1.90	1.91	1.06	1.07	1.20	1.07	1.06
10000	1.94	1.95	1.08	1.08	1.20	1.09	1.08
10500	1.97	1.98	1.07	1.08	1.18	1.12	1.10
11000	2.00	2.02	1.02	1.04	1.14	1.14	1.12
11500	2.04	2.05	1.05	1.05	1.12	1.15	1.12
12000	2.08	2.10	1.12	1.10	1.12	1.13	1.11
12500	2.13	2.14	1.16	1.15	1.13	1.11	1.10
13000	2.17	2.19	1.17	1.16	1.14	1.09	1.09
13500	2.23	2.25	1.18	1.19	1.20	1.10	1.11
14000	2.29	2.33	1.22	1.25	1.26	1.13	1.13
14500	2.36	2.40	1.26	1.30	1.30	1.13	1.13
15000	2.40	2.44	1.29	1.31	1.29	1.13	1.12
15500	2.44	2.47	1.29	1.29	1.24	1.13	1.12
16000	2.46	2.48	1.25	1.23	1.16	1.13	1.12
16500	2.47	2.49	1.20	1.19	1.04	1.13	1.14
17000	2.50	2.54	1.19	1.21	1.10	1.15	1.18
17250	2.52	2.56	1.19	1.22	1.15	1.16	1.19
17500	2.54	2.59	1.20	1.23	1.19	1.17	1.20
17750	2.56	2.60	1.20	1.22	1.20	1.17	1.20
18000	2.57	2.61	1.17	1.19	1.20	1.17	1.18
18250	2.59	2.62	1.15	1.16	1.20	1.16	1.16
18500	2.60	2.64	1.13	1.14	1.19	1.14	1.13
18750	2.62	2.66	1.11	1.12	1.18	1.11	1.10
19000	2.65	2.69	1.11	1.13	1.20	1.09	1.07
19250	2.69	2.74	1.16	1.19	1.24	1.06	1.06
19500	2.73	2.79	1.22	1.28	1.30	1.09	1.11
19750	2.79	2.87	1.29	1.37	1.39	1.13	1.17
20000	2.85	2.94	1.36	1.45	1.48	1.19	1.24

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
50	91.44	91.14	90.05	88.05	87.29	101.70
250	83.11	82.17	84.93	79.63	81.35	103.61
500	76.25	78.39	83.67	75.00	74.38	90.10
750	73.90	73.81	79.86	71.38	70.85	90.61
1000	71.50	71.26	75.41	68.34	68.38	85.05
1250	69.39	69.42	74.44	66.74	66.44	84.59
1500	68.41	67.87	72.88	65.34	65.13	84.96
1750	67.17	67.20	71.51	64.13	64.08	81.39
2000	66.15	66.15	70.61	63.52	63.28	80.07
2250	65.75	65.47	70.25	62.87	62.90	79.81
2500	65.03	64.90	69.50	62.44	62.27	77.84
2750	64.54	64.61	68.77	62.31	62.12	78.36
3000	64.47	64.08	68.34	61.85	61.65	77.33
3500	63.71	63.86	68.12	61.63	61.50	74.47
4000	63.68	63.70	67.94	61.71	61.57	74.04
4500	63.26	63.38	68.27	62.01	61.73	73.47
5000	63.00	63.24	67.85	62.44	62.12	73.54
5500	62.49	62.35	67.72	62.94	62.60	73.52
6000	62.28	62.20	67.06	63.10	62.89	74.32
6500	62.23	62.31	66.62	63.46	62.95	74.45
7000	62.61	62.40	66.69	64.15	63.27	75.13
7500	62.92	62.68	66.58	64.43	63.79	77.15
8000	63.37	63.26	67.34	64.79	64.09	78.82
8500	64.06	64.00	68.55	65.15	64.63	81.89
9000	64.50	64.89	69.18	65.20	65.11	87.03
9500	64.43	65.78	70.00	65.14	65.58	99.06
10000	64.34	66.17	71.20	64.89	65.86	94.92
10500	64.26	66.03	71.18	64.95	66.17	102.56
11000	64.54	66.41	71.26	64.73	66.74	90.60
11500	64.90	67.12	72.67	64.75	67.88	88.12
12000	65.60	67.90	73.05	65.13	68.44	90.25
12500	66.30	68.51	71.52	65.58	71.02	85.09
13000	67.82	70.31	71.57	67.00	73.90	87.70
13500	69.23	71.03	71.48	68.50	78.80	82.48
14000	70.69	71.86	70.66	71.36	82.51	81.91
14500	71.49	70.19	69.89	74.47	74.13	81.03
15000	70.06	68.98	69.41	79.53	69.69	80.57
15500	68.36	67.32	68.73	74.04	66.41	79.83
16000	66.26	65.55	68.55	69.52	64.10	77.00
16500	64.75	63.80	67.79	66.01	62.14	76.53
17000	63.20	62.12	67.43	63.69	60.61	75.75
17250	62.33	61.37	66.78	62.76	59.96	75.43
17500	61.88	60.72	66.40	61.69	59.27	75.52
17750	61.00	60.30	66.53	61.01	58.75	75.32
18000	60.48	59.75	66.55	60.10	58.07	74.88
18250	60.08	59.48	66.25	59.53	57.55	73.86
18500	59.72	59.08	66.47	58.81	57.09	73.96
18750	59.18	58.56	66.36	58.27	56.63	73.48
19000	58.86	58.11	66.33	57.66	56.30	71.85
19250	58.27	57.67	66.40	57.31	55.83	72.13
19500	57.97	57.26	67.12	56.94	55.45	71.70
19750	57.58	56.98	67.29	56.51	55.35	71.06
20000	57.30	56.75	68.07	56.13	55.00	70.09

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

REV. A

USB-1SP2T-183

220120

Page 2 of 6



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
50	0.76	0.77	1.15	1.15	1.15	1.10	1.10
250	0.87	0.88	1.10	1.10	1.11	1.08	1.08
500	0.97	0.97	1.10	1.10	1.11	1.09	1.09
750	1.05	1.05	1.09	1.09	1.10	1.11	1.11
1000	1.12	1.13	1.08	1.08	1.09	1.12	1.12
1250	1.15	1.16	1.07	1.08	1.07	1.13	1.13
1500	1.19	1.21	1.08	1.09	1.06	1.13	1.13
1750	1.24	1.26	1.11	1.12	1.06	1.13	1.12
2000	1.27	1.29	1.13	1.15	1.07	1.11	1.11
2250	1.31	1.33	1.15	1.17	1.07	1.10	1.10
2500	1.34	1.36	1.16	1.19	1.08	1.09	1.08
2750	1.37	1.40	1.17	1.20	1.08	1.07	1.06
3000	1.40	1.43	1.18	1.20	1.08	1.06	1.05
3500	1.45	1.48	1.19	1.20	1.08	1.04	1.02
4000	1.50	1.52	1.20	1.20	1.08	1.01	1.01
4500	1.54	1.56	1.17	1.16	1.07	1.03	1.04
5000	1.59	1.61	1.12	1.11	1.11	1.07	1.08
5500	1.65	1.68	1.10	1.13	1.21	1.11	1.12
6000	1.73	1.77	1.17	1.20	1.29	1.13	1.13
6500	1.79	1.83	1.20	1.23	1.29	1.13	1.13
7000	1.83	1.87	1.17	1.19	1.22	1.10	1.11
7500	1.87	1.89	1.11	1.12	1.15	1.06	1.07
8000	1.90	1.93	1.06	1.05	1.13	1.03	1.03
8500	1.94	1.97	1.03	1.02	1.15	1.03	1.03
9000	1.99	2.02	1.04	1.05	1.18	1.05	1.05
9500	2.04	2.07	1.06	1.07	1.20	1.06	1.06
10000	2.09	2.12	1.08	1.08	1.21	1.08	1.08
10500	2.12	2.16	1.07	1.07	1.18	1.12	1.10
11000	2.16	2.20	1.01	1.03	1.14	1.15	1.12
11500	2.20	2.24	1.07	1.07	1.12	1.15	1.12
12000	2.26	2.29	1.14	1.13	1.13	1.13	1.10
12500	2.31	2.34	1.18	1.16	1.13	1.10	1.08
13000	2.35	2.39	1.17	1.16	1.13	1.07	1.07
13500	2.42	2.46	1.18	1.18	1.18	1.08	1.09
14000	2.49	2.55	1.21	1.24	1.25	1.11	1.12
14500	2.56	2.63	1.25	1.28	1.28	1.12	1.12
15000	2.62	2.68	1.28	1.30	1.27	1.12	1.12
15500	2.66	2.71	1.29	1.29	1.23	1.14	1.13
16000	2.69	2.73	1.26	1.25	1.14	1.15	1.15
16500	2.72	2.77	1.22	1.22	1.03	1.16	1.17
17000	2.77	2.83	1.22	1.24	1.11	1.18	1.21
17250	2.79	2.86	1.22	1.25	1.16	1.18	1.21
17500	2.82	2.89	1.23	1.26	1.19	1.19	1.22
17750	2.84	2.91	1.22	1.25	1.21	1.19	1.21
18000	2.86	2.93	1.20	1.21	1.21	1.18	1.20
18250	2.88	2.94	1.16	1.18	1.20	1.16	1.17
18500	2.90	2.96	1.13	1.14	1.18	1.14	1.13
18750	2.93	3.00	1.11	1.12	1.18	1.10	1.09
19000	2.97	3.04	1.12	1.14	1.19	1.07	1.05
19250	3.03	3.11	1.18	1.21	1.24	1.06	1.06
19500	3.09	3.18	1.25	1.30	1.30	1.09	1.11
19750	3.16	3.27	1.31	1.38	1.38	1.14	1.17
20000	3.21	3.35	1.36	1.45	1.46	1.19	1.23

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
50	91.77	87.33	88.77	84.33	85.74	106.29
250	84.03	83.50	86.54	79.42	80.17	95.30
500	77.02	78.72	82.49	74.64	75.38	92.91
750	73.64	74.00	79.61	70.56	70.87	87.86
1000	71.06	71.21	75.24	67.96	68.17	84.28
1250	69.20	68.97	73.64	66.08	65.84	86.28
1500	67.58	67.23	72.22	64.63	64.31	82.30
1750	66.62	66.65	71.00	63.62	63.34	81.79
2000	65.89	65.86	69.85	62.73	62.93	80.84
2250	65.18	65.22	69.66	62.25	62.03	80.40
2500	64.87	64.74	68.74	61.65	61.60	80.10
2750	64.41	64.38	68.39	61.30	61.25	78.01
3000	63.75	63.69	67.70	61.17	60.84	76.83
3500	63.53	63.27	67.57	60.87	60.75	75.98
4000	63.21	63.22	67.65	60.97	60.69	74.01
4500	62.88	62.90	67.87	61.34	61.02	73.61
5000	62.48	62.53	67.72	61.57	61.18	73.73
5500	62.27	61.93	67.20	61.85	61.45	74.72
6000	61.82	61.97	66.46	62.41	61.61	74.86
6500	62.14	61.89	66.19	62.51	61.92	75.71
7000	62.28	62.22	66.56	63.03	62.28	76.46
7500	62.59	62.38	67.00	63.44	62.65	78.53
8000	62.83	62.94	67.33	63.94	63.12	82.86
8500	63.58	63.49	68.56	64.43	63.44	84.26
9000	63.87	64.30	69.18	64.51	64.10	87.22
9500	63.84	65.08	70.02	64.67	64.64	88.02
10000	63.84	65.42	70.82	64.70	65.01	89.43
10500	63.90	65.34	71.50	64.71	65.53	88.67
11000	64.26	66.02	72.35	64.68	66.05	86.63
11500	64.62	66.72	71.33	65.05	66.70	84.59
12000	65.45	67.43	72.17	65.34	67.84	85.26
12500	66.52	68.88	71.59	66.16	69.61	86.84
13000	68.04	70.15	70.54	67.20	72.23	83.39
13500	69.53	71.91	70.90	69.13	76.33	83.85
14000	71.56	73.00	70.53	72.12	85.15	82.28
14500	72.39	72.26	69.28	77.89	77.91	83.23
15000	71.25	70.12	68.91	101.84	71.65	80.71
15500	69.09	68.88	68.36	76.83	67.71	78.71
16000	68.06	66.89	68.35	70.50	65.17	78.25
16500	66.38	65.09	67.54	67.14	63.07	77.43
17000	64.47	63.32	67.27	64.45	61.42	77.43
17250	63.54	62.54	67.00	63.48	60.79	77.79
17500	62.99	61.91	66.93	62.20	59.86	76.75
17750	62.16	61.36	66.65	61.57	59.43	76.66
18000	61.66	60.86	66.48	60.88	58.88	75.76
18250	61.12	60.24	66.71	60.21	58.43	75.36
18500	60.67	59.91	66.69	59.54	57.78	75.07
18750	60.21	59.48	66.57	59.05	57.36	74.74
19000	59.68	58.99	67.13	58.47	56.94	73.73
19250	59.35	58.59	66.97	57.98	56.59	73.26
19500	58.91	58.13	67.68	57.70	56.29	72.49
19750	58.49	57.87	67.96	57.26	55.92	71.84
20000	58.18	57.48	68.57	56.83	55.82	71.12

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

REV. A

USB-1SP2T-183

220120

Page 4 of 6



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
50	0.80	0.80	1.16	1.16	1.16	1.10	1.10
250	0.91	0.91	1.11	1.11	1.11	1.08	1.08
500	1.00	1.01	1.10	1.11	1.11	1.09	1.09
750	1.08	1.09	1.09	1.09	1.11	1.11	1.11
1000	1.16	1.17	1.08	1.08	1.10	1.12	1.12
1250	1.19	1.20	1.08	1.08	1.08	1.12	1.13
1500	1.24	1.25	1.09	1.09	1.06	1.12	1.12
1750	1.28	1.30	1.11	1.13	1.06	1.12	1.12
2000	1.32	1.34	1.13	1.15	1.06	1.11	1.11
2250	1.35	1.37	1.16	1.18	1.07	1.10	1.10
2500	1.39	1.41	1.17	1.19	1.08	1.09	1.08
2750	1.42	1.44	1.19	1.21	1.08	1.07	1.07
3000	1.45	1.47	1.19	1.21	1.08	1.06	1.05
3500	1.50	1.52	1.20	1.21	1.08	1.04	1.02
4000	1.55	1.57	1.21	1.20	1.07	1.01	1.01
4500	1.59	1.61	1.18	1.17	1.07	1.03	1.05
5000	1.64	1.66	1.12	1.11	1.12	1.07	1.08
5500	1.71	1.74	1.11	1.13	1.22	1.11	1.12
6000	1.79	1.82	1.17	1.21	1.29	1.13	1.13
6500	1.85	1.89	1.20	1.23	1.29	1.12	1.13
7000	1.89	1.92	1.17	1.19	1.22	1.10	1.11
7500	1.93	1.95	1.11	1.12	1.15	1.06	1.07
8000	1.96	1.99	1.05	1.05	1.14	1.02	1.03
8500	2.01	2.03	1.03	1.02	1.16	1.03	1.04
9000	2.05	2.08	1.04	1.05	1.19	1.05	1.05
9500	2.11	2.13	1.05	1.07	1.21	1.06	1.06
10000	2.15	2.18	1.07	1.07	1.21	1.08	1.08
10500	2.19	2.21	1.06	1.05	1.18	1.12	1.10
11000	2.23	2.26	1.00	1.03	1.14	1.14	1.11
11500	2.27	2.30	1.08	1.08	1.12	1.14	1.11
12000	2.32	2.35	1.14	1.13	1.12	1.12	1.09
12500	2.37	2.39	1.17	1.15	1.12	1.09	1.07
13000	2.42	2.45	1.17	1.15	1.12	1.07	1.07
13500	2.48	2.52	1.18	1.18	1.18	1.08	1.10
14000	2.56	2.61	1.22	1.24	1.25	1.11	1.12
14500	2.63	2.69	1.25	1.29	1.28	1.11	1.12
15000	2.68	2.74	1.28	1.31	1.27	1.13	1.13
15500	2.73	2.77	1.30	1.30	1.22	1.14	1.14
16000	2.76	2.80	1.27	1.26	1.12	1.16	1.16
16500	2.78	2.83	1.23	1.23	1.03	1.16	1.18
17000	2.82	2.88	1.21	1.24	1.12	1.17	1.20
17250	2.84	2.91	1.21	1.24	1.16	1.17	1.21
17500	2.87	2.93	1.21	1.24	1.20	1.18	1.21
17750	2.88	2.95	1.20	1.23	1.22	1.18	1.20
18000	2.90	2.96	1.18	1.19	1.22	1.16	1.18
18250	2.92	2.98	1.15	1.16	1.21	1.15	1.16
18500	2.93	3.00	1.12	1.13	1.20	1.13	1.13
18750	2.96	3.03	1.10	1.11	1.20	1.09	1.08
19000	3.00	3.07	1.12	1.14	1.22	1.07	1.05
19250	3.04	3.12	1.17	1.20	1.26	1.06	1.06
19500	3.09	3.19	1.23	1.28	1.33	1.09	1.11
19750	3.15	3.26	1.29	1.36	1.40	1.13	1.16
20000	3.21	3.32	1.34	1.42	1.48	1.18	1.22

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SPDT Switch

# USB-1SP2T-183

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
50	91.16	87.79	88.79	83.65	84.54	95.46
250	81.73	83.34	86.01	78.89	79.63	97.32
500	76.45	76.29	82.49	74.54	74.08	89.98
750	73.53	73.26	78.24	70.44	70.23	87.06
1000	70.76	70.62	76.16	67.42	67.42	88.96
1250	68.53	68.76	73.23	65.57	65.58	84.17
1500	67.16	67.32	71.89	64.26	64.18	83.52
1750	66.31	66.34	70.68	62.99	62.88	80.62
2000	65.34	65.61	69.59	62.30	62.00	82.26
2250	64.94	64.78	69.08	61.51	61.57	79.57
2500	64.14	64.28	68.08	61.14	61.01	78.87
2750	63.83	63.93	68.44	60.71	60.55	78.21
3000	63.27	63.49	68.36	60.36	60.29	75.96
3500	62.93	62.97	67.59	60.26	59.90	75.51
4000	62.49	62.75	67.33	60.04	59.95	74.93
4500	62.38	62.26	67.48	60.31	60.08	74.36
5000	61.81	62.18	67.17	60.44	60.36	73.82
5500	61.74	61.69	66.68	60.75	60.44	74.94
6000	61.70	61.43	66.35	61.08	60.68	75.72
6500	61.71	61.60	65.82	61.38	60.93	76.56
7000	61.91	62.01	66.04	61.75	61.20	77.91
7500	62.01	61.99	66.71	62.34	61.53	79.77
8000	62.19	62.53	67.42	62.71	62.17	81.63
8500	62.91	63.01	68.42	63.14	62.50	82.86
9000	63.06	63.71	69.62	63.40	63.05	85.80
9500	63.38	64.32	69.70	63.83	63.55	86.62
10000	63.40	64.68	70.07	64.03	63.91	87.76
10500	63.49	64.74	70.55	63.98	64.30	86.33
11000	64.09	65.39	70.64	64.27	64.89	82.74
11500	64.49	65.99	71.35	64.52	65.50	83.78
12000	64.96	67.35	70.66	64.79	66.51	85.33
12500	66.58	68.48	70.59	65.59	67.93	83.31
13000	67.76	69.97	70.04	66.84	69.25	84.79
13500	69.80	71.43	69.94	68.30	72.30	81.00
14000	71.71	73.43	68.94	70.59	74.67	81.73
14500	73.21	73.31	68.95	74.36	76.40	83.94
15000	73.36	72.12	68.25	77.00	71.37	80.95
15500	72.03	70.22	68.29	75.41	68.64	79.77
16000	70.52	68.60	67.80	70.22	65.77	80.16
16500	68.28	66.58	67.48	67.44	64.02	79.15
17000	66.19	64.31	66.83	64.90	62.22	79.05
17250	65.26	63.60	66.78	63.81	61.40	77.57
17500	64.23	62.80	66.65	62.69	60.62	77.63
17750	63.33	62.17	66.41	62.09	59.89	76.92
18000	62.71	61.54	66.31	61.19	59.25	77.04
18250	62.23	61.20	66.50	60.37	58.79	76.10
18500	61.52	60.56	66.39	59.48	58.33	75.46
18750	61.14	60.30	66.36	59.13	57.80	75.14
19000	60.52	59.77	66.53	58.60	57.22	74.52
19250	60.04	59.26	66.85	58.18	57.00	74.00
19500	59.75	58.76	67.92	57.70	56.46	73.22
19750	59.22	58.39	67.87	57.30	56.26	72.20
20000	58.76	58.01	68.25	56.85	55.87	71.32

**Notes**




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)







## Typical Performance Curves

Test Conditions: @ Temperature = 0°C, pin = 8 dBm






## Typical Performance Curves

Test Conditions: @ Temperature = 0°C, pin = 8 dBm





## Typical Performance Curves

Test Conditions: @ Temperature = +25°C, pin = 8 dBm






## Typical Performance Curves

Test Conditions: @ Temperature = +25°C, pin = 8 dBm



## Typical Performance Curves

Test Conditions: @ Temperature = +50°C, pin = 8 dBm





**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



## Typical Performance Curves

Test Conditions: @ Temperature = +50°C, pin = 8 dBm




**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



## Outline Dimensions

NR3244



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
NR3244	2.30 (58.42)	2.00 (50.80)	.575 (14.61)	.100 (2.54)	2.250 (57.15)	2.50 (63.50)	2.050 (52.07)	.106 (2.69)	.500 (12.70)	.650 (16.51)	100

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

- Case material: Nickel Plated Aluminum.

**Mini-Circuits**<sup>®</sup>

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3