


Solid state, true DC

USB RF SPDT Switch Matrix USB-2SP2T-DCH

50Ω DC to 8000 MHz

The Big Deal

- DC passing & ultra-wide bandwidth, DC to 8 GHz
- High isolation, 50 dB typ up to 4 GHz
- High power handling, +35 dBm max
- Daisy-chain control of up to 35 modules



Software Package

Case Style: QM2278

Typical Applications

- Satcom / GNSS antenna switching (RF & DC paths)
- Signal routing / switch matrices
- High volume production testing / ATE
- Design verification testing

Model No.	Description	Qty.
USB-2SP2T-DCH	Switch Matrix	1

Included Accessories

MUSB-CBL-3+	3.3 ft USB cable	1
-------------	------------------	---

RoHS Compliant

See our web site for RoHS Compliance methodologies and qualifications

Product Overview

Mini-Circuits' USB-2SP2T-DCH is a low cost, USB controlled, solid state matrix, containing two independent SPDT RF switches. Each fast switching, absorptive SPDT switch operates from true DC all the way to 8 GHz with 10 μ s typical switch transition speed. High linearity (+50 dBm typ IP3), low insertion loss (1.5 dB typ) and high isolation (50 dB typical) allow the model to be used for a wide variety of RF applications.

Full software support is provided for USB control, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems). The latest version of the full software package can be downloaded from <https://www.minicircuits.com/softwaredownload/solidstate.html> at any time.

The USB-2SP2T-DCH is housed in a compact, low profile, rugged metal case (4.58" x 2.00" x 0.475") with 6 SMA (F) connectors (COM, 1 and 2 for each switch), and a USB Mini-B port for power control and two data bus connectors for Master / Slave connections to other modules.

Key Features

Feature	Advantages
High speed switch transition (10 μ sec typ)	High speed switching reduces the time the signal paths are interrupted and allows the switch to be used in a wider range of applications.
High Linearity (IP3 50 dBm typ.)	Results in little or negligible inter-modulation generation, meeting requirements for digital communications signals
Low insertion loss (1.5 dB typ)	Results in reduced system loss and heat build up
Dynamic daisy-chain control	Simplify control software and interconnections by cascading up to 35 modules of multiple switch types into a Master / Slave chain with a single USB interface.
Full software support included	Mini-Circuits' full software package, programming and user manual are available for down load from https://www.minicircuits.com/softwaredownload/solidstate.html at no extra cost.

Trademarks: Windows is a registered trademark of Microsoft Corporation in the United States and other countries. Linux is a registered trademark of Linus Torvalds. Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits USB-2SP2T-DCH are affiliated with or endorsed by the owners of the above referenced trademarks

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Rev. H
ECO-025516
EDR-11445
USB-2SP2T-DCH
MCIL
250512
Page 1 of 9

Electrical Specifications @ 0 to 50°C

Parameter	Port	Conditions	Min.	Typ.	Max.	Units
Operating Frequency			DC		8000	MHz
Insertion Loss	COM to any active port	DC to 300 MHz	-	0.75	1.2	dB
		300 - 3000 MHz	-	1.0	1.5	
		3000 - 6000 MHz	-	1.3	2.5	
		6000 - 8000 MHz	-	1.7	3.0	
Isolation	Between ports 1 and 2 of each switch	DC to 300 MHz	70	90	-	dB
		300 - 3000 MHz	46	57	-	
		3000 - 6000 MHz	33	44	-	
		6000 - 8000 MHz	28	37	-	
	COM to any terminated port	DC to 300 MHz	62	81	-	
		300 - 3000 MHz	40	51	-	
		3000 - 6000 MHz	31	41	-	
		6000 - 8000 MHz	26	36	-	
	Crosstalk between switches	DC to 8000 MHz	71	103	-	
Return Loss	COM or any active port	DC to 3000 MHz	-	21.0	-	dB
		3000 - 6000 MHz	-	19.0	-	
		6000 - 8000 MHz	-	15.5	-	
	Any terminated port	DC to 3000 MHz	-	23.0	-	
		3000 - 6000 MHz	-	17.5	-	
		6000 - 8000 MHz	-	16.5	-	
Power Input @1 dB Compression 1,2,3	COM to any active port	40 to 8000 MHz	-	38	-	dBm
IP3 3,4	COM to any active port	40 to 8000 MHz	-	50	-	dBm
Transition Time 5	-		-	10	14	µs
Minimum dwell time 6	High Speed Mode		-	20	-	µs
Switching Time (USB) 7	-	-	-	2	-	ms
Supply voltage (Vcc)	USB port	-	4.75	5	5.25	V _{DC}
Supply Current (Icc) 8		-	-	150	200	mA
Current Pass-through 9		-	-	-	500	
Operating RF Input Power	COM to any active port	Hot Switching 1	-	-	+23	dBm
	Any terminated port	Note 1	-	-	+23	
	COM to any active port	Through path 2	-	-	+35	
DC bias voltage	Any RF port	-	-7	-	7	V
DC pass-through current	COM to any active port		-60	-	60	mA

¹ Max operating power at terminated port degrades linearly below 20 MHz to +17 dBm at 2 MHz and remains constant from 2 MHz to DC.

² Max operating power at through path degrades linearly below 30 MHz to +25 dBm at 2 MHz and remains constant from 2 MHz to DC.

³ Compression and IP3 degrade below 40 MHz.

⁴ IP3 tested with 1 MHz span between signals.

⁵ Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

⁶ Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

⁷ Switching time (USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

⁸ Current consumption specified for a single unit without any slave modules.

⁹ Pass through current is the maximum current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. See page 5 for details.

Absolute Maximum Ratings


Operating Temperature		0°C to 50°C
Storage Temperature		-20°C to 60°C
DC supply voltage max.		6V
RF power into termination	DC - 20 MHz	Derate linearly from +24 dBm@20 Mhz to +18 dBm@ 2MHz and remains constant from 2 MHz to DC
	20 - 8000 MHz	+24 dBm
RF power @ Through Path	DC - 30 MHz	Derate linearly from +38 dBm@30 MHz to +28 dBm at 2 MHz and remains constant from 2 MHz to DC
	30 - 8000 MHz	38 dBm
DC voltage @ RF Ports		±7V
DC pass-through current		80mA

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

Connections


RF SPDT Switch A (1, 2, COM)	(SMA female)
RF SPDT Switch B (1, 2, COM)	(SMA female)
USB	(USB type Mini-B receptacle)
Serial In (Digital Control 2 port)	(Digital Snap Fit Connector)
Serial Out (Digital Control 1 port)	(Digital Snap Fit Connector)

Simplified Diagram




Typical Performance Curves


Insertion Loss over Temperature (1 Active)




Insertion Loss 1 - 2 Active




Isolation Com to 1 (2 Active)




Isolation Com to 2 (1 Active)



Isolation 1 to 2 (1 Active)




Crossover @ Active states




Typical Performance Curves (Continued)


Return Loss @ COM over Temperature (1 Active)




Return Loss @ 1 over Temperature (1 Active)




Return Loss @ 1 over Temperature (1 Terminated)



Return Loss @ 2 over Temperature (2 Active)




Return Loss @ 2 over Temperature (2 Terminated)



Connecting multiple modules (Daisy Chain)

The USB-2SP2T-DCH is designed to connect up to 35 modules in series (Daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules, the addresses will be set automatically as part of establishing the communications with the PC. The module connected to the PC USB port will be assigned address 0 (Master), the first module connected to it will get address 1(slave) and subsequent modules incrementing up to address 34 (slave).





Connections between modules will be made using the serial in/out ports with the module connected to the PC as a master and all others as slave modules. All control will be through the master module (address zero) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module. Power will be supplied from the PC via the master module up to a maximum of 500mA.

If connecting USB-2SP2T-DCH units in series, additional power supply will generally be needed every six to eight modules. If mixing modules of different types ensure the max current through any unit does not exceed 500mA. All power supplies should be connected to the module via the module's USB port, connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The Serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the set up simply connect the module to the setup and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Connecting slave units should be done only with control cables provided by Mini-Circuits

Outline Drawing (QM2278)



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	WT. GRAMS
4.58	2.00	.475	0.217	0.69	0.640	4.380	1.000	0.10	0.50	260
116.33	50.8	12.07	5.51	17.53	16.26	111.25	25.40	2.54	12.70	

Software & Documentation Download:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from <https://www.minicircuits.com/softwaredownload/solidstate.html>
- Please contact testsolutions@minicircuits.com for support


Minimum System Requirements

Parameter	Requirements	
Interface	USB HID	
System requirements	GUI	Windows 32 & 64 bit systems from Windows 98 up to Windows 10
	USB API (ActiveX & .Net)	Windows 32 & 64 bit systems with ActiveX or .Net support from Windows 98 up to Windows 10
	Daisy Chain Dynamic addressing	Additional unit of this model or another Mini-Circuits model supporting Dynamic addressing
	USB direct programming support	Linux, Windows systems from Windows 98 up to Windows 10
Hardware	Pentium® II or higher, RAM 256 MB	

Graphical User Interface (GUI) for Windows

Key Features:

- Set each switch manually
- Set timed sequence of switching states
- Configure switch address and upgrade Firmware
- Controlling up to 35 modules in 'daisy chain' configuration



Application Programming Interface (API)

Windows Support:

- API DLL files exposing the full switch functionality See programming manual at https://www.minicircuits.com/softwaredownload/Prog_Manual-Solid_State_Switch.pdf for details
 - ActiveX COM DLL file for creation of 32-bit programs
 - .Net library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note [AN-49-001](#) for summary of tested environments)

Linux Support:

- Full switch control in a Linux environment is achieved by way of USB interrupt commands. See programming manual at https://www.minicircuits.com/softwaredownload/Prog_Manual-H_Series_Switches.pdf for details

Ordering, Pricing & Availability Information see our web site

Model	Description
USB-2SP2T-DCH	USB RF SPDT Switch matrix

Included Accessories	Part No.	Description
	MUSB-CBL-3+	3.3 ft (1.0 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)

Optional Accessories	Description
MUSB-CBL-3+ (Spare)	3.3 ft (1.0 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)
MUSB-CBL-7+	6.6 ft (2.0 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)
CBL-1.5FT-MMD+	1.5 ft cable assembly for serial control Daisy Chain with snap fit connectors
USB-AC/DC-5+	AC/DC +5V power adaptor with USB connector ^{10,11}

¹⁰ The USB-AC/DC-5 may be used to provide additional power if needing to connect a number of switches in series exceeding 500mA total current draw.

¹¹ Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available, if you need a power plug for a country not listed please contact testsolutions@minicircuits.com

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS		VSWR, Active Ports			VSWR, Internally Terminated Ports	
	(dB)		(:1)			(:1)	
	COM-1	COM-2	Port1	Port2	COM	Port1	Port2
0.01	0.62	0.61	1.15	1.15	1.15	1.01	1.01
1	0.62	0.62	1.15	1.15	1.15	1.01	1.01
5	0.63	0.63	1.14	1.14	1.14	1.01	1.01
10	0.62	0.63	1.14	1.14	1.14	1.01	1.01
20	0.65	0.64	1.15	1.14	1.15	1.01	1.01
30	0.65	0.64	1.15	1.15	1.15	1.01	1.01
50	0.66	0.65	1.15	1.14	1.15	1.01	1.01
70	0.67	0.66	1.14	1.14	1.15	1.01	1.01
80	0.67	0.67	1.15	1.14	1.15	1.01	1.01
100	0.68	0.68	1.15	1.14	1.15	1.01	1.01
400	0.75	0.74	1.14	1.14	1.16	1.04	1.04
500	0.76	0.75	1.14	1.14	1.16	1.05	1.05
600	0.77	0.76	1.14	1.14	1.17	1.05	1.05
700	0.78	0.77	1.14	1.13	1.17	1.06	1.05
800	0.79	0.78	1.13	1.13	1.17	1.06	1.06
1000	0.81	0.80	1.13	1.12	1.17	1.07	1.07
1200	0.82	0.81	1.12	1.10	1.18	1.08	1.07
1400	0.84	0.83	1.11	1.09	1.17	1.08	1.07
1600	0.85	0.85	1.10	1.08	1.16	1.08	1.07
1800	0.87	0.86	1.11	1.09	1.14	1.08	1.07
2000	0.89	0.88	1.11	1.10	1.12	1.07	1.06
2200	0.91	0.91	1.13	1.12	1.10	1.06	1.05
2400	0.93	0.94	1.15	1.15	1.08	1.05	1.03
2600	0.95	0.96	1.16	1.18	1.07	1.04	1.02
2800	0.97	0.98	1.17	1.21	1.06	1.04	1.01
3000	0.98	0.99	1.17	1.21	1.06	1.04	1.01
3200	1.00	1.01	1.17	1.22	1.06	1.04	1.01
3400	1.02	1.03	1.17	1.23	1.06	1.05	1.01
3600	1.04	1.06	1.16	1.22	1.07	1.06	1.02
3800	1.06	1.08	1.15	1.20	1.08	1.06	1.03
4000	1.07	1.09	1.14	1.18	1.08	1.07	1.03
4200	1.09	1.11	1.13	1.16	1.09	1.07	1.03
4400	1.10	1.11	1.12	1.14	1.10	1.08	1.03
4600	1.12	1.13	1.11	1.12	1.11	1.08	1.02
4800	1.15	1.15	1.11	1.10	1.12	1.07	1.02
5000	1.17	1.17	1.10	1.07	1.12	1.07	1.02
5200	1.20	1.21	1.09	1.06	1.14	1.06	1.02
5400	1.23	1.24	1.11	1.08	1.13	1.05	1.01
5600	1.26	1.28	1.12	1.13	1.14	1.07	1.02
5800	1.30	1.33	1.17	1.21	1.15	1.09	1.04
6000	1.34	1.39	1.18	1.25	1.18	1.11	1.06
6200	1.37	1.44	1.23	1.30	1.18	1.15	1.10
6400	1.41	1.50	1.27	1.37	1.21	1.20	1.13
6600	1.45	1.54	1.30	1.42	1.22	1.25	1.17
6800	1.49	1.60	1.32	1.47	1.23	1.32	1.21
7000	1.53	1.64	1.34	1.49	1.24	1.37	1.26
7200	1.55	1.67	1.32	1.49	1.22	1.42	1.28
7400	1.56	1.67	1.29	1.44	1.19	1.45	1.31
7600	1.56	1.66	1.23	1.38	1.16	1.47	1.32
8000	1.54	1.59	1.10	1.20	1.16	1.47	1.31
8100	1.54	1.59	1.06	1.16	1.18	1.46	1.31
8300	1.57	1.61	1.02	1.07	1.24	1.43	1.28
8500	1.62	1.64	1.10	1.05	1.32	1.39	1.24

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION			
	(dB)			
	COM-1	COM-2	Port 1-2	Between switches
0.01	91.28	91.48	95.14	82.67
1	91.99	88.94	90.49	98.87
5	92.94	93.43	96.31	93.91
10	97.22	97.11	115.26	110.48
20	90.98	90.94	103.04	112.72
30	88.42	88.95	98.58	100.86
50	84.92	83.98	98.74	111.30
70	80.97	80.75	95.41	107.32
80	80.43	79.90	99.14	103.29
100	78.90	77.52	94.92	108.95
400	66.45	65.90	85.43	102.12
500	64.35	64.02	80.98	119.27
600	62.90	62.46	79.38	113.89
700	61.59	61.08	76.95	99.58
800	60.52	60.00	74.16	101.08
1000	58.27	57.89	72.34	101.71
1200	56.92	56.45	69.22	99.12
1400	55.71	55.20	66.41	108.89
1600	54.66	54.12	63.88	103.33
1800	53.74	53.08	61.46	106.54
2000	52.73	51.95	58.77	103.77
2200	51.10	50.40	56.32	96.73
2400	49.45	48.98	55.18	99.67
2600	48.64	48.34	55.11	108.87
2800	48.16	47.95	54.75	92.46
3000	47.66	47.52	54.06	101.03
3200	47.12	47.07	53.15	86.22
3400	46.52	46.58	52.14	83.85
3600	45.84	45.97	51.09	87.29
3800	45.14	45.39	50.17	87.97
4000	44.38	44.73	49.22	92.64
4200	43.54	44.00	48.34	94.72
4400	42.69	43.31	47.44	86.30
4600	41.86	42.64	46.56	89.26
4800	41.08	42.06	45.91	89.06
5000	40.40	41.49	45.34	81.60
5200	39.75	40.94	44.94	78.26
5400	39.18	40.34	44.53	82.36
5600	38.72	39.77	44.28	85.66
5800	38.40	39.20	44.13	80.97
6000	38.28	38.65	44.26	79.61
6200	38.04	38.19	43.59	82.99
6400	37.65	37.85	42.62	78.53
6600	37.31	37.61	41.64	82.08
6800	37.10	37.47	40.86	83.39
7000	36.84	37.48	39.89	78.06
7200	36.48	37.46	38.92	78.72
7400	36.43	37.41	38.30	76.90
7600	36.56	37.32	37.77	73.96
8000	36.43	37.01	36.59	70.98
8100	36.47	36.90	36.40	72.81
8300	36.47	36.63	36.01	72.08
8500	36.32	36.19	35.58	76.90

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
 USB-2SP2T-DCH
 170620
 Page 2 of 6

Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 25°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS		VSWR, Active Ports			VSWR, Internally Terminated Ports	
	(dB)		(:1)			(:1)	
	COM-1	COM-2	Port1	Port2	COM	Port1	Port2
0.01	0.00	0.65	1.16	1.16	1.16	1.02	1.03
1	0.66	0.66	1.16	1.16	1.16	1.02	1.03
5	0.67	0.67	1.15	1.15	1.15	1.02	1.03
10	0.00	0.68	1.15	1.15	1.15	1.02	1.03
20	0.68	0.68	1.16	1.16	1.16	1.02	1.03
30	0.68	0.68	1.16	1.16	1.16	1.02	1.03
50	0.69	0.69	1.15	1.15	1.16	1.02	1.03
70	0.70	0.70	1.15	1.15	1.15	1.03	1.03
80	0.71	0.71	1.15	1.15	1.16	1.03	1.03
100	0.72	0.72	1.15	1.16	1.16	1.03	1.03
400	0.79	0.79	1.15	1.15	1.16	1.04	1.04
500	0.80	0.80	1.15	1.15	1.17	1.04	1.04
600	0.82	0.82	1.15	1.14	1.17	1.04	1.04
700	0.83	0.83	1.15	1.14	1.17	1.05	1.04
800	0.84	0.84	1.14	1.14	1.18	1.05	1.04
1000	0.85	0.85	1.13	1.12	1.18	1.05	1.04
1200	0.87	0.87	1.13	1.11	1.18	1.05	1.04
1400	0.89	0.89	1.12	1.10	1.17	1.05	1.04
1600	0.91	0.91	1.11	1.10	1.16	1.04	1.03
1800	0.93	0.93	1.12	1.10	1.15	1.04	1.02
2000	0.95	0.95	1.13	1.12	1.13	1.04	1.01
2200	0.97	0.98	1.13	1.13	1.11	1.04	1.01
2400	1.00	1.00	1.15	1.16	1.10	1.04	1.01
2600	1.01	1.02	1.16	1.18	1.08	1.05	1.02
2800	1.03	1.05	1.17	1.20	1.07	1.06	1.03
3000	1.05	1.06	1.18	1.22	1.07	1.07	1.03
3200	1.07	1.09	1.17	1.23	1.07	1.08	1.04
3400	1.09	1.11	1.17	1.23	1.08	1.08	1.04
3600	1.11	1.13	1.16	1.23	1.08	1.09	1.04
3800	1.13	1.16	1.15	1.21	1.09	1.09	1.04
4000	1.14	1.17	1.15	1.19	1.09	1.09	1.04
4200	1.16	1.19	1.14	1.17	1.10	1.09	1.04
4400	1.18	1.19	1.13	1.15	1.10	1.08	1.03
4600	1.20	1.21	1.12	1.12	1.12	1.07	1.03
4800	1.23	1.23	1.11	1.10	1.13	1.06	1.03
5000	1.25	1.26	1.11	1.08	1.13	1.05	1.03
5200	1.29	1.30	1.11	1.08	1.14	1.03	1.03
5400	1.32	1.33	1.12	1.11	1.14	1.02	1.03
5600	1.35	1.38	1.14	1.16	1.16	1.05	1.05
5800	1.39	1.43	1.17	1.21	1.17	1.09	1.08
6000	1.42	1.48	1.19	1.26	1.18	1.12	1.10
6200	1.46	1.53	1.22	1.30	1.18	1.16	1.13
6400	1.50	1.59	1.26	1.36	1.21	1.22	1.17
6600	1.54	1.63	1.29	1.40	1.22	1.28	1.21
6800	1.58	1.68	1.31	1.43	1.22	1.33	1.25
7000	1.62	1.72	1.32	1.45	1.22	1.38	1.29
7200	1.65	1.76	1.31	1.45	1.21	1.43	1.31
7400	1.66	1.76	1.29	1.41	1.19	1.46	1.34
7600	1.67	1.76	1.24	1.36	1.16	1.48	1.35
8000	1.65	1.71	1.11	1.21	1.16	1.49	1.34
8100	1.66	1.71	1.07	1.18	1.18	1.48	1.33
8300	1.68	1.72	1.01	1.10	1.23	1.46	1.30
8500	1.73	1.76	1.10	1.05	1.33	1.41	1.24

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
USB-2SP2T-DCH
170620
Page 3 of 6

Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 25°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION			
	(dB)			
	COM-1	COM-2	Port 1-2	Between switches
0.01	85.27	84.81	92.15	86.61
1	95.35	123.11	97.80	90.55
5	95.04	88.87	90.86	95.28
10	97.66	102.41	105.48	112.41
20	93.80	88.82	103.62	107.21
30	88.65	88.18	102.26	96.16
50	85.04	83.59	97.00	104.88
70	81.27	81.05	100.61	103.51
80	80.53	79.98	101.97	103.15
100	78.58	78.17	94.10	105.13
400	66.54	65.98	86.81	102.86
500	64.46	64.04	83.03	114.72
600	62.98	62.51	80.40	109.75
700	61.63	61.13	77.47	101.34
800	60.63	60.12	74.73	105.42
1000	58.33	57.93	72.88	103.15
1200	56.96	56.47	69.54	98.84
1400	55.77	55.21	66.88	115.65
1600	54.73	54.12	64.15	110.17
1800	53.75	53.07	61.64	103.35
2000	52.67	51.93	58.91	110.52
2200	51.06	50.34	56.43	107.31
2400	49.43	48.99	55.28	99.72
2600	48.63	48.35	55.18	103.15
2800	48.16	47.95	54.73	95.50
3000	47.66	47.51	54.07	96.07
3200	47.12	47.05	53.15	87.60
3400	46.53	46.55	52.14	85.96
3600	45.80	45.96	51.04	87.83
3800	45.12	45.35	50.10	90.84
4000	44.36	44.70	49.16	97.14
4200	43.57	44.00	48.28	89.41
4400	42.70	43.28	47.36	87.46
4600	41.86	42.56	46.52	87.70
4800	41.09	41.96	45.85	89.53
5000	40.39	41.39	45.28	82.46
5200	39.76	40.82	44.83	80.84
5400	39.19	40.25	44.46	83.08
5600	38.74	39.72	44.21	86.66
5800	38.43	39.22	44.02	82.17
6000	38.29	38.70	44.02	81.73
6200	38.08	38.28	43.49	85.38
6400	37.64	37.94	42.56	80.67
6600	37.24	37.69	41.52	84.00
6800	36.98	37.53	40.69	81.12
7000	36.73	37.50	39.81	78.35
7200	36.39	37.45	38.87	77.12
7400	36.30	37.32	38.20	75.78
7600	36.41	37.15	37.68	73.14
8000	36.30	36.89	36.56	71.47
8100	36.35	36.79	36.38	73.89
8300	36.33	36.49	35.99	74.80
8500	36.13	36.03	35.57	77.64

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
 USB-2SP2T-DCH
 170620
 Page 4 of 6

Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 50°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS		VSWR, Active Ports			VSWR, Internally Terminated Ports	
	(dB)		(:1)			(:1)	
	COM-1	COM-2	Port1	Port2	COM	Port1	Port2
0.01	0.70	0.71	1.17	1.17	1.17	1.07	1.08
1	0.70	0.71	1.17	1.17	1.17	1.07	1.08
5	0.72	0.73	1.17	1.17	1.17	1.07	1.08
10	0.70	0.73	1.17	1.17	1.17	1.07	1.08
20	0.73	0.74	1.17	1.17	1.17	1.07	1.08
30	0.73	0.74	1.17	1.17	1.17	1.07	1.08
50	0.74	0.75	1.17	1.17	1.17	1.07	1.08
70	0.75	0.76	1.16	1.17	1.17	1.06	1.07
80	0.75	0.76	1.16	1.17	1.17	1.06	1.07
100	0.76	0.77	1.17	1.17	1.17	1.06	1.07
400	0.84	0.84	1.16	1.16	1.17	1.07	1.08
500	0.85	0.86	1.16	1.16	1.18	1.07	1.08
600	0.86	0.87	1.16	1.16	1.18	1.06	1.07
700	0.88	0.89	1.16	1.15	1.18	1.06	1.07
800	0.89	0.90	1.15	1.15	1.18	1.06	1.07
1000	0.90	0.91	1.15	1.14	1.19	1.05	1.06
1200	0.92	0.93	1.14	1.13	1.19	1.04	1.05
1400	0.94	0.95	1.13	1.11	1.18	1.02	1.04
1600	0.96	0.96	1.12	1.10	1.17	1.01	1.03
1800	0.98	0.98	1.12	1.11	1.16	1.01	1.02
2000	1.00	1.01	1.13	1.12	1.14	1.03	1.03
2200	1.03	1.04	1.14	1.14	1.12	1.05	1.04
2400	1.05	1.06	1.16	1.17	1.11	1.07	1.06
2600	1.07	1.09	1.18	1.19	1.09	1.08	1.07
2800	1.09	1.11	1.19	1.22	1.08	1.10	1.08
3000	1.11	1.13	1.19	1.24	1.08	1.11	1.08
3200	1.13	1.15	1.19	1.25	1.08	1.12	1.08
3400	1.15	1.18	1.18	1.25	1.08	1.12	1.08
3600	1.17	1.20	1.17	1.23	1.09	1.12	1.08
3800	1.19	1.23	1.16	1.22	1.09	1.12	1.08
4000	1.21	1.24	1.16	1.20	1.09	1.12	1.08
4200	1.23	1.26	1.15	1.18	1.10	1.12	1.08
4400	1.24	1.26	1.14	1.16	1.11	1.10	1.07
4600	1.26	1.28	1.13	1.14	1.12	1.09	1.07
4800	1.29	1.30	1.12	1.11	1.13	1.07	1.06
5000	1.31	1.33	1.12	1.08	1.13	1.04	1.06
5200	1.36	1.37	1.12	1.10	1.16	1.02	1.06
5400	1.39	1.41	1.14	1.14	1.16	1.04	1.07
5600	1.43	1.46	1.15	1.19	1.18	1.07	1.08
5800	1.47	1.51	1.18	1.23	1.18	1.12	1.12
6000	1.50	1.57	1.20	1.28	1.20	1.16	1.14
6200	1.55	1.62	1.24	1.32	1.21	1.20	1.19
6400	1.58	1.67	1.27	1.36	1.22	1.26	1.22
6600	1.62	1.71	1.29	1.38	1.21	1.31	1.27
6800	1.66	1.75	1.32	1.42	1.22	1.37	1.30
7000	1.70	1.79	1.33	1.43	1.22	1.41	1.34
7200	1.73	1.83	1.31	1.42	1.20	1.45	1.36
7400	1.74	1.83	1.28	1.39	1.17	1.47	1.38
7600	1.75	1.84	1.23	1.35	1.16	1.50	1.39
8000	1.72	1.80	1.11	1.23	1.16	1.51	1.37
8100	1.73	1.80	1.08	1.20	1.18	1.51	1.35
8300	1.76	1.81	1.01	1.12	1.25	1.48	1.31
8500	1.81	1.85	1.09	1.06	1.34	1.44	1.25

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State

USB DUAL RF SPDT Switch USB-2SP2T-DCH

Typical Performance Data

TEST CONDITIONS: @Temperature = 50°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION			
	(dB)			
	COM-1	COM-2	Port 1-2	Between switches
0.01	83.64	98.23	86.03	89.79
1	86.32	85.27	101.61	87.97
5	93.01	91.60	91.79	80.67
10	94.77	97.62	95.42	108.77
20	90.92	91.40	98.23	104.15
30	88.07	88.90	105.48	105.66
50	85.76	83.79	103.41	104.40
70	81.33	80.44	98.57	110.51
80	80.73	80.05	99.09	108.92
100	78.53	78.12	97.57	101.67
400	66.43	66.01	88.99	114.49
500	64.60	64.02	84.35	139.84
600	63.08	62.49	81.01	108.78
700	61.66	61.19	79.15	103.51
800	60.69	60.00	76.00	101.73
1000	58.35	57.88	73.21	99.68
1200	56.98	56.48	69.89	104.95
1400	55.75	55.20	66.95	105.52
1600	54.74	54.08	64.41	112.02
1800	53.72	52.99	61.78	104.15
2000	52.65	51.78	58.98	109.45
2200	50.98	50.22	56.44	98.90
2400	49.37	48.87	55.24	114.66
2600	48.59	48.28	55.03	100.45
2800	48.11	47.88	54.71	103.10
3000	47.60	47.43	54.00	93.56
3200	47.07	46.99	53.09	91.10
3400	46.47	46.46	52.09	85.56
3600	45.77	45.85	51.05	86.03
3800	45.07	45.24	50.06	88.17
4000	44.33	44.58	49.07	93.24
4200	43.50	43.86	48.22	88.80
4400	42.64	43.15	47.28	88.01
4600	41.80	42.42	46.40	86.70
4800	41.02	41.83	45.71	90.50
5000	40.32	41.26	45.13	81.97
5200	39.68	40.69	44.71	80.75
5400	39.13	40.12	44.28	84.37
5600	38.66	39.61	44.01	90.49
5800	38.34	39.14	43.77	82.38
6000	38.22	38.68	43.86	82.83
6200	38.09	38.27	43.50	85.26
6400	37.58	37.94	42.45	78.93
6600	37.17	37.74	41.46	80.86
6800	36.89	37.58	40.64	79.30
7000	36.62	37.46	39.76	76.46
7200	36.26	37.23	38.79	76.10
7400	36.14	36.98	38.12	76.02
7600	36.20	36.79	37.59	72.07
8000	36.04	36.55	36.47	71.15
8100	36.08	36.45	36.29	72.45
8300	36.01	36.16	35.93	73.23
8500	35.76	35.66	35.47	77.15

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Solid State USB DUAL RF SPDT Switch

USB-2SP2T-DCH

Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Solid State USB DUAL RF SPDT Switch

USB-2SP2T-DCH

Typical Performance Curves

TEST CONDITIONS: @Temperature =25°C, Pin=8dBm




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Solid State USB DUAL RF SPDT Switch

USB-2SP2T-DCH

Typical Performance Curves


TEST CONDITIONS: @Temperature = 50°C, Pin=8dBm




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCULStoreTerms.jsp

Outline Dimensions

QM2278



Bracket Option



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P
QM2278	4.58 (116.33)	2.00 (50.8)	.475 (12.07)	.217 (5.51)	.69 (17.53)	.640 (16.26)	4.380 (111.25)	1.000 (25.40)	0.10 (2.54)	0.50 (12.70)	.106 (2.69)	8.42 (213.87)	.125 (3.18)	8.220 (208.79)

CASE#	Q	WT. GRAMS
QM2278	1.92 (48.77)	260

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Nickel Plated Aluminum.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



Environmental Specifications ENV55

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3