



**SURFACE MOUNT**

# SPDT RF Switch

## VSW2-33-10W+

50Ω 50 to 3000 MHz Reflective RF Switch 10 W  
Positive Control Voltage; +3 V to +5 V

### THE BIG DEAL

- High Power, 10 W (Cold Switching)
- Good Isolation, 26 dB Typ. at 1 GHz
- Low Insertion Loss, 0.5 dB Typ. at 1 GHz
- High IP3, +56 dBm Typ. at 1 GHz
- Small Size, 3 x 2 x 0.89 mm
- Aqueous Washable



Generic photo used for illustration purposes only  
CASE STYLE: JZ1436

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

### APPLICATIONS

- Automated Switching Networks
- Cellular/ PCS
- ISM, WCDMA, WiMAX, LTE, TD-SCDMA

### PRODUCT OVERVIEW

The VSW2-33-10W+ is a PHEMT high power reflective SPDT switch operates with positive control voltage while consuming, 20  $\mu$ A typical. Compared to competitive models, it operates over a wide frequency range, 50 to 3000 MHz and control voltages up to +5 V. It is packaged in a tiny 2 x 3 x 1 mm package and is rated MSL1 and class 1A for HBM.

### KEY FEATURES

Features	Advantages
Broadband, 50 to 3000 MHz	Covers a range of wireless applications such as Cellular, PCS, LTE, WiMAX, Avionics, Broadcast, CATV, GPS, Radar, etc.
High Input Power, 10 W (Cold Switching) at +5 V Control	Suitable for Transmit/receive switching.
Low Insertion Loss, 0.5 dB Typ. at 1 GHz	Premium high power is transmitted with minimal loss and temperature rise of the DUT. In receive path results in minimal increase of system noise figure.
Positive Control Voltage, 0/+3 V or 0/+5 V	No external components are required for change of operating voltage from +3 to +5 V.
Good Isolation, 26 dB to 1 GHz and 18 dB to 3 GHz	Minimizes filtering requirement.

REV. B  
ECO-026600  
VSW2-33-10W+  
MCL NY  
260429





SURFACE MOUNT

# SPDT RF Switch

## VSW2-33-10W+

50Ω 50 to 3000 MHz Reflective RF Switch 10 W  
Positive Control Voltage; +3 V to +5 V

### RF ELECTRICAL SPECIFICATIONS<sup>1</sup>, T<sub>AMB</sub> = +25°C, V<sub>CTL</sub> = +3 V TO +5 V

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units	
Frequency Range		50		3000	MHz	
Insertion Loss <sup>2</sup>	50	-	0.4		dB	
	500	-	0.4	0.6		
	1000	-	0.5	0.7		
	2000	-	0.6	0.8		
	3000	-	0.6	0.8		
Isolation (From RF COM to RF1/RF2 and RF1 to RF2 Ports)	50	-	42	-	dB	
	500	28	31	-		
	1000	23	26	-		
	2000	17	22	-		
	3000	15	18	-		
Return Loss (ON STATE)	50	-	24	-	dB	
	500	-	27	-		
	1000	-	21	-		
	2000	-	17	-		
	3000	-	19	-		
Input IP3	100	-	+55	-	dBm	
	500	-	+56	-		
	1000	-	+56	-		
	2000	-	+55	-		
	3000	-	+53	-		
Operating Power <sup>3,4,5</sup> (Cold Switching)	V <sub>CTL</sub> = +3 V	50	-	-	7	W
		1000	-	-	7	
		2000	-	-	7	
		3000	-	-	7	
	V <sub>CTL</sub> = +5 V	50	-	-	10	
		1000	-	-	10	
		2000	-	-	9	
		3000	-	-	7	

1. Tested on Mini-Circuits' test board TB-530+, (see Characterization Test Circuit, Fig. 1).
2. Insertion loss values are de-embedded from test board loss.
3. Do not exceed RF input power as shown in Absolute Maximum Rating table.
4. Derate linearly to 3 W at +85°C ground lead temperature.
5. Compression 0.1 dB typ. over 1000-3000 MHz and 0.5 dB typical at 50 MHz at max. operating power.

### DC ELECTRICAL SPECIFICATIONS

Parameter	Min.	Typ.	Max.	Units
Control Voltage Low (V <sub>CTL</sub> )	0	-	0.2	V
Control Voltage High (V <sub>CTL</sub> )	2.8	-	5.2	V
Control Current at	(V <sub>CTL</sub> ) = +3 V	-	20	μA
	(V <sub>CTL</sub> ) = +5 V	-	42	





SURFACE MOUNT

# SPDT RF Switch

## VSW2-33-10W+

50Ω 50 to 3000 MHz Reflective RF Switch 10 W  
Positive Control Voltage; +3 V to +5 V

### SWITCHING SPECIFICATIONS

Parameter	Control Voltage (V)	Min.	Typ.	Max.	Units
Rise/Fall Time (10 to 90% or 90 to 10% RF)	0/+3	-	433	-	ns
	0/+5	-	150	-	
Switching Time, 50% CTRL to 90/10% RF	0/+3	-	550	-	ns
	0/+5	-	306	-	
Video Feed-Through, (Control 0 to +3 V, Freq. = 500 KHz)	0/+3	-	20	-	mV <sub>P,P</sub>
	0/+5	-	28	-	

### ABSOLUTE MAXIMUM RATINGS<sup>6</sup>

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C
Control Voltage	+10 V
RF Input Power	22 W, 50-2000 MHz 17 W, 2000-3000 MHz

6. Operation of this device above any of these conditions may cause permanent damage.

### TRUTH TABLE


(State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
LOW	HIGH	OFF	ON
HIGH	LOW	ON	OFF
LOW	LOW	N/A	N/A
HIGH	HIGH	N/A	N/A

ON - Low Insertion Loss State

OFF - Isolation State

### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF COM	5	RF Common/SUM Port, Requires DC block (see Fig. 2)
RF1	1	RF Out #1/In Port #1, Requires DC block (see Fig. 2)
RF2	3	RF Out #2/In Port #2, Requires DC block (see Fig. 2)
Control #1 (V <sub>CTL1</sub> )	6	Control IN #1
Control #2 (V <sub>CTL2</sub> )	4	Control IN #2
GND	2	RF DC Ground





## SURFACE MOUNT

# SPDT RF Switch

## VSW2-33-10W+

50Ω 50 to 3000 MHz Reflective RF Switch 10 W  
Positive Control Voltage; +3 V to +5 V

### CHARACTERIZATION TEST CIRCUIT




Figure 1. Block Diagram of Test Circuit Used for Characterization  
(DUT Soldered on Mini-Circuits' TB-530+, Cblock = 1000 pF)

#### Test Equipment:

**For Insertion Loss, Isolation, Return Loss and DC Current:**

Agilent's N5230A Network Analyzer, E3631A power supply.

**For Switching Time and DC Current:**

Agilent's 54832B oscilloscope, 81110A pulse generator and E3631A power supply.

For Input IP3:

Agilent's E8257D signal generators, E4418B power meter, N9020A Signal analyzer and E3631A power supply.

**For Compression:**

LZY-1+/LZY-2+/ZHL-900A-10W/ZHL-16W-43+ amplifier as driver amplifier at RF Common.

Agilent's N5230A Network Analyzer, E3631A power supply

#### Conditions:


Control = 0 and +3 V/+5 V

**For Insertion Loss, Isolation and Return Loss:**  $P_{IN} = 0$  dBm

**For Input IP3:**  $P_{IN} = +5$  dBm/tone

**For Switching Time:** RF frequency: 500 MHz at 0 dBm, Control Frequency: 100 KHz and 0 and +3 V/+5 V


### RECOMMENDED APPLICATION CIRCUIT



Frequency (MHz)	Cblock (Suggested Value)
50-3000	1000 pF

Figure 2. Evaluation board includes case, connectors, and components soldered to PCB.

### PRODUCT MARKING



Marking may contain other features or characters for internal lot control.





**SURFACE MOUNT**

# SPDT RF Switch

## VSW2-33-10W+

50Ω 50 to 3000 MHz Reflective RF Switch 10 W  
Positive Control Voltage; +3 V to +5 V

**ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS [CLICK HERE](#)**

Performance Data	Data Table Swept Graphs
Case Style	JZ1436 Plastic package, Lead Finish: Matte Tin
Tape & Reel	F93
Standard Quantities Available on Reel	7" Reels with 20, 50, 100, 200, 500, or 1000 devices 13" Reels with 3000 devices
Suggested Layout for PCB Design	PL-324
Evaluation Board	TB-530+
Environmental Ratings	ENV41

### ESD RATING


Human Body Model (HBM): Class 1A (250 to < 500 V) in accordance with JESD22-A114

Machine Model (MM): Class A (Passes 150 V) in accordance with JESD22-A115

### MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

### MSL TEST FLOW CHART



#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Typical Performance Data

RF FREQ (MHz)	INSERTION LOSS @ Vctl=+3V OVER TEMPERATURE						RF FREQ (MHz)	ISOLATION @ Vctl=+3V OVER TEMPERATURE											
	RF COM-RF1 (dB)			RF COM-RF2 (dB)				RF COM-RF1 (dB)			RF COM-RF2 (dB)			RF1-RF2 (dB)			RF1-RF2 (dB)		
														ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C		-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	0.28	0.32	0.35	0.27	0.31	0.34	5.0	49.67	50.02	50.18	49.67	50.05	50.18	50.04	50.34	50.57	49.91	50.40	50.64
7.0	0.29	0.33	0.37	0.28	0.32	0.36	7.0	48.42	48.89	49.16	48.52	49.05	49.18	48.91	49.49	49.71	48.83	49.39	49.71
10.0	0.30	0.34	0.38	0.29	0.33	0.37	10.0	46.29	47.19	47.65	46.33	47.13	47.62	46.83	47.61	48.16	46.70	47.69	48.22
50.0	0.30	0.35	0.39	0.30	0.35	0.40	50.0	41.27	42.16	42.73	41.36	42.19	42.78	41.79	42.71	43.36	41.68	42.65	43.32
100.0	0.30	0.36	0.40	0.30	0.36	0.40	100.0	39.03	39.83	40.35	39.09	39.84	40.38	39.49	40.33	40.93	39.44	40.29	40.90
200.0	0.30	0.36	0.41	0.30	0.36	0.41	200.0	36.43	37.11	37.42	36.54	37.12	37.44	36.90	37.58	37.93	36.77	37.52	37.91
300.0	0.30	0.37	0.42	0.29	0.36	0.42	300.0	34.60	35.07	35.17	34.62	35.05	35.13	35.01	35.47	35.64	34.90	35.44	35.63
400.0	0.30	0.37	0.43	0.29	0.37	0.43	400.0	33.00	33.33	33.30	32.97	33.27	33.24	33.37	33.68	33.73	33.28	33.67	33.70
500.0	0.30	0.38	0.45	0.29	0.38	0.44	500.0	31.64	31.81	31.74	31.61	31.76	31.68	31.95	32.16	32.14	31.92	32.13	32.10
600.0	0.32	0.40	0.47	0.29	0.38	0.45	600.0	30.47	30.50	30.42	30.41	30.44	30.34	30.69	30.81	30.76	30.73	30.80	30.76
700.0	0.30	0.40	0.48	0.29	0.39	0.47	700.0	29.33	29.34	29.22	29.28	29.29	29.16	29.56	29.65	29.58	29.60	29.66	29.60
800.0	0.30	0.41	0.48	0.29	0.40	0.47	800.0	28.29	28.35	28.21	28.23	28.28	28.14	28.55	28.65	28.55	28.55	28.66	28.58
900.0	0.34	0.43	0.50	0.32	0.42	0.49	900.0	27.44	27.48	27.34	27.38	27.42	27.27	27.73	27.79	27.69	27.71	27.81	27.71
1000.0	0.33	0.44	0.52	0.31	0.43	0.51	1000.0	26.66	26.67	26.54	26.60	26.61	26.49	26.93	26.99	26.90	26.98	27.03	26.95
1100.0	0.34	0.45	0.54	0.32	0.44	0.53	1100.0	25.95	25.94	25.83	25.87	25.87	25.76	26.19	26.25	26.17	26.27	26.36	26.26
1200.0	0.34	0.46	0.55	0.33	0.45	0.54	1200.0	25.22	25.23	25.11	25.22	25.27	25.12	25.55	25.64	25.53	25.61	25.66	25.56
1300.0	0.35	0.47	0.57	0.33	0.46	0.56	1300.0	24.74	24.71	24.60	24.71	24.70	24.58	25.02	25.07	25.00	25.08	25.11	25.04
1400.0	0.36	0.49	0.58	0.34	0.48	0.57	1400.0	24.23	24.19	24.08	24.19	24.17	24.05	24.48	24.55	24.47	24.59	24.60	24.54
1500.0	0.37	0.50	0.60	0.36	0.49	0.58	1500.0	23.71	23.71	23.60	23.67	23.69	23.57	24.01	24.09	24.00	24.09	24.13	24.05
1600.0	0.38	0.52	0.62	0.36	0.50	0.60	1600.0	23.24	23.28	23.15	23.17	23.25	23.08	23.56	23.65	23.53	23.60	23.69	23.61
1700.0	0.39	0.52	0.63	0.36	0.51	0.61	1700.0	22.83	22.86	22.73	22.78	22.83	22.69	23.22	23.27	23.17	23.21	23.29	23.20
1800.0	0.40	0.53	0.64	0.36	0.52	0.62	1800.0	22.51	22.49	22.36	22.44	22.45	22.31	22.86	22.90	22.79	22.92	22.93	22.84
1900.0	0.39	0.54	0.65	0.37	0.52	0.63	1900.0	22.13	22.10	21.98	22.09	22.09	21.95	22.48	22.54	22.44	22.54	22.55	22.47
2000.0	0.39	0.54	0.66	0.37	0.53	0.64	2000.0	21.78	21.76	21.63	21.74	21.75	21.59	22.16	22.21	22.11	22.20	22.23	22.13
2100.0	0.40	0.55	0.67	0.38	0.54	0.65	2100.0	21.45	21.44	21.31	21.39	21.41	21.26	21.82	21.87	21.77	21.89	21.93	21.82
2200.0	0.40	0.56	0.68	0.39	0.55	0.67	2200.0	21.14	21.15	21.00	21.07	21.10	20.95	21.54	21.59	21.48	21.59	21.64	21.52
2300.0	0.41	0.57	0.69	0.39	0.56	0.68	2300.0	20.81	20.84	20.67	20.77	20.82	20.64	21.26	21.31	21.18	21.27	21.33	21.20
2400.0	0.40	0.56	0.69	0.39	0.56	0.68	2400.0	20.49	20.51	20.35	20.45	20.49	20.31	20.93	20.98	20.86	20.97	21.04	20.91
2500.0	0.41	0.56	0.70	0.39	0.56	0.69	2500.0	20.25	20.21	20.05	20.20	20.20	20.02	20.65	20.69	20.59	20.74	20.76	20.65
3000.0	0.41	0.58	0.73	0.39	0.58	0.73	3000.0	18.80	18.81	18.64	18.76	18.79	18.62	19.36	19.38	19.24	19.34	19.40	19.28
3500.0	0.43	0.62	0.78	0.40	0.60	0.76	3500.0	17.16	17.15	17.03	17.11	17.14	17.00	17.68	17.71	17.61	17.77	17.79	17.70
4000.0	0.48	0.67	0.84	0.44	0.65	0.82	4000.0	15.68	15.65	15.56	15.58	15.59	15.49	15.93	16.04	15.97	16.10	16.14	16.09
4500.0	0.57	0.75	0.94	0.51	0.73	0.91	4500.0	14.19	14.20	14.16	14.11	14.15	14.10	14.32	14.48	14.44	14.50	14.59	14.57
5000.0	0.70	0.88	1.09	0.63	0.85	1.04	5000.0	13.15	13.20	13.18	13.05	13.13	13.10	13.27	13.34	13.33	13.46	13.49	13.49
5500.0	0.87	1.07	1.30	0.83	1.05	1.27	5500.0	12.58	12.64	12.60	12.46	12.56	12.52	12.62	12.67	12.64	12.84	12.86	12.82
6000.0	1.03	1.26	1.51	1.02	1.28	1.51	6000.0	12.31	12.34	12.36	12.21	12.29	12.30	12.33	12.36	12.39	12.48	12.50	12.53
6500.0	1.15	1.40	1.68	1.10	1.40	1.67	6500.0	12.13	12.18	12.23	12.01	12.12	12.16	12.16	12.23	12.25	12.19	12.23	12.27
7000.0	1.18	1.43	1.74	1.14	1.44	1.72	7000.0	11.78	11.89	11.96	11.64	11.82	11.88	11.89	12.09	12.16	11.82	12.02	12.11
7500.0	1.26	1.48	1.76	1.16	1.42	1.71	7500.0	11.37	11.50	11.62	11.19	11.39	11.49	11.42	11.70	11.89	11.35	11.61	11.80
8000.0	1.33	1.53	1.84	1.22	1.45	1.74	8000.0	10.98	11.05	11.18	10.77	10.93	11.02	11.02	11.16	11.26	10.99	11.12	11.26

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	RETURN LOSS @ Vctl=+3V OVER TEMPERATURE (dB)											
	RF COM			RF COM			RF1			RF2		
	ON1			ON2			ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	5.5	5.6	5.6	5.6	5.6	5.6	5.5	5.6	5.6	5.6	5.6	5.6
7.0	7.8	7.8	7.9	7.8	7.9	7.9	7.8	7.8	7.9	7.8	7.9	7.9
10.0	10.5	10.6	10.6	10.5	10.6	10.6	10.5	10.6	10.6	10.5	10.6	10.6
50.0	23.0	23.3	23.3	23.1	23.3	23.3	23.0	23.3	23.2	23.1	23.3	23.3
100.0	27.1	27.0	26.9	27.2	27.1	27.0	27.2	27.1	26.4	27.4	27.1	26.7
200.0	30.7	28.0	27.5	30.0	28.3	27.4	30.1	28.3	27.3	29.5	28.2	27.3
300.0	29.3	27.2	25.9	29.2	27.7	26.1	30.9	27.7	27.4	28.8	27.5	26.7
400.0	26.6	26.3	24.8	28.1	26.7	25.4	28.1	26.6	26.1	27.8	26.5	25.5
500.0	25.1	25.3	24.0	26.7	25.6	24.7	25.4	25.7	24.3	26.7	25.6	24.3
600.0	24.4	23.8	22.8	25.3	24.4	23.5	24.1	24.2	23.0	25.4	24.5	23.5
700.0	24.6	22.9	22.1	24.4	23.3	22.4	24.7	23.3	22.6	24.7	23.7	23.0
800.0	23.0	21.6	20.9	23.1	22.0	21.1	23.8	22.2	21.5	23.7	22.7	21.9
900.0	20.8	20.4	19.8	21.3	20.7	20.1	21.7	21.1	20.5	22.0	21.6	20.9
1000.0	20.0	19.7	19.3	20.6	20.0	19.5	20.8	20.5	20.0	21.4	21.0	20.4
1100.0	19.5	19.1	18.8	19.9	19.4	19.0	20.2	20.0	19.6	20.7	20.3	20.0
1200.0	18.7	18.6	18.3	19.1	18.8	18.5	19.5	19.5	19.2	19.9	19.7	19.5
1300.0	18.3	18.2	17.9	18.7	18.4	18.1	19.1	19.2	18.9	19.5	19.3	19.1
1400.0	18.2	17.8	17.7	18.2	18.0	17.8	19.0	18.8	18.7	19.0	18.9	18.8
1500.0	18.0	17.5	17.5	17.7	17.6	17.5	19.0	18.5	18.5	18.5	18.6	18.5
1600.0	17.4	17.2	17.1	17.5	17.3	17.3	18.4	18.2	18.3	18.3	18.4	18.4
1700.0	16.7	17.0	17.0	17.2	17.2	17.2	17.6	18.1	18.1	18.1	18.3	18.4
1800.0	16.7	16.9	16.9	17.2	17.1	17.1	17.4	17.9	18.0	18.1	18.3	18.3
1900.0	16.9	16.9	16.9	17.2	17.1	17.1	17.7	18.0	18.2	18.1	18.3	18.4
2000.0	17.0	17.0	17.1	17.2	17.1	17.2	17.9	18.1	18.3	18.1	18.3	18.5
2100.0	17.2	17.1	17.1	17.3	17.2	17.3	18.1	18.2	18.4	18.3	18.5	18.7
2200.0	17.2	17.1	17.2	17.3	17.3	17.3	18.2	18.4	18.6	18.2	18.5	18.8
2300.0	17.4	17.4	17.5	17.4	17.4	17.5	18.5	18.7	19.2	18.5	18.8	19.2
2400.0	17.6	17.8	17.8	17.9	17.9	17.9	18.7	19.3	19.5	19.0	19.4	19.7
2500.0	17.9	18.4	18.2	18.4	18.4	18.3	19.0	19.9	20.0	19.6	20.1	20.5
3000.0	22.0	22.0	21.6	23.1	22.3	21.9	24.6	25.7	25.8	26.3	26.4	26.6
3500.0	30.1	28.5	26.8	28.9	27.4	26.1	34.2	38.5	38.0	31.3	34.3	36.5
4000.0	33.6	33.2	29.8	36.2	33.0	29.6	40.0	37.6	38.6	32.5	34.2	35.1
4500.0	21.9	23.0	22.3	23.6	23.5	22.8	26.6	27.4	27.0	27.2	27.1	27.1
5000.0	16.1	16.6	16.4	16.5	16.6	16.4	18.0	18.9	18.8	17.9	18.4	18.2
5500.0	13.1	13.1	12.9	12.7	12.9	12.7	14.9	15.0	15.0	14.0	14.5	14.4
6000.0	11.6	11.3	11.2	10.9	10.8	10.8	13.5	13.2	13.2	11.9	12.1	12.1
6500.0	10.7	10.4	10.2	10.2	10.1	9.9	12.3	12.2	12.1	11.6	11.6	11.5
7000.0	10.8	10.5	10.4	10.5	10.3	10.4	12.5	12.3	12.3	11.9	11.8	11.9
7500.0	10.8	11.0	11.3	10.9	11.3	11.5	13.0	13.1	13.5	13.0	13.3	13.6
8000.0	11.5	11.9	12.2	11.6	12.3	12.6	13.8	14.1	14.7	13.6	14.6	15.2

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	INSERTION LOSS @ Vctl=+5V OVER TEMPERATURE						RF FREQ (MHz)	ISOLATION @ Vctl=+5V OVER TEMPERATURE											
	RF COM-RF1 (dB)			RF COM-RF2 (dB)				RF COM-RF1 (dB)			RF COM-RF2 (dB)			RF1-RF2 (dB)			RF1-RF2 (dB)		
														ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C		-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	0.32	0.35	0.38	0.25	0.28	0.31	5.0	49.48	49.30	48.97	49.32	49.30	49.08	51.20	51.22	51.12	51.11	51.13	50.82
7.0	0.31	0.35	0.38	0.27	0.30	0.34	7.0	47.71	47.97	48.01	47.65	48.00	48.03	48.85	49.27	49.42	48.86	49.20	49.36
10.0	0.30	0.34	0.38	0.28	0.32	0.36	10.0	46.24	46.73	47.02	46.20	46.69	47.18	47.11	47.60	48.01	47.04	47.65	48.03
50.0	0.30	0.35	0.39	0.30	0.35	0.39	50.0	40.82	41.57	42.17	40.85	41.60	42.25	41.26	42.11	42.82	41.26	42.09	42.76
100.0	0.30	0.35	0.39	0.30	0.35	0.40	100.0	38.48	39.21	39.81	38.52	39.23	39.86	38.93	39.71	40.39	38.88	39.70	40.34
200.0	0.29	0.35	0.40	0.30	0.36	0.40	200.0	36.06	36.64	36.99	36.09	36.65	37.06	36.50	37.12	37.58	36.46	37.10	37.52
300.0	0.29	0.35	0.41	0.30	0.36	0.41	300.0	34.25	34.64	34.80	34.29	34.68	34.90	34.66	35.13	35.41	34.63	35.09	35.31
400.0	0.29	0.36	0.42	0.29	0.36	0.42	400.0	32.65	32.90	32.94	32.67	32.94	33.05	33.07	33.38	33.55	33.05	33.35	33.43
500.0	0.29	0.36	0.43	0.29	0.36	0.43	500.0	31.25	31.40	31.35	31.27	31.44	31.48	31.66	31.86	31.94	31.65	31.84	31.83
600.0	0.30	0.37	0.44	0.29	0.37	0.43	600.0	29.99	30.06	29.96	30.00	30.11	30.09	30.40	30.53	30.56	30.40	30.52	30.47
700.0	0.28	0.37	0.45	0.29	0.37	0.45	700.0	28.85	28.87	28.73	28.87	28.92	28.88	29.25	29.35	29.36	29.26	29.34	29.26
800.0	0.29	0.38	0.45	0.30	0.39	0.45	800.0	27.77	27.80	27.66	27.80	27.86	27.80	28.22	28.31	28.31	28.24	28.30	28.21
900.0	0.32	0.40	0.47	0.31	0.39	0.46	900.0	26.93	26.94	26.79	26.94	26.98	26.93	27.35	27.43	27.41	27.37	27.42	27.31
1000.0	0.30	0.40	0.48	0.30	0.40	0.48	1000.0	26.12	26.12	25.97	26.14	26.17	26.11	26.53	26.60	26.59	26.56	26.59	26.49
1100.0	0.30	0.41	0.49	0.30	0.41	0.49	1100.0	25.38	25.37	25.21	25.40	25.42	25.35	25.78	25.83	25.81	25.81	25.82	25.70
1200.0	0.31	0.42	0.51	0.31	0.42	0.51	1200.0	24.65	24.65	24.49	24.68	24.71	24.64	25.07	25.14	25.12	25.10	25.13	25.01
1300.0	0.31	0.43	0.52	0.32	0.43	0.52	1300.0	24.01	24.02	23.87	24.04	24.09	24.03	24.45	24.53	24.52	24.47	24.51	24.41
1400.0	0.33	0.44	0.53	0.33	0.45	0.53	1400.0	23.46	23.46	23.32	23.49	23.53	23.47	23.92	23.99	23.97	23.94	23.97	23.86
1500.0	0.34	0.45	0.55	0.34	0.46	0.55	1500.0	22.99	22.97	22.81	23.02	23.04	22.97	23.44	23.50	23.47	23.47	23.49	23.36
1600.0	0.35	0.47	0.56	0.35	0.47	0.56	1600.0	22.51	22.49	22.32	22.53	22.55	22.47	22.99	23.04	23.01	23.01	23.03	22.91
1700.0	0.35	0.48	0.58	0.35	0.48	0.58	1700.0	22.03	22.02	21.85	22.05	22.08	22.01	22.50	22.57	22.54	22.52	22.56	22.45
1800.0	0.36	0.49	0.59	0.36	0.49	0.59	1800.0	21.60	21.58	21.42	21.62	21.65	21.58	22.08	22.15	22.12	22.11	22.15	22.03
1900.0	0.36	0.50	0.60	0.37	0.50	0.61	1900.0	21.23	21.21	21.03	21.25	21.27	21.19	21.74	21.78	21.76	21.75	21.77	21.64
2000.0	0.36	0.50	0.61	0.37	0.51	0.62	2000.0	20.85	20.83	20.65	20.88	20.90	20.81	21.38	21.42	21.38	21.39	21.39	21.26
2100.0	0.37	0.51	0.62	0.37	0.52	0.63	2100.0	20.46	20.44	20.26	20.49	20.52	20.43	21.00	21.05	21.01	21.00	21.02	20.90
2200.0	0.37	0.52	0.63	0.38	0.52	0.64	2200.0	20.10	20.08	19.90	20.12	20.15	20.06	20.64	20.70	20.66	20.64	20.67	20.54
2300.0	0.38	0.53	0.64	0.39	0.54	0.65	2300.0	19.75	19.74	19.55	19.79	19.81	19.71	20.31	20.36	20.30	20.32	20.32	20.17
2400.0	0.38	0.54	0.66	0.39	0.54	0.67	2400.0	19.45	19.45	19.25	19.48	19.53	19.42	20.01	20.05	19.99	20.02	20.02	19.86
2500.0	0.39	0.54	0.67	0.40	0.55	0.68	2500.0	19.18	19.17	18.98	19.22	19.25	19.13	19.71	19.77	19.71	19.71	19.73	19.59
3000.0	0.40	0.58	0.72	0.42	0.60	0.74	3000.0	17.67	17.64	17.45	17.71	17.72	17.62	18.26	18.29	18.22	18.25	18.25	18.10
3500.0	0.45	0.64	0.80	0.47	0.66	0.81	3500.0	16.03	16.03	15.89	16.08	16.13	16.09	16.63	16.73	16.75	16.54	16.61	16.53
4000.0	0.53	0.73	0.90	0.54	0.75	0.92	4000.0	14.57	14.64	14.53	14.59	14.71	14.70	15.08	15.25	15.31	15.01	15.10	15.05
4500.0	0.65	0.86	1.04	0.65	0.87	1.05	4500.0	13.30	13.39	13.32	13.36	13.50	13.49	13.85	13.98	13.98	13.78	13.84	13.77
5000.0	0.83	1.06	1.25	0.82	1.05	1.24	5000.0	12.44	12.54	12.47	12.48	12.63	12.65	12.81	12.93	13.00	12.84	12.91	12.85
5500.0	1.02	1.29	1.50	1.01	1.28	1.50	5500.0	11.96	12.09	12.02	12.01	12.18	12.20	12.38	12.49	12.52	12.37	12.46	12.45
6000.0	1.19	1.49	1.72	1.18	1.48	1.72	6000.0	11.61	11.74	11.68	11.66	11.83	11.85	12.14	12.30	12.34	12.14	12.29	12.29
6500.0	1.29	1.58	1.82	1.24	1.55	1.82	6500.0	11.27	11.41	11.37	11.31	11.49	11.54	11.82	12.04	12.16	11.85	12.04	12.11
7000.0	1.37	1.69	1.94	1.31	1.64	1.91	7000.0	10.80	10.98	11.00	10.85	11.07	11.16	11.44	11.74	11.89	11.59	11.85	11.92
7500.0	1.42	1.75	2.02	1.40	1.75	2.04	7500.0	10.26	10.53	10.62	10.32	10.61	10.78	11.00	11.19	11.36	11.28	11.40	11.47
8000.0	1.48	1.81	2.11	1.56	1.88	2.19	8000.0	10.07	10.32	10.48	10.15	10.43	10.66	10.68	10.93	11.15	10.94	11.16	11.28

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	RETURN LOSS @ Vctl=+5V OVER TEMPERATURE (dB)											
	RF COM			RF COM			RF1			RF2		
	ON1			ON2			ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	5.5	5.5	5.5	5.6	5.7	5.7	5.5	5.5	5.5	5.7	5.7	5.7
7.0	7.7	7.8	7.8	7.9	8.0	8.0	7.7	7.8	7.8	7.9	8.0	8.0
10.0	10.4	10.5	10.5	10.6	10.7	10.7	10.4	10.5	10.5	10.7	10.7	10.8
50.0	23.3	23.5	23.6	23.6	23.8	23.8	23.4	23.6	23.5	23.7	23.8	23.8
100.0	27.8	27.8	27.6	28.2	28.2	27.9	28.2	27.8	27.2	28.6	28.2	27.5
200.0	31.5	29.7	28.4	32.1	30.1	28.7	32.0	30.0	28.5	32.6	30.5	29.1
300.0	32.0	29.6	27.8	33.0	30.1	27.9	32.1	30.3	28.9	33.0	31.1	29.6
400.0	30.8	29.2	27.8	31.6	29.8	28.1	32.0	30.0	28.3	33.3	31.0	29.2
500.0	30.6	29.1	27.9	30.9	29.2	27.9	31.5	29.2	27.3	32.9	30.4	28.3
600.0	29.5	28.0	26.7	30.3	28.4	26.8	29.4	27.9	26.5	31.3	29.5	27.9
700.0	29.4	27.8	26.4	29.7	27.8	26.1	28.6	27.2	26.0	30.2	28.5	27.1
800.0	28.0	26.3	25.1	27.8	26.0	24.7	27.4	25.7	24.5	28.4	26.4	25.1
900.0	25.5	24.6	23.8	25.7	24.5	23.6	25.4	24.4	23.5	26.0	24.9	23.9
1000.0	24.9	24.3	23.6	24.9	24.2	23.4	24.8	24.1	23.5	25.2	24.5	23.7
1100.0	24.5	23.8	23.3	24.4	23.7	23.1	24.6	23.7	23.1	24.8	23.9	23.3
1200.0	23.9	23.0	22.4	23.8	22.9	22.1	24.2	23.3	22.6	24.3	23.5	22.8
1300.0	22.8	22.2	21.8	22.7	22.1	21.5	23.3	22.8	22.3	23.3	22.9	22.4
1400.0	21.7	21.5	21.3	21.6	21.3	21.1	22.5	22.2	21.9	22.5	22.2	21.9
1500.0	21.2	21.0	20.7	20.9	20.7	20.5	22.1	21.8	21.5	21.9	21.7	21.5
1600.0	21.0	20.7	20.5	20.8	20.5	20.2	22.1	21.7	21.4	21.6	21.5	21.4
1700.0	20.6	20.4	20.3	20.4	20.1	19.9	21.7	21.5	21.3	21.2	21.1	21.0
1800.0	19.9	20.0	20.1	19.6	19.6	19.5	20.9	21.0	21.0	20.4	20.5	20.5
1900.0	19.6	19.8	19.9	19.2	19.3	19.3	20.6	20.7	20.9	20.0	20.1	20.2
2000.0	19.8	19.8	19.9	19.3	19.3	19.4	20.8	20.8	20.9	20.1	20.1	20.3
2100.0	19.9	19.9	19.9	19.5	19.4	19.4	20.9	20.9	21.0	20.2	20.2	20.4
2200.0	19.8	20.0	20.1	19.6	19.7	19.7	20.7	21.0	21.2	20.2	20.4	20.6
2300.0	19.6	19.9	20.2	19.4	19.6	19.8	20.6	20.9	21.2	20.2	20.4	20.7
2400.0	19.9	20.0	20.1	19.6	19.7	19.7	20.9	21.0	21.2	20.4	20.5	20.7
2500.0	20.3	20.3	20.3	20.0	20.0	20.0	21.4	21.5	21.7	20.8	21.0	21.2
3000.0	23.0	22.8	22.6	21.8	21.6	21.3	26.2	25.8	25.5	23.9	23.7	23.4
3500.0	23.7	23.9	23.2	22.6	22.5	21.8	27.8	27.7	27.2	25.9	25.3	24.5
4000.0	20.7	20.7	20.4	20.4	20.3	19.9	24.2	24.4	23.9	24.5	24.2	23.6
4500.0	16.0	16.2	16.2	16.2	16.5	16.5	18.1	18.5	18.4	18.9	19.3	19.3
5000.0	12.6	12.7	12.5	13.0	13.1	12.9	14.1	14.2	14.2	14.6	14.9	15.0
5500.0	10.5	10.5	10.4	10.7	10.7	10.6	11.9	11.9	11.9	12.1	12.3	12.3
6000.0	9.3	9.3	9.4	9.5	9.5	9.5	10.6	10.6	10.7	10.9	11.0	11.1
6500.0	9.1	9.3	9.4	9.4	9.6	9.5	10.4	10.7	10.9	10.9	11.2	11.3
7000.0	9.0	9.3	9.5	9.4	9.6	9.7	10.5	10.8	11.1	11.0	11.2	11.4
7500.0	9.4	9.6	9.8	9.5	9.6	9.7	10.9	11.3	11.6	11.0	11.3	11.6
8000.0	9.5	9.6	9.6	9.1	9.3	9.3	11.3	11.6	11.8	10.5	10.9	11.2

**Truth Table** (State of control voltage selects the desired switch state)







State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	INPUT IP3	
	Vctl=+3V (dBm)	Vctl =+5V (dBm)
	RF COM-RF1	RF COM-RF1
100.0	59.54	60.57
300.0	57.79	58.53
500.0	56.49	57.90
700.0	57.57	60.31
900.0	56.93	62.42
1000.0	59.52	59.07
1200.0	58.70	59.40
1400.0	57.70	58.88
1600.0	55.80	56.80
1800.0	55.24	57.85
2000.0	56.81	58.06
2250.0	59.39	59.21
2500.0	55.98	58.40
2750.0	58.24	57.03
3000.0	54.39	57.43
3250.0	54.20	56.44
3500.0	53.27	54.28
3750.0	53.06	54.66
4000.0	55.09	55.02

## Typical Performance Curves




**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended


ON- low insertion loss state OFF- Isolation State

## Typical Performance Curves


Insertion Loss @ Vctl=+3V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+3V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+3V over Temperature,  
RF1-RF2



Return Loss @ Vctl=+3V over Temperature  
RF COM



Return Loss @ Vctl=+3V over Temperature  
RF1(ON1) & RF2 (ON2)




**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended


ON- low insertion loss state OFF- Isolation State

## Typical Performance Curves


Insertion Loss @ Vctl=+5V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+5V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+5V over Temperature,  
RF1-RF2



Return Loss @ Vctl=+5V over Temperature  
RF COM



Return Loss @ Vctl=+5V over Temperature  
RF1(ON1) & RF2 (ON2)




Truth Table (State of control voltage selects the desired switch state)


State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
JZ1436	.118 (3.00)	.079 (2.00)	.035 (.89)	.048 (1.22)	.024 (.61)	.033 (.84)	.024 (.61)	.015 (.38)	.013 (.33)	.037 (.94)	.104 (2.64)	.144 (3.66)	.048 (1.22)

CASE#	P	Q	R	S	T	WT, GRAM
JZ1436	.014 (.36)	.024 (.61)	.033 (.84)	.009 (.23)	.005 (.125)	.015


Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Matte Tin plate.

# Tape & Reel Packaging TR-F93

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
12	4	7	20
			50
			100
			200
			500
		1000	
		13	3000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M125849	NEW RELEASE	01/05/10	MMG	RD


**SUGGESTED MOUNTING CONFIGURATION FOR  
JZ1436 CASE STYLE, "06SW01" PIN CODE**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN MMG	12/23/09
TOLERANCES ON:	CHECKED AV	01/04/10
2 PL DECIMALS ±	APPROVED RD	01/05/10
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



**Mini-Circuits®**



13 Neptune Avenue  
Brooklyn NY 11235

**PL, 06SW01, JZ1436, TB-530+**

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-324	OR
FILE:	98PL324	SCALE:	10:1
		SHEET:	1 OF 1

# Evaluation Board and Circuit




COMPONENT	VALUE/PART NUMBER
DUT	Mini-Circuits VSW2-33-10W+
C1 - C5	0.001 uF

Schematic Diagram

**Notes:**

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Temperature Cycling	-65° to 150°C, 500 cycles	JESD22-A104, condition C
Autoclave	121°C, 100% RH, 30 PSIA, 96 hours, unbiased	JESD22-A102
High Temp Storage	150°C 1008 hours	JESD22-A103
Solderability	Per Reference Spec	JESD22-B102
Resistance to Solvent	Per Reference Spec	MIL-STD-202, Method 215J
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	JESD22-A113