



USB & DAISY-CHAIN

Solid-State Switch

USB-4SP2T-852H



50Ω 10 to 8500 MHz 4 x SPDT SMA Female

THE BIG DEAL

- 4 x Solid-State SPDT Absorptive Switches
- High-Speed Switch Transition, 5 μ s
- Very High Isolation, 60 dB
- High Power Handling, +30 dBm max
- Daisy-Chain Control of up to 35 modules

APPLICATIONS

- High Volume Production Testing / ATE
- 5G FR1, WiFi 6E, Bluetooth Testing
- Design Verification Testing
- RF Signal Routing / Switch Matrices



Generic photo used for illustration purposes only

PRODUCT OVERVIEW

Mini-Circuits' USB-4SP2T-852H is a low cost, USB controlled solid state matrix containing four independent SPDT RF switches. Each fast switching absorptive switch operates from 10 MHz to 8500 MHz with 5 μ s typical switch transition speed. High linearity (+50 dBm typ IP3) and high isolation (60 dB typical) allows the model to be used for a wide variety of RF applications.

The USB-4SP2T-852H is housed in a compact, low profile, rugged metal case (8.4 × 2.00 × 0.475") with 12 SMA (F) connectors (COM, 1 & 2 for each switch), a USB Mini-B port for power and control, and two data bus connectors for Master / Slave connections to other modules.

Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

KEY FEATURES

Feature	Advantages
Four RF SPDT Absorptive Switches	Wideband (10 to 8500 MHz) with low insertion loss (3 dB typ.), high isolation (60 dB typ), and high power rating (+30 dBm through path).
High Linearity (IP3 +50 dBm typ.)	Excellent intermodulation performance, meeting requirements for digital communications signals.
Internal DC Blocking Capacitors	No need for external DC blocking circuitry.
Dynamic Daisy-Chain Control	Simplify control software and interconnections by cascading up to 35 modules of multiple switch types into a Master / Slave chain with a single USB interface.
Full Software Support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box while the comprehensive API (application programming interface), with examples and instructions, allows easy automation in most programming environments.

Trademarks:

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.





USB & DAISY-CHAIN

Solid-State Switch

USB-4SP2T-852H

Mini-Circuits

50Ω 10 to 8500 MHz 4 x SPDT SMA Female

ELECTRICAL SPECIFICATIONS AT -10 TO +60°C

Parameter	Ports	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	–	–	10	–	8500	MHz
Insertion Loss	COM to any active port	10 - 700	–	1.6	2.8	dB
		700 - 2500	–	2.0	3.2	
		2500 - 5000	–	2.8	4.0	
		5000 - 6000	–	3.0	4.2	
		6000 - 7200	–	3.0	4.5	
		7200 - 8000	–	3.4	4.8	
		8000 - 8500	–	3.6	5.0	
Isolation	Between ports 1 to 2 (of any given switch)	10 - 700	82	100	–	dB
		700 - 2500	67	82	–	
		2500 - 5000	55	65	–	
		5000 - 6000	50	61	–	
		6000 - 8500	45	52	–	
	COM to any terminated port (of any given switch)	10 - 700	85	100	–	
		700 - 2500	70	85	–	
		2500 - 5000	58	70	–	
		5000 - 6000	52	63	–	
		6000 - 8500	45	54	–	
	Crosstalk between switches	10 - 8500	65	100	–	
Return Loss	COM port	10 - 6000	–	19.0	–	dB
		6000 - 7200	–	18.0	–	
		7200 - 8000	–	15.0	–	
		8000 - 8500	–	12.5	–	
	Any port connected to COM	10 - 6000	–	19.0	–	
		6000 - 7200	–	18.0	–	
		7200 - 8000	–	15.0	–	
		8000 - 8500	–	12.5	–	
	Any terminated port	10 - 2500	–	23.0	–	
		2500 - 5000	–	21.0	–	
		5000 - 6000	–	18.0	–	
		6000 - 7200	–	18.0	–	
		7200 - 8000	–	17.0	–	
		8000 - 8500	–	13.0	–	





ELECTRICAL SPECIFICATIONS AT -10 TO +60°C (CONTINUED)

Parameter	Ports	Condition (MHz)		Min.	Typ.	Max.	Unit
Power Input at 1 dB compression ^{1,2}	COM to any active port	100 - 8500		-	+38	-	dBm
Input IP3 ^{2,3}	COM to any active port	100 - 8500		-	+50	-	dBm
Transition Time ⁴	-	-		-	200	300	ns
Minimum Dwell Time ⁵	High-speed mode	-		-	25	-	μs
Switching Time (USB) ⁶	-	-		-	2	-	ms
Supply Voltage (Vcc)	USB port	-		4.75	5	5.25	V _{DC}
Supply Current (Icc)		-		-	55	85	mA
Current Pass-Through ⁸	-	-		-	-	500	mA
Operating RF Input Power ⁷	Per port (COM & 1 - 2)	Hot switching	10 - 8500	-	-	+24	dBm
	Total on any through path (bi-directional)	Cold switching	10 - 40	-	-	Note 1	
			40 - 6000	-	-	+30	
			6000-8500	-	-	+29	
	Per terminated port (1 - 2)	Into internal termination	10 - 8500	-	-	+24	

1. Max power at through path derates linearly from +30 dBm @ 40 MHz to +25 dBm @ 10 MHz.

2. Compression and IP3 may degrade below 100 MHz.

3. IP3 tested with 1 MHz span between signals, +5 dBm per tone.

4. Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

5. Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

6. Switching time(USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

7. The switch can tolerate the max cold switching power on the active path simultaneously with the max internal termination power on every terminated port.

8. Pass-Through current is the maximum current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. Refer to "Connecting Multiple Modules" section for more details.

ABSOLUTE MAXIMUM RATINGS ⁸

Operating Temperature	-10°C to +60°C
Storage Temperature	-20°C to +85°C
DC Supply Voltage max at USB and pin #6 of D-Sub	6 V
DC Voltage at RF Ports	16 V

8. Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.



USB & DAISY-CHAIN

Solid-State Switch


USB-4SP2T-852H

Mini-Circuits


50Ω 10 to 8500 MHz 4 x SPDT SMA Female

TYPICAL PERFORMANCE GRAPHS


Insertion Loss over Temperature (1 Active)




Insertion Loss 1 - 2 Active




Isolation COM to 1 (2 Active)




Isolation COM to 2 (1 Active)



Isolation 1 to 2 (1 Active)



Crosstalk @ Active states



Mini-Circuits



USB & DAISY-CHAIN

Solid-State Switch


USB-4SP2T-852H

Mini-Circuits


50Ω 10 to 8500 MHz 4 x SPDT SMA Female

TYPICAL PERFORMANCE GRAPHS (CONTINUED)


Return Loss @ COM over Temperature (1 Active)




Return Loss @ 1 over Temperature (1 Active)




Return Loss @ 1 over Temperature (1 Terminated)



Return Loss @ 2 over Temperature (2 Active)



Return Loss @ 2 over Temperature (2 Terminated)





CONTROL INTERFACES

USB Control	Supported protocols	HID (Human Interface Device) - Full-speed
	Min communication time ⁹	3 ms typ (full transmit/receive cycle)

9. USB min communication time is based on the polling interval of the USB HID protocol (1 ms polling interval, 64 bytes per packet), medium CPU load and no other high speed USB devices using the USB bus.

SOFTWARE & DOCUMENTATION

Mini-Circuits' full software and support package including user guide, Windows GUI, API, programming manual and examples can be downloaded free of charge (refer to the last page for the download path).

A comprehensive set of software control options is provided:

- GUI for Windows – Simple software interface for control via Ethernet and USB.
- Programming / automation via USB:
 - DLL files provide a full API for Windows with a set of intuitive functions which can be implemented in any programming environment supporting .Net Framework or ActiveX.
 - Direct USB programming is possible in any other environment (not supporting .Net or ActiveX).

Please contact testsolutions@minicircuits.com for support.


MINIMUM SYSTEM REQUIREMENTS

GUI	Windows 7 or later
USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
USB Direct Programming	Linux, Windows 7 or later
Daisy-Chain Dynamic Addressing	An additional Mini-Circuits model supporting dynamic addressing
Hardware	Intel i3 (or equivalent) or later




GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB
- Run GUI in "demo mode" to evaluate software without a hardware connection




- View and set switch states at the click of a button
- Configure and run timed switching sequences





CONNECTING MULTIPLE MODULES (DAISY-CHAIN)

The model is designed to connect up to 35 modules in series (daisy-chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 34 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC acting as the master and all others as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module.


Power will be supplied from the PC via the master module up to a maximum of 500 mA. Additional power supplies should be connected as needed to keep the total current per supply below 500 mA. All power supplies should be connected to the module via the module's USB port. Connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The serial master/slave bus allows connecting modules of different types to the same daisy-chain as long as all support Mini-Circuits' dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Note: Different module types may have different current consumption which will change the number of units which can be connected before an additional power supply is needed. For example, if connecting units with a current consumption of 100 mA each, additional power supply is recommended every sixth module. If using units with current consumption of 50 mA additional power supply is recommended every eleventh module.



BLOCK DIAGRAM



SWITCH STATE TABLE (EACH SWITCH)

State	Switch path
1	COM to 1
2	COM to 2


CONNECTIONS

Port name	Connector type
RF Ports-Switch A (COM, 1 & 2)	SMA female
RF Ports-Switch B (COM, 1 & 2)	SMA female
RF Ports-Switch C (COM, 1 & 2)	SMA female
RF Ports-Switch D (COM, 1 & 2)	SMA female
USB	USB type Mini-B receptacle
Serial In (digital control 2 port)	Digital snap fit connector ¹⁰
Serial Out (digital control 1 port)	Digital snap fit connector ¹⁰

10. Mating connector is Hirose ST40X-10S-CV(30).



CASE STYLE DRAWING (QM2279)



NOTES:

1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions: Inches [mm]. Tolerances 2 Pl. $\pm$.03 inch; 3 Pl. $\pm$.015 inch.
4. Weight: 450 grams
5. Marking may contain other features or characters for internal lot control.



USB & DAISY-CHAIN

Solid-State Switch

USB-4SP2T-852H

50Ω 10 to 8500 MHz 4 x SPDT SMA Female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE [CLICK HERE](#)

Performance Data & Graphs	Data Graphs
Case Style	QM2279
Environmental Rating	ENV55T2
User Guide	https://www.minicircuits.com/softwaredownload/solidstate.html
Regulatory Compliance	Refer to user guide for compliance information  https://www.minicircuits.com/app/AN49-012.pdf
Support	testsolutions@minicircuits.com

INCLUDED ACCESSORIES ¹¹

	Part No.	Description	Qty.
	MUSB-CBL-3+	3.0 ft (0.9 m) USB Cable: USB type A (Male) to USB type Mini-B (Male)	1

11. Additional quantities are available for purchase as optional accessories.

OPTIONAL ACCESSORIES

	Part No.	Description
	MUSB-CBL-7+	6.6 ft (2.0 m) USB Cable: USB type A (Male) to USB type Mini-B (Male)
	CBL-1.5FT-MMD+	1.5 ft (0.45 m) Cable assembly for serial control daisy-chain with snap fit connectors
	USB-AC/DC-5	AC/DC +5V power adaptor with USB connector ^{12, 13}

12. The power adaptor may be used to provide additional power via USB port when connecting several units in daisy-chain control.

13. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed, please contact testsolutions@minicircuits.com

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.

Freq. (MHz)	Insertion Loss (dB)		Isolation, Active states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2
10	-1.27	-1.27	-119.00	-115.09	-100.91
250	-1.42	-1.42	-99.25	-102.60	-98.37
500	-1.48	-1.48	-97.46	-104.14	-94.87
750	-1.54	-1.54	-103.40	-98.68	-98.73
1000	-1.59	-1.59	-95.40	-95.10	-92.64
1250	-1.64	-1.64	-93.24	-93.27	-89.70
1500	-1.68	-1.68	-92.13	-92.39	-87.28
1750	-1.73	-1.73	-88.39	-87.85	-86.14
2000	-1.78	-1.78	-86.91	-85.13	-82.02
2250	-1.82	-1.82	-82.58	-82.38	-78.44
2500	-1.86	-1.86	-80.47	-80.53	-76.72
2750	-1.90	-1.90	-77.23	-75.61	-74.10
3000	-1.93	-1.93	-73.94	-72.95	-70.36
3250	-1.99	-1.99	-70.93	-70.16	-67.13
3500	-2.06	-2.06	-68.95	-68.48	-64.28
3750	-2.15	-2.15	-68.52	-68.87	-63.64
4000	-2.27	-2.27	-69.22	-69.45	-64.02
4250	-2.39	-2.39	-69.80	-69.76	-64.74
4500	-2.50	-2.50	-70.44	-69.88	-64.94
4750	-2.60	-2.60	-69.71	-68.55	-64.98
5000	-2.68	-2.68	-68.86	-67.59	-64.18
5250	-2.73	-2.73	-67.45	-66.11	-63.41
5500	-2.78	-2.78	-65.49	-64.91	-62.07
5750	-2.85	-2.85	-63.13	-63.87	-60.30
6000	-2.93	-2.93	-61.62	-61.19	-58.80
6250	-3.01	-3.01	-59.69	-58.92	-56.66
6500	-3.10	-3.10	-56.86	-55.99	-53.85
6750	-3.20	-3.20	-53.99	-53.03	-51.55
7000	-3.28	-3.28	-52.64	-51.68	-51.15
7250	-3.35	-3.35	-52.70	-52.11	-52.12
7500	-3.40	-3.40	-53.44	-53.15	-53.40
7750	-3.43	-3.43	-54.15	-54.12	-54.47
8000	-3.46	-3.46	-54.66	-54.87	-55.03
8250	-3.45	-3.45	-54.85	-55.58	-55.09
8500	-3.47	-3.47	-54.74	-55.79	-55.06
8750	-3.52	-3.52	-54.67	-56.09	-54.48
9000	-3.62	-3.62	-54.06	-54.94	-53.68
9250	-3.77	-3.77	-53.00	-53.54	-52.79
9500	-4.00	-4.00	-51.56	-51.39	-51.08
9750	-4.33	-4.33	-48.98	-48.21	-49.18
10000	-4.68	-4.68	-45.67	-45.12	-46.30

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.

Freq. (MHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
10	-18.59	-18.56	-18.73	-23.90	-24.31
250	-19.21	-19.18	-19.42	-24.14	-24.65
500	-19.91	-19.50	-19.76	-24.18	-24.62
750	-20.99	-19.51	-20.39	-23.29	-24.52
1000	-22.51	-20.43	-21.45	-22.94	-24.21
1250	-23.68	-21.81	-23.34	-22.37	-24.11
1500	-24.97	-23.92	-25.85	-22.01	-23.77
1750	-25.65	-25.18	-29.16	-21.91	-24.14
2000	-27.92	-24.77	-30.61	-22.06	-24.34
2250	-29.47	-22.35	-27.02	-22.36	-24.03
2500	-29.35	-20.92	-24.96	-23.04	-24.33
2750	-25.73	-19.79	-23.01	-24.06	-24.64
3000	-22.09	-19.88	-21.86	-25.89	-24.76
3250	-19.78	-20.30	-21.24	-27.01	-24.53
3500	-18.08	-20.99	-20.23	-27.53	-23.81
3750	-17.51	-21.81	-20.21	-27.45	-23.60
4000	-17.69	-21.34	-19.63	-25.84	-22.57
4250	-18.59	-20.10	-19.27	-24.01	-21.84
4500	-20.73	-19.34	-19.66	-22.93	-21.50
4750	-22.96	-18.43	-19.86	-21.48	-20.74
5000	-27.40	-18.98	-21.27	-20.46	-20.07
5250	-36.19	-20.19	-23.48	-19.80	-19.97
5500	-31.78	-22.14	-26.29	-19.55	-20.11
5750	-26.55	-23.37	-26.50	-19.51	-20.46
6000	-25.53	-21.64	-23.32	-20.22	-21.14
6250	-27.76	-19.42	-20.87	-21.39	-22.71
6500	-30.20	-17.74	-19.60	-23.14	-25.35
6750	-24.58	-16.55	-18.96	-25.11	-30.33
7000	-19.24	-15.41	-17.99	-26.01	-38.69
7250	-16.05	-14.23	-16.30	-23.53	-28.21
7500	-14.07	-12.97	-14.65	-19.93	-22.35
7750	-13.45	-12.22	-13.49	-17.15	-18.85
8000	-13.86	-12.08	-13.01	-15.00	-16.34
8250	-14.94	-12.62	-13.11	-13.22	-14.38
8500	-16.93	-14.42	-14.33	-11.85	-12.71
8750	-20.05	-18.63	-18.33	-10.59	-11.38
9000	-19.56	-21.54	-26.08	-9.89	-10.55
9250	-16.26	-16.48	-20.79	-9.44	-9.71
9500	-12.74	-12.22	-13.89	-8.94	-8.90
9750	-10.40	-9.77	-10.46	-8.61	-8.38
10000	-8.85	-8.75	-8.80	-8.54	-8.05

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.

Freq. (MHz)	Insertion Loss (dB)		Isolation, Active states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2
10	-1.35	-1.35	-112.26	-106.93	-104.70
250	-1.50	-1.50	-108.33	-103.19	-102.58
500	-1.57	-1.57	-101.79	-95.57	-98.75
750	-1.62	-1.62	-98.02	-98.51	-96.44
1000	-1.68	-1.68	-98.69	-99.81	-92.72
1250	-1.72	-1.72	-93.34	-93.96	-92.33
1500	-1.77	-1.77	-90.75	-93.66	-86.63
1750	-1.81	-1.81	-89.13	-90.24	-84.31
2000	-1.84	-1.84	-86.25	-87.27	-82.80
2250	-1.87	-1.87	-82.84	-84.08	-79.25
2500	-1.91	-1.91	-80.37	-80.35	-77.05
2750	-1.94	-1.94	-77.63	-76.25	-74.98
3000	-1.98	-1.98	-74.92	-74.31	-70.76
3250	-2.04	-2.04	-72.23	-71.71	-67.91
3500	-2.10	-2.10	-69.82	-69.94	-65.26
3750	-2.17	-2.17	-69.16	-69.70	-64.34
4000	-2.24	-2.24	-69.81	-69.76	-64.59
4250	-2.32	-2.32	-70.56	-70.14	-65.15
4500	-2.39	-2.39	-70.86	-69.92	-64.99
4750	-2.46	-2.46	-70.27	-69.60	-64.87
5000	-2.54	-2.54	-69.54	-68.61	-64.38
5250	-2.60	-2.60	-67.56	-67.38	-63.36
5500	-2.65	-2.65	-65.94	-65.97	-62.07
5750	-2.69	-2.69	-63.68	-63.88	-60.44
6000	-2.75	-2.75	-61.78	-61.14	-58.76
6250	-2.80	-2.80	-59.77	-58.90	-56.53
6500	-2.86	-2.86	-56.95	-56.09	-53.91
6750	-2.94	-2.94	-54.37	-53.74	-51.94
7000	-3.01	-3.01	-53.29	-52.89	-51.50
7250	-3.08	-3.08	-53.42	-53.43	-52.30
7500	-3.15	-3.15	-54.03	-54.31	-53.44
7750	-3.23	-3.23	-54.49	-54.88	-54.40
8000	-3.31	-3.31	-54.73	-55.29	-54.89
8250	-3.36	-3.36	-54.81	-55.69	-55.17
8500	-3.40	-3.40	-54.63	-55.64	-54.98
8750	-3.40	-3.40	-54.42	-55.81	-54.58
9000	-3.44	-3.44	-54.04	-55.40	-53.56
9250	-3.59	-3.59	-53.33	-54.24	-52.74
9500	-3.90	-3.90	-52.04	-52.40	-51.17
9750	-4.37	-4.37	-49.61	-49.18	-49.29
10000	-4.82	-4.82	-46.22	-45.95	-46.72

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.

Freq. (MHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
10	-18.01	-17.97	-18.10	-23.30	-23.65
250	-18.64	-18.64	-18.81	-23.82	-24.28
500	-19.08	-19.21	-19.31	-23.94	-24.32
750	-19.77	-19.96	-20.10	-23.93	-24.42
1000	-21.14	-21.24	-21.49	-23.75	-24.48
1250	-23.06	-23.23	-23.23	-23.66	-24.31
1500	-25.79	-26.39	-26.26	-23.70	-24.19
1750	-29.65	-29.65	-30.65	-23.39	-24.41
2000	-31.11	-29.51	-32.16	-22.98	-24.10
2250	-28.06	-26.13	-28.20	-22.68	-23.23
2500	-24.44	-22.83	-24.54	-22.25	-22.97
2750	-21.89	-20.52	-22.41	-21.87	-22.76
3000	-20.53	-18.86	-20.62	-21.62	-22.25
3250	-19.71	-17.79	-19.29	-21.46	-21.83
3500	-19.12	-17.07	-18.45	-21.38	-21.75
3750	-19.10	-16.76	-18.26	-21.36	-21.92
4000	-19.42	-16.92	-18.21	-21.63	-21.81
4250	-19.87	-17.53	-18.57	-21.91	-21.87
4500	-21.03	-18.82	-19.78	-22.51	-22.43
4750	-21.94	-20.71	-21.11	-23.33	-22.47
5000	-23.66	-23.66	-23.17	-23.70	-22.20
5250	-26.48	-28.13	-26.36	-24.37	-22.41
5500	-31.38	-37.20	-31.38	-25.24	-22.91
5750	-42.70	-33.46	-32.11	-25.82	-23.12
6000	-32.94	-27.40	-27.70	-26.93	-23.43
6250	-27.15	-24.06	-24.29	-28.54	-24.34
6500	-23.81	-22.14	-22.27	-30.55	-25.95
6750	-21.48	-20.68	-21.12	-34.53	-28.42
7000	-19.86	-19.20	-19.72	-37.78	-33.24
7250	-18.27	-17.81	-18.07	-30.47	-36.18
7500	-16.50	-16.26	-16.23	-25.08	-27.85
7750	-15.25	-14.94	-14.58	-21.32	-22.56
8000	-14.39	-13.99	-13.47	-18.33	-18.94
8250	-14.05	-13.60	-12.92	-15.81	-16.09
8500	-14.66	-14.28	-13.38	-13.80	-13.82
8750	-17.35	-17.21	-16.02	-11.92	-11.90
9000	-21.00	-24.12	-21.42	-10.63	-10.62
9250	-17.74	-21.36	-20.97	-9.68	-9.51
9500	-12.31	-13.70	-13.56	-8.73	-8.50
9750	-9.33	-9.89	-9.84	-8.01	-7.84
10000	-7.84	-8.02	-8.00	-7.55	-7.36

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.

Freq. (MHz)	Insertion Loss (dB)		Isolation, Active states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2
10	-1.44	-1.44	-101.91	-112.22	-101.61
250	-1.61	-1.61	-101.36	-101.04	-99.17
500	-1.68	-1.68	-108.89	-101.88	-97.24
750	-1.74	-1.74	-109.61	-100.76	-101.04
1000	-1.80	-1.80	-95.56	-95.47	-96.21
1250	-1.85	-1.85	-93.47	-102.91	-89.75
1500	-1.90	-1.90	-92.84	-92.60	-88.55
1750	-1.95	-1.95	-90.61	-90.46	-83.69
2000	-1.98	-1.98	-85.60	-87.39	-82.64
2250	-2.01	-2.01	-85.12	-83.82	-78.68
2500	-2.05	-2.05	-81.58	-79.11	-77.35
2750	-2.08	-2.08	-79.16	-77.51	-75.26
3000	-2.12	-2.12	-75.53	-75.18	-71.60
3250	-2.18	-2.18	-73.23	-72.83	-68.81
3500	-2.24	-2.24	-71.33	-71.24	-66.35
3750	-2.31	-2.31	-70.75	-70.92	-65.31
4000	-2.39	-2.39	-70.86	-70.91	-65.39
4250	-2.47	-2.47	-71.22	-71.19	-65.62
4500	-2.55	-2.55	-71.70	-71.02	-65.73
4750	-2.63	-2.63	-70.96	-70.08	-65.42
5000	-2.70	-2.70	-70.02	-69.52	-64.79
5250	-2.77	-2.77	-68.58	-68.39	-63.88
5500	-2.82	-2.82	-66.48	-66.57	-62.48
5750	-2.87	-2.87	-64.29	-64.27	-60.95
6000	-2.93	-2.93	-62.62	-61.91	-59.37
6250	-2.99	-2.99	-60.22	-59.59	-57.00
6500	-3.05	-3.05	-57.58	-56.93	-54.56
6750	-3.14	-3.14	-55.36	-54.70	-52.86
7000	-3.21	-3.21	-54.28	-53.90	-52.37
7250	-3.28	-3.28	-54.36	-54.28	-53.09
7500	-3.36	-3.36	-54.82	-54.99	-54.09
7750	-3.44	-3.44	-55.24	-55.53	-54.92
8000	-3.55	-3.55	-55.41	-55.90	-55.40
8250	-3.61	-3.61	-55.28	-56.12	-55.60
8500	-3.66	-3.66	-55.12	-56.05	-55.32
8750	-3.69	-3.69	-54.90	-56.19	-54.88
9000	-3.75	-3.75	-54.56	-55.99	-53.80
9250	-3.91	-3.91	-53.92	-54.94	-52.99
9500	-4.24	-4.24	-52.60	-52.90	-51.73
9750	-4.73	-4.73	-50.21	-49.88	-49.71
10000	-5.17	-5.17	-46.88	-46.68	-47.41

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.



Freq. (MHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
10	-17.36	-17.34	-17.42	-22.55	-22.87
250	-18.01	-18.03	-18.22	-23.25	-23.79
500	-18.47	-18.62	-18.62	-23.34	-23.62
750	-19.23	-19.30	-19.33	-23.21	-23.50
1000	-20.62	-20.75	-20.95	-23.27	-23.89
1250	-22.41	-22.85	-22.82	-23.18	-23.76
1500	-25.39	-25.79	-25.82	-23.15	-23.67
1750	-29.15	-29.12	-30.23	-22.76	-23.86
2000	-31.04	-29.43	-31.81	-22.40	-23.41
2250	-27.53	-25.66	-27.91	-22.11	-22.86
2500	-23.84	-22.30	-24.17	-21.68	-22.36
2750	-21.57	-20.22	-21.84	-21.56	-22.14
3000	-20.23	-18.51	-20.06	-21.41	-21.98
3250	-19.15	-17.49	-18.86	-21.21	-21.60
3500	-18.64	-16.65	-17.94	-21.00	-21.38
3750	-18.69	-16.30	-17.62	-21.09	-21.57
4000	-18.73	-16.55	-17.63	-21.37	-21.47
4250	-19.12	-17.10	-18.05	-21.50	-21.54
4500	-20.30	-18.32	-19.20	-21.92	-21.95
4750	-21.35	-20.33	-20.67	-22.86	-22.22
5000	-23.14	-23.18	-22.83	-23.32	-22.15
5250	-26.11	-27.27	-25.88	-23.87	-22.35
5500	-31.66	-34.10	-30.25	-24.58	-22.88
5750	-40.69	-33.00	-31.49	-25.11	-23.18
6000	-31.97	-26.84	-27.37	-26.42	-23.54
6250	-26.76	-23.44	-24.07	-28.39	-24.50
6500	-23.53	-21.46	-21.91	-30.84	-26.00
6750	-21.47	-19.88	-20.48	-36.08	-28.69
7000	-19.80	-18.58	-19.26	-42.84	-33.69
7250	-18.15	-17.55	-17.92	-30.64	-39.76
7500	-16.48	-16.33	-16.26	-25.26	-29.00
7750	-15.29	-15.20	-14.72	-21.48	-23.20
8000	-14.56	-14.31	-13.59	-18.60	-19.29
8250	-14.28	-13.91	-13.03	-16.12	-16.30
8500	-14.93	-14.58	-13.48	-14.09	-13.93
8750	-17.54	-17.46	-16.19	-12.13	-11.95
9000	-20.68	-24.19	-21.56	-10.74	-10.64
9250	-17.20	-20.66	-20.12	-9.77	-9.56
9500	-12.01	-13.40	-13.22	-8.81	-8.57
9750	-9.17	-9.74	-9.71	-8.08	-7.94
10000	-7.79	-7.96	-8.01	-7.62	-7.47

4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Graphs

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.





4 x SP2T Solid-State Switch

USB-4SP2T-852H



Typical Performance Graphs

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.



Typical Performance Graphs

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.





4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Graphs

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.





4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Graphs

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.

**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>





4 x SP2T Solid-State Switch

USB-4SP2T-852H

Typical Performance Graphs

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.


**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



Outline Dimensions

QM2279



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
QM2279	8.42 (213.9)	2.00 (50.8)	.475 (12.06)	.217 (5.51)	.69 (17.53)	.640 (16.26)	8.220 (208.79)	1.000 (25.40)	.10 (2.54)	.50 (12.70)	0.106 (2.69)	450

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Nickel Plated Aluminum.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Environmental Specifications ENV55T2



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-10° to 60° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3