

The Big Deal:

- Excellent Combination of gain, P1dB, IP3 and NF
- Flat Gain Response:
± 0.9 dB over 3300-3800 MHz
- 50Ω Input and Output:
no External Components Required



CASE STYLE: DL1636

Product Overview:

YSF-382+ is an advanced amplifier module in a Mini-Circuits System In Package **MSiP[®]**. This module is fully matched to 50Ω in/out impedance and has built-in Input & Output DC block capacitors. It is enclosed in a 5 x 6 mm MCLP plastic package. The YSF-382+ uses E-PHEMT technology enabling it to work with a single positive supply voltage.

Key Features

Feature	Advantages
Gain Flatness ± 0.9dB	The YSF-382+ provides outstanding gain flatness over the full International WIMAX communications band (3300-3800 MHz) making this ideal for use in applications where gain-flatness and repeatability are critical performance requirements.
Medium Gain: 15dB	The YSF-382+ is a two-stage design with internal feedback and bias to provide flat 15 dB nominal gain, supporting applications where a single gain block must overcome large system losses such as long cable runs and lossy components.
Strong Combination of Performance	The YSF-382+ provides a strong combination of performance parameters including high gain (15 dB), high IP3 (+36 dBm) and P1dB (+20 dBm) and low noise figures (2.5 dB) that are difficult to achieve in a single stage design and available only in the YSF amplifier series.
Integrated Matching, DC Blocking and Bias in Small Package	The YSF-382+ includes all support circuits including: Matching, Bias and DC Blocking, all integrated into a single 5x6mm package making the total footprint equal to or smaller than most solutions.
Excellent Return Loss	The YSF-382+ includes integrated input and output matching and bias circuits to make this amplifier a simple, complete drop-in solution. The matching circuits provide good output return loss (11dB), and are designed to give optimal P1dB and IP3 performance in a 50Ω environment.
High Reverse Isolation	With 28 dB of reverse isolation – the YSF-382+ is an ideal gain block for use in integrated systems to minimize VSWR interactions resulting from cascading highly reflective components such as sharp filters.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Flat Gain Amplifier

3.3-3.8 GHz

Product Features

- Matched 50-ohm surface mount amplifier
- Medium gain, 15 dB typ.
- Up to +20 dBm typ. output power
- High IP3, +36 dBm
- Low Noise Figure, 2.5 dB typ.
- High directivity, 28 dB isolation
- Internal Input & Output DC Block
- Separate terminal for DC
- Protected by us patent 8,994,157



YSF-382+

CASE STYLE: DL1636

Typical Applications

- WiMax
- Portable Wireless
- Receivers & transmitters
- Radar



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

General Description

YSF-382+ is an advanced amplifier module in a Mini-Circuits System In Package **MSiP[®]**. This module is fully matched to 50Ω in/out impedance and has built-in Input & Output DC block capacitors. It is enclosed in a 5 x 6 mm MCLP plastic package. The YSF-382+ uses E-PHEMT* technology enabling it to work with a single positive supply voltage.

simplified schematic and pad description



Function	Pad Number	Description
RF-IN	5	RF Input
RF-OUT	3	RF Output
DC	4	DC Supply
GND	Paddle	Connected to ground
NOT USED	1,2,6,7,8	No internal connection

*Enhancement mode Pseudomorphic High Electron Mobility Transistor

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Electrical Specifications⁽¹⁾ at 25°C, Zo=50Ω unless noted

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		3300		3800	MHz
Gain	3300	14.5	16.0	19.0	dB
	3600	13.0	14.5	17.0	
	3800	12.5	14.0	17.0	
Gain Flatness			0.9		± dB
Input Return Loss	3300	—	17.5		dB
	3600	10.00	14.5		
	3800	—	13.1		
Output Return Loss	3300	—	10.0		dB
	3600	7.0	10.5		
	3800	—	11.0		
Reverse Isolation			28.0		dB
Output Power @ 1 dB compression	3300	—	20.0		dBm
	3600	—	20.0		
	3800	18.0	20.0		
Output Power @ 3 dB compression			21.0		dBm
Output IP3	3300	—	36.0		dBm
	3600	31.0	36.0		
	3800	—	36.0		
Noise Figure	3300		2.5	—	dB
	3600		2.5	3.5	
	3800		2.6	—	
Device Operating Voltage			5		V
Device Operating Current			118	145	mA
Device Current Variation vs. Temperature ⁽²⁾			2		μA/°C
Device Current Variation vs Voltage			0.002		mA/mV
Thermal Resistance, junction-to-ground lead ⁽³⁾			56		°C/W

⁽¹⁾ Measured on Mini-Circuits Characterization test board TB-616+. See Characterization Test Circuit (Fig. 1)

⁽²⁾ D(+85°C to -45°C)


⁽³⁾ Thermal Resistance= $\frac{\text{Hot spot temperature} - \text{Ground lead temperature}}{\text{Power Dissipation}}$

Absolute Maximum Ratings

Parameter	Ratings	Units
Operating Temperature ⁽⁴⁾	-40 to 85	°C
Storage Temperature	-65 to 150	°C
DC Voltage on Pad 4	7	V
Power Dissipation	1.5	W
Input Power	21	dBm

Note: Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.

⁽⁴⁾ Case is defined as ground paddle.



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Characterization Test Circuit




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization Test Fixture TB-616+) Gain, Return loss, Output power at 1dB compression (P1 dB), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 10 MHz apart, 2.5 dBm/tone at output.

Recommended Application Circuit

(refer to evaluation board for PCB Layout and component values)





Fig 2. Recommended Application Circuit

Product Marking



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Additional Detailed Technical Information

additional information is available on our dash board. To access this information [click here](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DL1636 Plastic package, exposed paddle, lead finish: tin/silver/nickel
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 or 1K devices. 13" reels with 2K, or 4K devices.
Suggested Layout for PCB Design	PL-352
Evaluation Board	TB-616-6+
Environmental Ratings	ENV08T1

ESD Rating

Human Body Model (HBM): Class 1A in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (25V) in accordance with ANSI/ESD STM5.2-1999




Attention

Observe precautions
for handling electrostatic
sensitive devices

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL Test Flow Chart



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id=122.35mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.91	30.81	18.70	10.56	2.35	0.88	37.63	20.75	2.47
3325.0	16.81	30.68	18.44	10.46	2.33	0.87	37.82	20.86	2.52
3350.0	16.70	30.66	18.05	10.37	2.35	0.88	37.46	20.83	2.51
3375.0	16.59	30.55	17.61	10.27	2.34	0.87	38.02	20.75	2.46
3400.0	16.48	30.59	17.30	10.15	2.37	0.87	37.76	20.83	2.51
3425.0	16.39	30.61	16.97	10.15	2.39	0.88	37.52	20.81	2.48
3450.0	16.28	30.43	16.63	10.07	2.36	0.88	38.19	20.80	2.44
3475.0	16.18	30.34	16.25	9.98	2.35	0.88	38.02	20.82	2.46
3500.0	16.09	30.37	16.06	9.94	2.38	0.88	37.87	20.83	2.53
3525.0	16.01	30.21	15.70	9.91	2.35	0.88	37.78	20.71	2.55
3550.0	15.90	30.06	15.37	9.83	2.33	0.88	38.08	20.83	2.46
3575.0	15.80	30.10	15.16	9.80	2.36	0.88	38.06	20.84	2.55
3600.0	15.71	30.05	14.92	9.76	2.36	0.88	38.28	20.69	2.57
3625.0	15.63	29.91	14.69	9.77	2.35	0.88	38.04	20.84	2.53
3650.0	15.54	29.85	14.46	9.77	2.35	0.88	38.53	20.87	2.54
3675.0	15.45	29.84	14.27	9.83	2.37	0.89	38.05	20.82	2.49
3700.0	15.36	29.67	14.02	9.89	2.35	0.89	38.39	20.86	2.53
3725.0	15.28	29.77	13.82	9.96	2.40	0.89	38.20	21.09	2.57
3750.0	15.20	29.56	13.61	10.06	2.36	0.90	37.93	20.93	2.60
3775.0	15.11	29.48	13.39	10.15	2.37	0.90	38.52	21.01	2.59
3800.0	15.04	29.40	13.25	10.25	2.37	0.91	37.98	21.01	2.59

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id=121.67mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.96	30.54	19.12	10.28	2.26	0.87	37.27	20.41	2.48
3325.0	16.86	30.67	18.84	10.17	2.31	0.87	37.46	20.48	2.46
3350.0	16.76	30.51	18.40	10.10	2.29	0.87	36.99	20.47	2.44
3375.0	16.64	30.48	17.99	9.99	2.30	0.87	37.70	20.39	2.46
3400.0	16.54	30.43	17.68	9.90	2.30	0.87	37.36	20.45	2.52
3425.0	16.44	30.30	17.31	9.89	2.29	0.87	37.54	20.45	2.46
3450.0	16.34	30.43	16.92	9.80	2.34	0.87	37.31	20.44	2.43
3475.0	16.23	30.18	16.51	9.72	2.29	0.87	37.44	20.44	2.45
3500.0	16.14	30.12	16.36	9.69	2.29	0.87	37.33	20.46	2.51
3525.0	16.06	30.05	15.98	9.65	2.29	0.87	37.70	20.33	2.50
3550.0	15.95	29.96	15.63	9.58	2.29	0.87	37.89	20.47	2.44
3575.0	15.85	29.97	15.39	9.56	2.31	0.87	37.77	20.47	2.52
3600.0	15.76	29.89	15.15	9.52	2.30	0.87	38.11	20.34	2.51
3625.0	15.68	29.72	14.93	9.52	2.28	0.87	38.25	20.48	2.50
3650.0	15.58	29.74	14.69	9.52	2.30	0.87	38.14	20.51	2.54
3675.0	15.49	29.63	14.47	9.56	2.30	0.88	38.00	20.46	2.51
3700.0	15.41	29.57	14.22	9.63	2.30	0.88	38.39	20.50	2.55
3725.0	15.32	29.54	13.99	9.69	2.32	0.88	38.33	20.70	2.56
3750.0	15.24	29.38	13.77	9.79	2.30	0.89	37.87	20.56	2.57
3775.0	15.15	29.26	13.55	9.84	2.29	0.89	38.21	20.63	2.52
3800.0	15.08	29.26	13.41	9.96	2.31	0.90	37.89	20.62	2.54

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id=122.70mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.87	30.93	18.41	10.80	2.40	0.88	37.98	21.07	2.54
3325.0	16.76	30.85	18.15	10.67	2.39	0.88	37.67	21.20	2.50
3350.0	16.66	30.71	17.77	10.57	2.38	0.88	37.45	21.16	2.46
3375.0	16.56	30.72	17.43	10.49	2.40	0.88	37.98	21.09	2.46
3400.0	16.45	30.71	17.07	10.42	2.41	0.88	37.63	21.18	2.53
3425.0	16.35	30.71	16.77	10.38	2.43	0.89	37.62	21.15	2.46
3450.0	16.25	30.59	16.34	10.30	2.42	0.89	37.83	21.13	2.42
3475.0	16.15	30.40	16.00	10.20	2.39	0.88	37.83	21.17	2.51
3500.0	16.06	30.49	15.80	10.15	2.43	0.89	37.77	21.17	2.51
3525.0	15.97	30.40	15.50	10.13	2.42	0.89	38.08	21.05	2.58
3550.0	15.87	30.26	15.20	10.07	2.40	0.89	38.32	21.17	2.44
3575.0	15.77	30.34	14.99	10.02	2.44	0.89	38.32	21.17	2.57
3600.0	15.68	30.15	14.77	10.00	2.41	0.89	38.58	21.01	2.54
3625.0	15.60	30.13	14.53	10.00	2.42	0.89	38.10	21.17	2.55
3650.0	15.51	30.08	14.31	10.02	2.43	0.89	38.51	21.20	2.58
3675.0	15.41	30.03	14.11	10.07	2.44	0.90	38.40	21.16	2.51
3700.0	15.33	29.95	13.85	10.11	2.44	0.90	38.82	21.19	2.52
3725.0	15.24	29.79	13.64	10.19	2.42	0.90	38.31	21.44	2.56
3750.0	15.15	29.58	13.41	10.28	2.39	0.91	38.19	21.26	2.56
3775.0	15.07	29.55	13.25	10.37	2.40	0.91	38.44	21.36	2.55
3800.0	15.00	29.63	13.13	10.45	2.44	0.91	38.11	21.34	2.55

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id=120.34mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	17.77	30.33	20.90	10.64	2.06	0.86	37.17	20.87	1.92
3325.0	17.67	30.50	21.11	10.33	2.10	0.86	36.98	20.97	1.88
3350.0	17.56	30.41	20.52	10.28	2.10	0.86	36.79	20.94	1.92
3375.0	17.42	30.27	19.57	10.17	2.09	0.86	37.52	20.86	1.90
3400.0	17.34	30.39	19.39	10.12	2.13	0.86	37.10	20.94	1.92
3425.0	17.26	30.14	18.83	10.16	2.09	0.86	36.90	20.92	1.88
3450.0	17.08	30.19	18.43	9.80	2.11	0.86	37.29	20.91	1.81
3475.0	17.05	30.18	18.09	9.81	2.12	0.86	36.96	20.92	1.88
3500.0	16.95	30.02	17.72	9.80	2.10	0.86	37.36	20.93	1.93
3525.0	16.86	29.86	17.41	9.78	2.08	0.86	37.19	20.83	1.94
3550.0	16.72	29.77	16.72	9.67	2.08	0.86	37.32	20.93	1.86
3575.0	16.63	29.78	16.59	9.61	2.10	0.86	37.33	20.92	1.92
3600.0	16.52	29.72	16.26	9.52	2.10	0.86	37.39	20.78	2.00
3625.0	16.45	29.62	16.08	9.51	2.09	0.86	37.63	20.91	1.94
3650.0	16.33	29.66	15.54	9.45	2.12	0.86	37.33	20.93	1.98
3675.0	16.31	29.63	15.61	9.55	2.12	0.86	37.44	20.86	1.93
3700.0	16.21	29.51	15.21	9.64	2.11	0.87	37.78	20.86	1.90
3725.0	16.08	29.26	14.60	9.69	2.08	0.87	37.24	21.08	1.95
3750.0	16.02	29.37	14.50	9.72	2.12	0.88	37.42	20.95	1.99
3775.0	15.96	29.29	14.25	9.84	2.12	0.88	37.30	21.06	1.96
3800.0	15.85	29.06	13.99	9.99	2.10	0.88	37.46	21.12	1.97

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id=120.40mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	17.78	30.33	20.90	10.64	2.03	0.85	36.54	20.51	1.97
3325.0	17.68	30.50	21.11	10.33	2.09	0.85	36.38	20.58	1.90
3350.0	17.58	30.41	20.52	10.28	2.06	0.85	36.28	20.57	1.87
3375.0	17.43	30.27	19.57	10.17	2.07	0.85	36.73	20.49	1.88
3400.0	17.35	30.39	19.39	10.12	2.07	0.85	36.54	20.55	1.94
3425.0	17.28	30.14	18.83	10.16	2.10	0.86	36.31	20.54	1.87
3450.0	17.10	30.19	18.43	9.80	2.10	0.85	36.73	20.53	1.82
3475.0	17.06	30.18	18.09	9.81	2.11	0.85	36.31	20.52	1.90
3500.0	16.96	30.02	17.72	9.80	2.09	0.85	36.54	20.55	1.92
3525.0	16.87	29.86	17.41	9.78	2.08	0.85	36.39	20.44	1.95
3550.0	16.74	29.77	16.72	9.67	2.08	0.85	36.64	20.55	1.84
3575.0	16.64	29.78	16.59	9.61	2.06	0.85	36.68	20.54	1.94
3600.0	16.53	29.72	16.26	9.52	2.09	0.85	36.63	20.41	2.01
3625.0	16.47	29.62	16.08	9.51	2.08	0.85	36.72	20.54	1.95
3650.0	16.35	29.66	15.54	9.45	2.10	0.86	36.68	20.55	2.00
3675.0	16.32	29.63	15.61	9.55	2.11	0.86	36.60	20.48	1.94
3700.0	16.23	29.51	15.21	9.64	2.09	0.86	36.63	20.50	1.89
3725.0	16.10	29.26	14.60	9.69	2.09	0.87	36.68	20.69	1.95
3750.0	16.03	29.37	14.50	9.72	2.09	0.87	36.66	20.56	1.98
3775.0	15.98	29.29	14.25	9.84	2.08	0.87	36.42	20.65	1.96
3800.0	15.87	29.06	13.99	9.99	2.06	0.88	36.58	20.70	1.98

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id=120.94mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	17.76	30.39	20.69	10.72	2.07	0.86	38.09	21.20	1.96
3325.0	17.65	30.60	20.89	10.41	2.13	0.86	37.47	21.33	1.88
3350.0	17.55	30.55	20.24	10.35	2.13	0.86	37.29	21.28	1.91
3375.0	17.42	30.38	19.35	10.25	2.12	0.86	38.11	21.21	1.89
3400.0	17.32	30.50	19.09	10.17	2.15	0.86	37.52	21.30	1.95
3425.0	17.25	30.22	18.60	10.23	2.11	0.86	37.51	21.27	1.89
3450.0	17.05	30.30	18.12	9.85	2.15	0.86	38.07	21.25	1.82
3475.0	17.04	30.31	17.93	9.87	2.15	0.86	37.33	21.28	1.89
3500.0	16.93	30.09	17.46	9.88	2.12	0.86	37.37	21.29	1.92
3525.0	16.85	29.95	17.15	9.86	2.11	0.86	37.88	21.19	1.95
3550.0	16.71	29.83	16.56	9.76	2.10	0.86	37.74	21.28	1.89
3575.0	16.62	29.80	16.41	9.69	2.11	0.86	37.91	21.27	1.97
3600.0	16.51	29.76	16.12	9.60	2.11	0.86	38.12	21.12	2.03
3625.0	16.44	29.74	15.96	9.58	2.12	0.86	37.90	21.26	1.96
3650.0	16.32	29.75	15.39	9.52	2.14	0.87	38.22	21.27	2.02
3675.0	16.30	29.74	15.48	9.62	2.15	0.87	38.15	21.21	1.89
3700.0	16.20	29.49	15.10	9.71	2.11	0.87	38.22	21.20	1.91
3725.0	16.07	29.36	14.46	9.75	2.11	0.88	37.92	21.44	1.98
3750.0	16.01	29.42	14.36	9.78	2.13	0.88	38.39	21.30	1.96
3775.0	15.95	29.21	14.10	9.92	2.10	0.88	38.16	21.44	1.93
3800.0	15.85	29.08	13.88	10.07	2.10	0.89	38.14	21.50	1.95

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id=121.83mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.20	30.93	16.48	11.04	2.57	0.90	37.48	20.61	3.06
3325.0	16.04	30.90	16.17	10.80	2.59	0.90	37.10	20.72	3.14
3350.0	15.97	30.89	16.09	10.72	2.60	0.90	37.03	20.69	3.09
3375.0	15.90	30.82	15.83	10.71	2.59	0.90	37.59	20.62	3.06
3400.0	15.76	30.86	15.50	10.51	2.63	0.90	37.23	20.71	3.14
3425.0	15.68	30.74	15.09	10.63	2.62	0.90	37.35	20.69	3.08
3450.0	15.52	30.66	14.90	10.44	2.62	0.90	37.44	20.67	3.06
3475.0	15.44	30.64	14.74	10.24	2.62	0.90	37.17	20.70	3.08
3500.0	15.37	30.55	14.44	10.32	2.62	0.90	37.57	20.71	3.15
3525.0	15.29	30.51	14.22	10.33	2.62	0.90	37.30	20.58	3.14
3550.0	15.20	30.40	13.97	10.26	2.61	0.90	37.73	20.72	3.19
3575.0	15.11	30.45	13.82	10.25	2.65	0.91	37.79	20.73	3.19
3600.0	15.00	30.13	13.55	10.25	2.58	0.91	37.99	20.59	3.13
3625.0	14.93	30.20	13.46	10.27	2.62	0.91	37.94	20.75	3.09
3650.0	14.81	30.06	13.21	10.19	2.60	0.91	37.84	20.80	3.15
3675.0	14.76	30.23	13.17	10.35	2.67	0.92	37.60	20.78	3.15
3700.0	14.67	30.10	12.95	10.44	2.66	0.92	38.29	20.81	3.15
3725.0	14.59	29.94	12.77	10.60	2.64	0.92	37.85	21.02	3.16
3750.0	14.45	29.79	12.45	10.60	2.63	0.93	37.42	20.83	3.19
3775.0	14.44	29.96	12.59	10.71	2.69	0.93	37.94	20.94	3.17
3800.0	14.34	29.76	12.30	10.89	2.66	0.94	37.53	20.97	3.21

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id=120.86mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.23	30.73	16.74	10.64	2.49	0.89	37.07	20.25	3.07
3325.0	16.07	30.58	16.42	10.43	2.48	0.89	36.45	20.33	3.12
3350.0	16.00	30.72	16.31	10.34	2.53	0.89	36.63	20.32	3.03
3375.0	15.93	30.61	16.08	10.33	2.52	0.89	37.10	20.24	3.03
3400.0	15.78	30.60	15.70	10.14	2.53	0.89	36.83	20.32	3.08
3425.0	15.70	30.45	15.32	10.26	2.51	0.89	36.69	20.31	3.02
3450.0	15.55	30.42	15.12	10.07	2.53	0.89	37.04	20.31	3.01
3475.0	15.46	30.52	14.93	9.88	2.57	0.89	36.78	20.31	3.00
3500.0	15.39	30.45	14.60	9.97	2.57	0.89	37.09	20.33	3.07
3525.0	15.32	30.22	14.40	9.97	2.52	0.89	36.87	20.19	3.12
3550.0	15.22	30.19	14.13	9.92	2.53	0.89	37.45	20.35	3.10
3575.0	15.13	30.16	14.00	9.91	2.54	0.89	37.17	20.36	3.10
3600.0	15.02	29.99	13.70	9.90	2.52	0.90	37.37	20.23	3.10
3625.0	14.95	30.02	13.61	9.92	2.55	0.90	37.89	20.39	3.08
3650.0	14.83	29.83	13.33	9.84	2.52	0.90	37.52	20.43	3.13
3675.0	14.79	30.02	13.31	9.97	2.59	0.90	37.15	20.40	3.06
3700.0	14.70	29.88	13.10	10.06	2.57	0.91	37.56	20.45	3.08
3725.0	14.61	29.71	12.88	10.20	2.55	0.91	37.23	20.63	3.12
3750.0	14.48	29.52	12.58	10.21	2.53	0.91	37.20	20.47	3.14
3775.0	14.46	29.68	12.69	10.32	2.59	0.92	37.30	20.57	3.12
3800.0	14.36	29.48	12.41	10.49	2.56	0.92	37.28	20.60	3.18

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 5.25V, Id=122.63mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
3300.0	16.18	31.08	16.25	11.29	2.62	0.91	37.70	20.94	3.12
3325.0	16.00	31.00	16.08	11.02	2.64	0.90	37.17	21.06	3.19
3350.0	15.96	31.04	15.91	10.97	2.65	0.91	37.20	21.04	3.11
3375.0	15.88	30.89	15.66	10.97	2.63	0.91	37.39	20.97	3.13
3400.0	15.74	30.95	15.30	10.75	2.66	0.91	37.42	21.06	3.16
3425.0	15.66	30.72	14.96	10.88	2.62	0.91	37.17	21.03	3.12
3450.0	15.51	30.80	14.76	10.68	2.67	0.91	37.58	21.00	3.09
3475.0	15.43	30.86	14.63	10.49	2.70	0.91	37.57	21.06	3.12
3500.0	15.36	30.67	14.32	10.57	2.67	0.91	37.66	21.06	3.17
3525.0	15.28	30.59	14.11	10.56	2.66	0.91	37.39	20.94	3.17
3550.0	15.18	30.57	13.85	10.51	2.67	0.91	37.99	21.06	3.20
3575.0	15.09	30.40	13.70	10.51	2.64	0.91	37.68	21.07	3.22
3600.0	14.99	30.48	13.42	10.49	2.69	0.92	38.11	20.92	3.19
3625.0	14.92	30.47	13.38	10.51	2.71	0.92	37.95	21.09	3.16
3650.0	14.80	30.39	13.11	10.42	2.71	0.92	37.83	21.14	3.26
3675.0	14.75	30.28	13.06	10.58	2.70	0.92	37.72	21.13	3.18
3700.0	14.66	30.18	12.86	10.70	2.69	0.93	38.02	21.15	3.14
3725.0	14.58	30.13	12.65	10.84	2.70	0.93	37.82	21.37	3.23
3750.0	14.42	29.79	12.31	10.86	2.64	0.93	37.79	21.17	3.24
3775.0	14.43	30.12	12.49	11.00	2.75	0.94	38.21	21.28	3.24
3800.0	14.32	29.88	12.22	11.16	2.71	0.94	38.03	21.31	3.24


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
DL1636	.236 (6.00)	.193 (4.90)	.035 (0.90)	.008 (0.20)	.160 (4.05)	.153 (3.89)	.017 (0.42)	-- --	.024 (0.60)	.050 (1.27)	.162 (4.11)	.040 (1.02)	.020 (0.51)

CASE #	P	Q	R	S	T	WT. GRAM
DL1636	.257 (6.53)	.011 (0.28)	.155 (3.94)	.020 (0.51)	.050 (1.27)	.08

Dimensions are in inches (mm). Tolerances: 3Pl. $\pm .004$, unless otherwise specified.

Notes:

- Case material: Plastic.
- Termination finish:

For RoHS Case Styles: Tin-Silver-Nickel plate or Matte-Tin. All models, (+) suffix. See model data sheet.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F68



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M133331	NEW RELEASE	11/07/11	PW	TH

**SUGGESTED MOUNTING CONFIGURATION FOR
DL1636 CASE STYLE, "08AM05" PIN CODE**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. FOOTPRINT FOR 0805 CHIP CAPACITOR IS SHOWN FOR REFERENCE.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

PW

08/25/11

TOLERANCES ON:

CHECKED

IL


10/21/11

2 PL DECIMALS $\pm$

APPROVED

TH

11/07/11

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 08AM05, DL1636, TB-616-X+

SIZE
ACODE IDENT
15542

DRAWING NO:

98-PL-352

REV:

OR

FILE: 98PL352


SCALE:

8:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-616-6+



COMPONENT	VALUE
DUT	YSF-382+
C1	1000 pF

Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215