



Mini-Circuits

WIDEBAND, MICROWAVE

Monolithic Amplifier


AVA-183A+

50Ω

5 to 18 GHz

THE BIG DEAL

- Surface Mount Amplifier up to 18 GHz
- Integrated DC blocks, Bias-Tee & Microwave bypass capacitor
- Superior Value
- Suitable for low phase noise applications
- Gain, 13.8 dB typ. & Flatness, ± 1.2 dB
- Output Power, up to +19.0 dBm typ.
- Excellent isolation, 36 dB typ. at 12 GHz
- Single Positive Supply Voltage, +5V
- Unconditionally Stable
- Aqueous washable; 3mm x 3mm SMT package



Generic photo used for illustration purposes only

CASE STYLE: DQ849

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Military EW and Radar
- DBS
- Wideband Isolation amplifier
- Microwave point-to-point radios
- Satellite systems

PRODUCT OVERVIEW

The AVA-183A+ is a surface mount, microwave amplifier fabricated using InGaAs PHEMT technology and is a fully integrated gain block up to 18 GHz. It is packaged in Mini-Circuits industry standard 3x3 mm MCLP package, which provides excellent RF and thermal performance. The AVA-183A+ integrates the entire matching network with the majority of the bias circuit inside the package, reducing the need for complicated external circuits. This approach makes the AVA-183A+ extremely flexible and enables simple, straightforward use.

KEY FEATURES

Feature	Advantages
Wideband, 5 to 18 GHz	Broad frequency range supports a wide array of applications from microwave radio and radar, to military communications and countermeasures.
Excellent Gain Flatness	Typical ± 1.2 dB gain flatness across the entire frequency range minimizes the need for external equalizer networks making it a great fit for instrumentation and EW applications.
High Isolation	With reverse isolation of 31-42 dB (17-23 dB directivity), the AVA-183A+ is an excellent choice for buffering broadband circuits. It is an ideal LO driver amplifier and provides designers system flexibility and margin when integrating cascaded RF components.
Single +5V Supply	No hassle associated with amplifiers using dual supply; such as power supply sequencing. Integrated output bias-tee, simplifies layout & reduces cost.
Manufacturability	MSL1 and ESD Class1A (HBM) ratings minimize special handling on production lines.
Low additive phase noise, typically -151 dBc/Hz @10 KHz offset	Ideal for low phase noise synthesizer applications

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-011155
AVA-183A+
RS/TH/CP
230728

PAGE 1 OF 5



WIDEBAND, MICROWAVE

Monolithic Amplifier

AVA-183A+

ELECTRICAL SPECIFICATIONS⁽¹⁾ AT 25°C, Z₀=50Ω, (REFER TO CHARACTERIZATION CIRCUIT, FIG.1)

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		5.0		18.0	GHz
DC Voltage (V _{D1} , V _{D2})			5.0		V
DC Current (I _{D1} +I _{D2})		104	131	166	mA
Gain	5.0	—	12.9	—	dB
	8.0	12.0	14.7	—	
	10.0	12.0	14.0	—	
	12.0	—	13.4	—	
	14.0	—	13.1	—	
	16.0	—	13.6	—	
	18.0	10.8	12.4	—	
Input Return Loss	5.0		10.4		dB
	8.0		17.0		
	10.0		11.0		
	12.0		11.0		
	14.0		11.0		
	16.0		11.0		
	18.0		7.5		
Output Return Loss	5.0		8.0		dB
	8.0		18.0		
	10.0		14.0		
	12.0		11.0		
	14.0		10.6		
	16.0		11.2		
	18.0		11.8		
Output IP3 ⁽²⁾	5.0		32.2		dBm
	8.0		29.0		
	10.0		27.7		
	12.0		26.3		
	14.0		25.1		
	16.0		24.3		
	18.0		24.4		
Output Power @ 1 dB compression	5.0	—	17.6		dBm
	8.0	—	18.0		
	10.0	16.0	19.0		
	12.0	—	19.0		
	14.0	—	19.9		
	16.0	—	19.6		
	18.0	—	18.7		
Noise Figure	5.0		7.4		dB
	8.0		4.3		
	10.0		4.5		
	12.0		4.8		
	14.0		5.1		
	16.0		5.1		
	18.0		6.0		
Additive Phase Noise 5.0 GHz, 10KHz offset			-151		dBc/Hz
Directivity (Isolation-Gain)	12		23.1		dB
DC Current Variation vs. Temperature ⁽³⁾			0.046		mA/°C
Thermal Resistance			61		°C/W

MAXIMUM RATINGS⁽⁴⁾

Parameter	Ratings
Operating Temperature ⁽⁵⁾	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Channel Temperature	150°C
DC Voltage (Pad 7,8)	+5.5 V
DC Voltage (Pads 2, 5)	+10 V
Power Dissipation	980 mW
DC Current (Pad 7+8)	180 mA
Input Power (CW)	+20 dBm


(1) Measured on Mini-Circuits Characterization test fixture TB-547-2+ See Characterization Test Circuit (Fig. 1)

(2) At P_{out}=9dBm/100

(3) (Current at 85°C - Current at -45°C)/130

(4) Permanent damage may occur if any of these limits are exceeded. These maximum ratings are not intended for continuous normal operation.

(5) Defined with reference to ground pad temperature.







Mini-Circuits

WIDEBAND, MICROWAVE



Monolithic Amplifier

AVA-183A+

INTERMODULATION AND IP3 VS. FREQUENCY AND OUTPUT POWER



SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION




Function	Pad Number	Description (See Application Circuit, Fig. 2)
RF-IN	2	RF input pad
RF-OUT	5	RF output pad
DC	8(V_{D1}), 7(V_{D2})	DC power supply
GND	paddle in center of bottom	Connected to ground
NOT USED	1,3,4,6	No internal connection; recommended use: per PCB Layout PL-328

Mini-Circuits



CHARACTERIZATION TEST CIRCUIT



C1=5.6pF, 0402 (NPO)
 C2=18pF, 0402 (NPO)
 C3=0.001μF, 0402 (NPO)
 C4=0.1 μF, 0402 (X7R)
 L1=3.3nH, 0805 (wire wound)

ML1-ML7 are short microstrip lines
 Refer to 98-PL-328

Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization Test Board TB-547-2+) Gain, Output power at 1dB compression (P1dB), Noise Figure, Output IP3 (OIP3) are measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain: Pin=-25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 9 dBm/tone at output.
3. Vs adjusted for 5.0V at device (VD1 and VD2), compensating loss of bias lines.

RECOMMENDED APPLICATION CIRCUIT

(refer to evaluation board for PCB Layout and component values)




Fig 2. Recommended Application Circuit

C1=5.6pF, 0402 (NPO)
 C2=18pF, 0402 (NPO)
 C3=0.001μF, 0402 (NPO)
 C4=0.1 μF, 0402 (X7R)
 L1=3.3nH, 0805 (wire wound)

ML1-ML7 are short microstrip lines
 Refer to 98-PL-328

PRODUCT MARKING



- ← black body
- ← model family designation

Marking may contain other features or characters for internal lot control



Mini-Circuits

WIDEBAND, MICROWAVE

Monolithic Amplifier

AVA-183A+

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ849 Plastic package, exposed paddle, lead finish: Matte-tin
Tape & Reel Standard quantities available on reel	F104 7" reels with 20, 50, 100, 200, 500, 1000 or 2000 devices
Suggested Layout for PCB Design	PL-328
Evaluation Board	TB-547-2+
Environmental Ratings	ENV08T1

ESD RATING


Human Body Model (HBM): 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): M1 (25V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART



- NOTES
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 132.12mA @ Temperature = 25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	12.93	41.14	11.79	7.77	10.13	0.88	32.66	17.23	7.19
5.2	13.37	40.17	13.87	8.47	9.09	0.88	29.59	17.82	6.52
5.4	13.72	39.50	16.20	9.25	8.44	0.89	30.15	17.86	5.98
5.6	13.96	38.93	18.66	9.76	7.88	0.90	30.59	18.15	5.60
5.8	14.15	38.57	20.99	10.38	7.55	0.91	31.46	17.78	5.28
6.0	14.29	38.04	22.30	10.85	7.08	0.92	34.16	17.96	5.06
6.2	14.40	37.74	22.08	11.54	6.84	0.93	30.07	17.91	4.84
6.4	14.50	37.46	21.65	11.97	6.58	0.94	28.87	18.07	4.69
6.6	14.57	37.19	21.24	12.52	6.38	0.94	29.02	18.07	4.58
6.8	14.63	36.96	21.15	13.45	6.24	0.96	28.88	17.92	4.47
7.0	14.69	36.89	21.97	14.34	6.21	0.96	29.38	17.58	4.45
7.2	14.72	36.56	22.39	15.65	6.02	0.97	30.81	17.45	4.31
7.4	14.75	36.53	24.94	16.93	6.03	0.98	29.25	17.80	4.25
7.6	14.76	36.40	27.93	19.10	5.99	0.98	28.57	16.36	4.20
7.8	14.75	36.35	33.77	21.29	6.01	0.99	28.25	17.82	4.19
8.0	14.74	36.30	44.19	25.61	6.01	0.99	28.00	17.58	4.19
8.2	14.69	36.39	33.39	33.75	6.12	0.99	27.87	17.81	4.18
8.3	14.68	36.23	29.04	41.01	6.01	0.99	27.85	17.77	4.19
8.4	14.63	36.56	25.86	34.88	6.26	1.00	28.06	17.76	4.16
8.8	14.50	36.38	21.05	21.53	6.17	0.99	27.62	18.08	4.24
8.9	14.46	36.28	20.21	20.07	6.10	0.99	27.48	17.64	4.30
9.0	14.40	36.18	19.63	18.58	6.04	0.99	27.39	18.02	4.31
9.1	14.36	36.30	18.94	17.69	6.13	0.99	27.62	18.01	4.28
9.2	14.29	36.39	17.71	16.70	6.18	0.99	27.53	18.60	4.29
9.3	14.24	36.37	17.03	15.65	6.15	0.98	27.64	17.95	4.29
9.6	14.05	36.76	15.97	14.41	6.48	0.98	27.18	18.49	4.42
9.7	13.99	36.75	15.28	13.87	6.47	0.98	27.20	18.89	4.42
9.8	13.89	36.87	15.00	13.31	6.58	0.97	27.41	18.20	4.43
9.9	13.90	36.74	15.13	13.01	6.46	0.97	27.04	18.51	4.45
10.0	13.87	36.50	14.73	12.80	6.27	0.97	27.15	18.69	4.44
10.5	13.59	36.78	13.13	11.56	6.48	0.96	26.88	19.10	4.61
11.0	13.37	36.62	11.81	10.88	6.34	0.96	26.54	19.35	4.75
11.5	13.18	36.52	10.96	10.41	6.25	0.97	26.03	19.05	4.79
12.0	13.00	36.27	10.38	10.02	6.07	0.97	25.66	18.74	4.91
12.5	12.89	36.15	9.93	9.93	5.99	0.97	25.38	19.15	5.01
13.0	12.79	35.85	9.56	9.77	5.76	0.98	25.14	18.72	5.17
13.5	12.76	35.20	9.77	9.81	5.39	0.98	25.11	19.45	5.22
14.0	12.86	34.98	10.37	10.15	5.30	0.98	27.99	19.49	5.25
14.5	13.04	34.39	11.70	10.43	4.99	0.96	25.06	19.49	5.26
15.0	13.33	33.80	13.83	11.39	4.73	0.96	24.26	19.97	5.35
15.5	13.54	33.05	16.50	12.31	4.39	0.95	26.16	20.00	5.23
16.0	13.70	32.65	17.83	13.31	4.21	0.96	24.17	20.15	5.26
16.5	13.75	32.25	16.28	15.85	4.07	0.98	24.06	20.21	5.29
17.0	13.56	31.98	13.43	14.68	3.93	0.99	23.96	19.93	5.33
17.5	13.15	31.97	10.79	13.29	3.93	1.01	23.19	18.80	5.63
18.0	12.62	32.20	9.09	11.54	4.02	1.02	24.16	18.21	5.93

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 131.25mA @ Temperature = 25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	13.06	41.12	11.77	7.80	9.96	0.88	33.38	16.71	7.17
5.2	13.50	40.11	13.84	8.50	8.90	0.89	30.58	17.35	6.48
5.4	13.84	39.48	16.15	9.30	8.32	0.90	31.18	17.35	5.96
5.6	14.08	38.90	18.57	9.80	7.76	0.90	32.19	17.62	5.56
5.8	14.26	38.53	20.96	10.44	7.43	0.91	37.51	17.18	5.26
6.0	14.41	38.01	22.27	10.92	6.97	0.92	30.91	17.39	5.03
6.2	14.52	37.71	22.25	11.61	6.73	0.93	37.74	17.30	4.81
6.4	14.62	37.46	21.75	12.06	6.51	0.94	29.88	17.44	4.65
6.6	14.69	37.22	21.46	12.61	6.33	0.95	29.71	17.45	4.55
6.8	14.74	36.92	21.29	13.54	6.14	0.96	29.94	17.29	4.50
7.0	14.80	36.89	22.09	14.43	6.13	0.96	33.18	16.93	4.51
7.2	14.84	36.57	22.45	15.79	5.95	0.97	34.06	16.83	4.31
7.4	14.86	36.61	25.08	17.05	6.02	0.98	33.14	17.16	4.23
7.6	14.88	36.38	27.88	19.25	5.91	0.98	30.98	16.71	4.20
7.8	14.87	36.34	33.16	21.44	5.92	0.99	28.86	17.17	4.17
8.0	14.86	36.32	49.36	25.90	5.94	0.99	28.52	16.94	4.14
8.2	14.81	36.44	33.89	34.64	6.07	0.99	28.65	17.18	4.17
8.3	14.80	36.28	29.25	47.90	5.96	0.99	28.75	17.13	4.13
8.4	14.76	36.52	26.34	35.06	6.15	1.00	29.59	17.14	4.11
8.8	14.63	36.37	21.28	21.73	6.07	0.99	28.74	17.43	4.20
8.9	14.60	36.21	20.48	20.15	5.96	0.99	28.54	17.00	4.24
9.0	14.52	36.25	19.86	18.70	6.01	0.99	28.03	17.36	4.27
9.1	14.50	36.24	19.09	17.76	5.99	0.99	28.97	17.34	4.26
9.2	14.43	36.33	17.92	16.78	6.05	0.99	27.85	17.94	4.27
9.3	14.38	36.35	17.21	15.73	6.06	0.98	29.09	17.30	4.25
9.6	14.20	36.65	16.08	14.52	6.31	0.98	27.96	17.83	4.37
9.7	14.15	36.65	15.42	13.94	6.29	0.98	27.60	18.23	4.38
9.8	14.03	36.92	15.14	13.38	6.52	0.97	28.81	17.53	4.40
9.9	14.06	36.61	15.27	13.05	6.26	0.97	27.43	17.86	4.40
10.0	14.03	36.46	14.86	12.93	6.15	0.97	28.08	18.04	4.39
10.5	13.76	36.69	13.25	11.69	6.32	0.96	27.56	18.46	4.54
11.0	13.55	36.62	11.95	11.05	6.24	0.97	26.98	18.38	4.69
11.5	13.37	36.41	11.11	10.50	6.07	0.97	26.33	18.43	4.82
12.0	13.20	36.18	10.49	10.10	5.91	0.97	25.88	18.11	4.87
12.5	13.10	36.00	10.05	10.01	5.77	0.97	25.57	18.52	4.94
13.0	13.02	35.78	9.69	9.82	5.60	0.98	25.32	18.07	5.07
13.5	13.00	35.07	9.94	9.88	5.20	0.97	25.36	18.82	5.11
14.0	13.11	34.96	10.51	10.20	5.17	0.97	27.12	18.87	5.23
14.5	13.29	34.27	11.88	10.49	4.81	0.96	25.64	18.84	5.24
15.0	13.58	33.62	14.06	11.41	4.52	0.96	25.07	19.37	5.30
15.5	13.80	32.79	16.78	12.31	4.15	0.95	25.33	19.40	5.21
16.0	13.96	32.65	18.15	13.44	4.10	0.96	24.69	19.58	5.20
16.5	14.02	32.14	16.62	16.19	3.91	0.98	24.44	19.65	5.27
17.0	13.84	31.94	13.64	14.90	3.81	0.99	24.04	19.63	5.30
17.5	13.41	31.88	10.88	13.27	3.78	1.00	24.37	18.14	5.59
18.0	12.86	32.15	9.14	11.48	3.90	1.01	25.06	17.54	5.90

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 132.75mA @ Temperature = 25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	12.80	41.17	11.80	7.75	10.30	0.88	29.67	17.64	7.22
5.2	13.25	40.19	13.88	8.44	9.22	0.88	29.13	18.22	6.54
5.4	13.60	39.54	16.23	9.21	8.59	0.89	29.60	18.29	6.04
5.6	13.85	38.94	18.73	9.72	7.99	0.90	29.91	18.58	5.63
5.8	14.04	38.57	21.00	10.33	7.64	0.91	29.44	18.29	5.33
6.0	14.18	38.07	22.29	10.80	7.18	0.92	29.66	18.47	5.10
6.2	14.29	37.74	21.99	11.47	6.91	0.93	28.52	18.44	4.88
6.4	14.40	37.48	21.57	11.89	6.67	0.94	28.44	18.59	4.72
6.6	14.47	37.19	21.09	12.44	6.44	0.94	28.69	18.62	4.62
6.8	14.53	37.02	21.14	13.37	6.35	0.95	28.49	18.47	4.50
7.0	14.59	36.88	21.91	14.25	6.27	0.96	28.23	18.14	4.40
7.2	14.62	36.57	22.41	15.57	6.10	0.97	28.45	18.00	4.37
7.4	14.64	36.50	24.98	16.81	6.09	0.98	27.91	18.36	4.28
7.6	14.66	36.40	28.09	18.97	6.07	0.98	27.71	17.92	4.22
7.8	14.65	36.34	34.37	21.12	6.07	0.99	28.06	18.38	4.23
8.0	14.64	36.29	40.22	25.29	6.07	0.99	27.82	18.14	4.18
8.2	14.58	36.43	32.75	32.64	6.23	0.99	27.60	18.39	4.19
8.3	14.57	36.23	28.61	37.16	6.08	0.99	27.55	18.33	4.25
8.4	14.52	36.57	25.53	34.14	6.35	1.00	27.51	18.35	4.21
8.8	14.38	36.39	20.89	21.41	6.25	0.99	27.19	18.67	4.25
8.9	14.34	36.29	19.98	19.93	6.19	0.99	27.10	18.25	4.31
9.0	14.27	36.24	19.42	18.52	6.17	0.99	27.14	18.61	4.34
9.1	14.23	36.37	18.73	17.64	6.25	0.99	27.08	18.61	4.30
9.2	14.16	36.44	17.61	16.67	6.31	0.99	27.47	19.16	4.34
9.3	14.11	36.39	16.91	15.59	6.26	0.98	26.99	18.54	4.32
9.6	13.92	36.82	15.80	14.34	6.62	0.98	26.90	19.10	4.44
9.7	13.85	36.77	15.16	13.79	6.57	0.98	27.09	19.47	4.44
9.8	13.76	36.81	14.89	13.19	6.62	0.97	26.76	18.80	4.43
9.9	13.76	36.79	14.96	12.93	6.58	0.97	26.94	19.11	4.47
10.0	13.74	36.55	14.60	12.71	6.40	0.97	26.75	19.26	4.48
10.5	13.44	36.88	13.02	11.48	6.64	0.96	26.63	19.65	4.62
11.0	13.21	36.66	11.73	10.79	6.46	0.96	26.43	19.55	4.72
11.5	13.00	36.55	10.85	10.34	6.37	0.97	25.98	19.58	4.83
12.0	12.81	36.35	10.27	9.93	6.23	0.97	25.67	19.30	4.94
12.5	12.69	36.23	9.78	9.87	6.14	0.98	25.34	19.69	5.02
13.0	12.59	35.93	9.42	9.72	5.91	0.98	25.14	19.29	5.18
13.5	12.55	35.26	9.67	9.75	5.54	0.98	25.06	19.94	5.30
14.0	12.65	35.04	10.28	10.10	5.45	0.98	25.05	19.98	5.29
14.5	12.82	34.50	11.58	10.36	5.17	0.96	25.22	19.97	5.32
15.0	13.11	33.98	13.64	11.28	4.93	0.96	23.97	20.41	5.38
15.5	13.32	33.22	16.23	12.19	4.58	0.95	25.52	20.46	5.29
16.0	13.47	32.71	17.51	13.13	4.34	0.96	23.99	20.61	5.31
16.5	13.51	32.31	16.05	15.69	4.20	0.98	24.10	20.65	5.34
17.0	13.32	32.05	13.31	14.72	4.07	0.99	26.34	20.47	5.40
17.5	12.92	32.04	10.71	13.39	4.05	1.01	22.91	19.38	5.63
18.0	12.39	32.25	9.02	11.62	4.14	1.02	24.05	18.79	5.97

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 126.94mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	14.34	40.89	11.10	7.50	8.19	0.87	31.49	17.17	6.20
5.2	14.74	39.99	13.00	8.29	7.51	0.88	32.40	17.73	5.54
5.4	15.06	39.39	15.07	9.14	7.09	0.89	31.80	17.84	5.04
5.6	15.28	38.82	17.47	9.78	6.67	0.90	31.17	18.09	4.67
5.8	15.44	38.51	19.60	10.34	6.46	0.91	32.07	17.76	4.35
6.0	15.57	38.00	21.32	10.93	6.09	0.92	32.51	17.98	4.19
6.2	15.67	37.69	21.61	11.51	5.88	0.93	35.90	17.97	3.94
6.4	15.78	37.48	21.78	12.01	5.72	0.93	34.66	18.11	3.77
6.6	15.84	37.22	21.25	12.64	5.55	0.94	34.06	18.18	3.70
6.8	15.90	36.94	21.49	13.26	5.39	0.95	34.38	18.00	3.57
7.0	15.96	36.87	21.73	14.40	5.37	0.96	34.92	17.70	3.49
7.2	16.00	36.58	22.33	15.24	5.22	0.97	35.85	17.61	3.41
7.4	16.03	36.55	23.85	16.85	5.23	0.97	38.98	17.95	3.39
7.6	16.06	36.44	26.18	18.42	5.19	0.98	39.82	17.41	3.33
7.8	16.07	36.36	29.73	20.90	5.17	0.98	36.44	17.88	3.32
8.0	16.07	36.35	34.06	24.39	5.19	0.99	35.88	17.63	3.25
8.2	16.04	36.39	35.75	29.89	5.25	0.99	36.09	17.89	3.27
8.3	16.04	36.16	34.25	33.36	5.12	0.99	38.38	17.81	3.26
8.4	16.00	36.50	29.31	31.11	5.33	0.99	36.85	17.68	3.25
8.8	15.89	36.47	23.35	22.03	5.34	0.99	38.02	17.95	3.34
8.9	15.87	36.23	21.96	20.51	5.18	0.99	35.69	17.42	3.36
9.0	15.81	36.20	21.00	19.17	5.18	0.99	36.26	18.01	3.37
9.1	15.81	36.16	20.57	18.13	5.14	0.98	37.28	18.09	3.34
9.2	15.73	36.17	19.25	17.11	5.15	0.98	35.74	18.58	3.35
9.3	15.70	36.32	18.29	16.30	5.23	0.98	37.51	17.96	3.38
9.6	15.55	36.53	17.01	14.87	5.38	0.97	36.49	18.39	3.45
9.7	15.49	36.69	16.22	14.51	5.47	0.98	35.65	18.79	3.44
9.8	15.42	36.64	15.56	13.85	5.44	0.97	36.01	18.25	3.45
9.9	15.42	36.47	15.54	13.37	5.31	0.97	35.35	18.74	3.51
10.0	15.42	36.36	15.44	13.12	5.23	0.96	36.47	18.87	3.50
10.5	15.15	36.53	13.43	11.82	5.32	0.96	35.28	19.24	3.61
11.0	15.04	36.47	12.04	11.25	5.23	0.96	33.78	18.97	3.70
11.5	14.88	36.13	10.98	10.51	4.97	0.96	32.70	19.03	3.74
12.0	14.77	36.02	10.29	10.15	4.86	0.96	31.75	18.65	3.87
12.5	14.72	35.78	9.84	10.04	4.70	0.97	30.79	19.18	3.94
13.0	14.70	35.51	9.59	10.02	4.53	0.98	30.35	18.64	4.04
13.5	14.76	34.71	10.08	10.01	4.15	0.96	30.15	19.36	4.10
14.0	14.88	34.50	11.22	10.15	4.09	0.95	30.12	19.38	4.13
14.5	15.10	33.90	13.00	10.30	3.83	0.93	29.52	19.30	4.18
15.0	15.42	33.27	15.43	11.05	3.56	0.93	28.43	20.01	4.24
15.5	15.66	32.48	19.32	11.69	3.26	0.92	28.50	20.07	4.13
16.0	15.93	31.86	21.69	13.19	3.05	0.93	27.90	20.08	4.08
16.5	16.06	31.54	19.20	14.22	2.92	0.94	27.76	20.33	4.17
17.0	16.01	31.20	15.37	13.16	2.78	0.94	26.95	19.43	4.23
17.5	15.69	31.14	11.90	11.76	2.73	0.94	27.01	18.70	4.36
18.0	15.19	31.39	9.22	9.74	2.72	0.95	26.95	18.28	4.71

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 124.70mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	14.98	40.85	10.87	7.48	7.55	0.88	28.20	16.25	6.16
5.2	15.36	39.97	12.66	8.27	6.95	0.88	29.12	16.89	5.49
5.4	15.66	39.39	14.65	9.13	6.60	0.90	28.86	16.95	4.99
5.6	15.87	38.84	16.90	9.76	6.24	0.90	28.46	17.21	4.63
5.8	16.02	38.57	18.97	10.35	6.08	0.91	28.33	16.80	4.31
6.0	16.15	38.06	20.69	10.91	5.74	0.92	28.08	17.02	4.13
6.2	16.25	37.75	21.28	11.52	5.55	0.93	29.94	16.99	3.90
6.4	16.35	37.58	21.51	12.01	5.42	0.93	30.04	17.13	3.75
6.6	16.42	37.30	21.14	12.62	5.25	0.94	29.75	17.18	3.63
6.8	16.47	37.05	21.19	13.25	5.11	0.95	29.82	17.04	3.55
7.0	16.54	36.94	21.46	14.33	5.07	0.96	29.55	16.71	3.43
7.2	16.57	36.68	21.69	15.18	4.94	0.96	29.09	16.62	3.42
7.4	16.61	36.63	22.86	16.67	4.94	0.97	30.09	17.02	3.32
7.6	16.64	36.50	24.42	18.28	4.89	0.98	30.49	16.49	3.30
7.8	16.65	36.48	26.61	20.51	4.91	0.98	30.33	16.94	3.25
8.0	16.66	36.39	28.40	23.93	4.88	0.99	30.21	16.67	3.26
8.2	16.63	36.46	29.53	28.62	4.94	0.99	30.39	16.89	3.24
8.3	16.64	36.20	29.78	31.90	4.80	0.99	30.43	16.82	3.22
8.4	16.61	36.55	27.65	30.74	5.00	0.99	30.70	16.70	3.20
8.8	16.50	36.56	23.16	22.52	5.03	0.99	30.34	16.88	3.25
8.9	16.50	36.22	22.29	20.84	4.83	0.99	30.86	16.39	3.31
9.0	16.44	36.26	21.54	19.40	4.86	0.98	30.13	16.88	3.35
9.1	16.43	36.19	20.96	18.45	4.81	0.98	30.78	17.01	3.31
9.2	16.36	36.26	19.50	17.22	4.85	0.98	30.55	17.50	3.33
9.3	16.34	36.29	18.69	16.47	4.86	0.98	30.69	16.88	3.32
9.6	16.19	36.51	17.40	15.09	5.00	0.97	31.10	17.28	3.41
9.7	16.13	36.65	16.59	14.68	5.08	0.97	30.50	17.65	3.44
9.8	16.08	36.66	16.00	14.01	5.08	0.97	30.34	17.18	3.44
9.9	16.08	36.46	15.96	13.51	4.94	0.96	30.44	17.71	3.45
10.0	16.07	36.31	15.89	13.28	4.85	0.96	30.50	17.86	3.43
10.5	15.83	36.49	13.76	11.98	4.93	0.96	30.76	18.26	3.57
11.0	15.74	36.37	12.42	11.34	4.81	0.96	31.59	17.97	3.66
11.5	15.60	36.04	11.37	10.56	4.58	0.95	30.91	18.01	3.72
12.0	15.53	35.92	10.72	10.17	4.46	0.95	30.62	17.64	3.83
12.5	15.51	35.59	10.30	10.04	4.26	0.96	29.42	18.14	3.89
13.0	15.52	35.31	10.12	9.95	4.10	0.96	29.79	17.58	4.00
13.5	15.60	34.51	10.79	9.94	3.76	0.94	29.91	18.17	4.06
14.0	15.73	34.16	12.14	10.11	3.65	0.93	30.26	18.17	4.05
14.5	15.97	33.79	14.36	10.17	3.47	0.91	30.05	17.98	4.10
15.0	16.31	33.05	17.57	10.88	3.18	0.91	29.88	18.61	4.17
15.5	16.59	32.21	23.45	11.47	2.88	0.91	30.66	18.72	4.12
16.0	16.92	31.63	28.99	12.80	2.67	0.91	30.51	18.64	4.06
16.5	17.13	31.20	24.16	13.75	2.52	0.92	30.56	18.81	4.12
17.0	17.16	30.77	18.52	12.53	2.36	0.90	30.37	17.82	4.10
17.5	16.93	30.70	13.94	11.02	2.31	0.89	30.78	17.22	4.34
18.0	16.48	30.92	10.49	9.00	2.29	0.88	31.00	16.97	4.61

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 128.59mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	13.97	40.93	11.22	7.48	8.60	0.87	40.30	17.72	6.22
5.2	14.38	39.95	13.16	8.29	7.80	0.88	39.05	18.23	5.59
5.4	14.70	39.38	15.31	9.12	7.38	0.89	40.26	18.38	5.05
5.6	14.93	38.84	17.76	9.76	6.97	0.90	37.28	18.65	4.68
5.8	15.09	38.50	19.95	10.31	6.71	0.91	37.69	18.42	4.37
6.0	15.23	38.00	21.60	10.90	6.33	0.92	36.72	18.62	4.19
6.2	15.33	37.69	21.74	11.49	6.10	0.93	33.92	18.64	3.94
6.4	15.44	37.48	21.87	11.98	5.94	0.93	35.60	18.81	3.80
6.6	15.51	37.21	21.15	12.62	5.76	0.94	36.94	18.88	3.69
6.8	15.56	36.92	21.56	13.24	5.58	0.95	35.10	18.70	3.63
7.0	15.63	36.83	21.79	14.39	5.55	0.96	33.32	17.32	3.50
7.2	15.66	36.54	22.58	15.21	5.40	0.97	32.74	18.34	3.44
7.4	15.69	36.51	24.24	16.88	5.41	0.97	32.22	18.67	3.41
7.6	15.72	36.40	27.11	18.42	5.37	0.98	32.34	18.13	3.33
7.8	15.73	36.30	31.54	21.02	5.34	0.98	33.92	18.59	3.30
8.0	15.73	36.31	40.14	24.58	5.37	0.99	33.01	17.40	3.31
8.2	15.68	36.39	38.83	30.85	5.47	0.99	32.29	18.62	3.30
8.3	15.69	36.16	34.92	35.32	5.32	0.99	32.68	18.58	3.33
8.4	15.65	36.48	29.15	32.03	5.53	0.99	31.39	18.43	3.31
8.8	15.52	36.51	22.86	21.99	5.59	0.99	31.93	18.73	3.36
8.9	15.51	36.24	21.43	20.41	5.40	0.99	30.67	18.21	3.39
9.0	15.45	36.20	20.56	19.05	5.39	0.99	32.15	18.80	3.40
9.1	15.44	36.19	20.19	18.00	5.37	0.98	30.91	18.87	3.38
9.2	15.38	36.17	18.98	16.99	5.36	0.98	32.04	19.33	3.37
9.3	15.33	36.33	17.92	16.23	5.45	0.98	30.71	18.74	3.38
9.6	15.16	36.52	16.69	14.74	5.60	0.98	30.74	19.17	3.50
9.7	15.09	36.66	15.84	14.43	5.70	0.98	31.55	19.54	3.52
9.8	15.05	36.64	15.32	13.76	5.66	0.97	30.13	19.02	3.47
9.9	15.03	36.52	15.21	13.27	5.56	0.97	31.39	19.48	3.50
10.0	15.03	36.42	15.18	13.01	5.49	0.97	30.98	19.60	3.49
10.5	14.74	36.54	13.16	11.71	5.56	0.96	30.69	19.90	3.67
11.0	14.61	36.54	11.76	11.16	5.50	0.97	29.80	19.67	3.76
11.5	14.44	36.21	10.73	10.44	5.23	0.97	29.45	19.72	3.80
12.0	14.31	36.11	10.01	10.11	5.13	0.97	29.02	19.41	3.94
12.5	14.24	35.84	9.56	10.02	4.95	0.98	28.81	20.16	3.97
13.0	14.20	35.62	9.27	10.02	4.80	0.99	28.23	19.42	4.15
13.5	14.25	34.84	9.71	10.02	4.42	0.98	28.05	20.12	4.17
14.0	14.35	34.60	10.74	10.17	4.35	0.96	27.75	20.14	4.13
14.5	14.56	34.02	12.38	10.31	4.08	0.94	28.66	20.11	4.25
15.0	14.86	33.49	14.54	11.08	3.86	0.94	27.74	20.68	4.30
15.5	15.08	32.54	17.88	11.72	3.49	0.93	26.47	20.97	4.22
16.0	15.33	32.11	19.37	13.31	3.33	0.94	25.94	20.83	4.16
16.5	15.42	31.78	17.27	14.37	3.20	0.95	26.68	21.20	4.22
17.0	15.32	31.42	14.06	13.43	3.04	0.96	25.09	20.34	4.27
17.5	14.98	31.39	11.08	12.15	3.01	0.97	24.98	19.50	4.50
18.0	14.46	31.62	8.67	10.12	2.98	0.98	24.97	19.02	4.77

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 132.70mA @ Temperature = 85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	12.16	41.14	12.16	7.93	11.19	0.88	39.08	16.96	8.05
5.2	12.60	40.27	14.22	8.54	10.09	0.89	30.45	17.56	7.37
5.4	12.97	39.51	16.56	9.31	9.24	0.90	31.00	17.60	6.82
5.6	13.22	38.98	18.71	9.70	8.61	0.90	31.76	17.86	6.46
5.8	13.43	38.47	21.15	10.38	8.10	0.91	33.95	17.53	6.08
6.0	13.58	38.01	22.16	10.81	7.64	0.92	52.90	17.71	5.87
6.2	13.70	37.72	22.14	11.63	7.39	0.93	32.24	17.64	5.64
6.4	13.80	37.38	21.25	11.99	7.06	0.94	29.73	17.80	5.49
6.6	13.87	37.06	21.40	12.58	6.81	0.95	29.74	17.82	5.37
6.8	13.95	36.95	21.02	13.73	6.75	0.96	29.70	17.68	5.29
7.0	13.99	36.76	22.11	14.49	6.63	0.96	30.44	17.39	5.70
7.2	14.02	36.45	22.64	16.18	6.46	0.97	32.56	17.26	5.10
7.4	14.03	36.42	25.55	17.24	6.48	0.98	30.75	17.58	5.10
7.6	14.04	36.29	29.03	19.73	6.44	0.98	29.85	17.20	5.02
7.8	14.03	36.21	36.88	21.93	6.43	0.99	28.97	17.65	5.00
8.0	13.99	36.22	35.34	26.00	6.48	0.99	28.68	17.44	4.99
8.2	13.93	36.42	30.38	31.34	6.69	0.99	28.56	17.66	5.01
8.3	13.92	36.23	27.38	32.16	6.55	1.00	28.62	17.61	5.04
8.4	13.88	36.33	24.10	28.58	6.64	1.00	28.80	17.69	5.01
8.8	13.71	36.42	20.58	20.57	6.75	0.99	28.40	17.98	5.08
8.9	13.66	36.19	19.40	18.84	6.58	0.99	28.14	17.59	5.12
9.0	13.59	36.28	19.11	17.58	6.66	0.99	28.04	17.84	5.19
9.1	13.54	36.34	18.46	16.73	6.71	0.98	28.32	17.77	5.11
9.2	13.47	36.55	17.54	16.08	6.88	0.98	28.07	18.36	5.15
9.3	13.42	36.43	16.79	14.97	6.77	0.98	28.35	17.80	5.17
9.6	13.24	36.60	15.95	13.75	6.94	0.97	27.81	18.32	5.31
9.7	13.16	36.74	15.27	13.34	7.05	0.97	27.76	18.72	5.30
9.8	13.10	36.77	15.26	12.67	7.08	0.96	28.02	18.04	5.31
9.9	13.07	36.77	15.41	12.44	7.08	0.96	27.59	18.26	5.34
10.0	13.04	36.60	14.97	12.46	6.95	0.96	27.82	18.36	5.30
10.5	12.72	36.70	13.39	11.22	7.06	0.96	27.50	18.79	5.50
11.0	12.47	36.73	12.23	10.79	7.13	0.96	27.11	18.77	5.63
11.5	12.25	36.62	11.47	10.46	7.08	0.96	26.56	18.76	5.76
12.0	12.05	36.49	10.86	10.04	6.99	0.96	26.16	18.51	5.85
12.5	11.89	36.25	10.33	10.01	6.84	0.97	25.83	18.82	5.99
13.0	11.75	36.20	9.92	9.69	6.78	0.97	25.60	18.51	6.09
13.5	11.71	35.54	10.03	9.79	6.33	0.97	25.64	19.03	6.19
14.0	11.79	35.06	10.46	10.33	6.06	0.98	24.80	19.10	6.26
14.5	11.97	34.77	11.55	10.54	5.88	0.97	25.09	19.01	6.28
15.0	12.25	34.11	13.39	11.42	5.51	0.97	25.40	19.35	6.35
15.5	12.45	33.37	15.62	12.30	5.12	0.96	24.82	19.34	6.31
16.0	12.56	33.09	17.23	12.48	4.96	0.95	25.30	19.54	6.23
16.5	12.62	32.60	16.15	16.04	4.80	0.99	24.08	19.48	6.32
17.0	12.41	32.37	13.68	15.85	4.72	1.00	23.76	19.44	6.37
17.5	11.93	32.39	11.09	14.85	4.79	1.03	24.56	18.33	6.66
18.0	11.38	32.70	9.68	13.61	5.07	1.04	25.81	17.74	6.97

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 132.35mA @ Temperature = 85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	12.30	40.91	12.16	7.97	10.74	0.88	31.09	16.46	8.00
5.2	12.74	40.11	14.22	8.63	9.79	0.89	31.26	17.09	7.32
5.4	13.10	39.32	16.48	9.38	8.92	0.90	31.79	17.09	6.78
5.6	13.36	38.75	18.73	9.87	8.29	0.90	33.34	17.37	6.36
5.8	13.55	38.32	20.99	10.49	7.88	0.91	34.86	16.95	6.07
6.0	13.70	37.86	22.23	11.03	7.43	0.92	29.67	17.14	5.84
6.2	13.82	37.56	22.19	11.78	7.18	0.93	36.26	17.07	5.61
6.4	13.92	37.23	21.69	12.22	6.87	0.94	30.90	17.22	5.40
6.6	13.99	36.95	21.72	12.86	6.66	0.95	30.41	17.25	5.32
6.8	14.07	36.92	21.61	14.02	6.66	0.96	30.70	17.07	5.20
7.0	14.11	36.68	22.48	14.89	6.51	0.97	34.56	16.79	5.12
7.2	14.14	36.46	23.35	16.53	6.40	0.98	32.59	16.65	5.09
7.4	14.15	36.37	26.04	17.91	6.38	0.98	33.60	16.99	5.01
7.6	14.16	36.23	29.78	20.32	6.32	0.99	32.47	16.59	4.95
7.8	14.15	36.05	37.53	23.17	6.23	0.99	29.59	17.07	4.96
8.0	14.12	36.24	37.23	28.13	6.41	0.99	29.22	16.84	4.92
8.2	14.07	36.29	30.35	41.19	6.49	0.99	29.33	17.05	4.94
8.3	14.07	36.09	27.63	36.35	6.34	1.00	29.60	17.02	4.99
8.4	14.05	35.91	25.03	28.82	6.21	0.99	30.21	17.06	4.95
8.8	13.88	36.17	20.83	20.23	6.43	0.99	29.61	17.32	4.99
8.9	13.84	36.08	19.87	18.96	6.37	0.99	29.21	16.93	5.05
9.0	13.77	36.19	19.44	17.74	6.47	0.99	28.81	17.18	5.12
9.1	13.72	36.26	18.73	16.72	6.52	0.98	29.68	17.13	5.06
9.2	13.67	36.32	17.96	15.94	6.56	0.98	28.44	17.72	5.09
9.3	13.62	36.18	17.22	14.95	6.44	0.98	29.86	17.14	5.07
9.6	13.46	36.34	16.31	13.73	6.58	0.97	28.67	17.66	5.22
9.7	13.37	36.44	15.59	13.33	6.67	0.97	28.26	18.03	5.20
9.8	13.34	36.37	15.52	12.81	6.60	0.96	29.44	17.34	5.25
9.9	13.30	36.50	15.55	12.66	6.71	0.96	28.09	17.58	5.26
10.0	13.27	36.51	15.29	12.59	6.73	0.96	28.87	17.71	5.25
10.5	13.00	36.46	13.80	11.21	6.68	0.95	28.28	18.12	5.41
11.0	12.79	36.51	12.61	10.80	6.75	0.95	27.70	18.13	5.55
11.5	12.61	36.34	11.74	10.51	6.63	0.96	26.99	18.10	5.63
12.0	12.42	36.19	10.98	10.20	6.52	0.96	26.51	17.86	5.78
12.5	12.29	36.01	10.40	10.18	6.40	0.97	26.12	18.16	5.86
13.0	12.18	35.81	9.95	9.93	6.23	0.98	25.90	17.83	6.06
13.5	12.18	35.23	10.12	10.05	5.85	0.98	25.99	18.39	6.09
14.0	12.29	34.98	10.52	10.56	5.72	0.98	25.12	18.44	6.14
14.5	12.47	34.31	11.60	10.94	5.32	0.98	25.98	18.31	6.18
15.0	12.77	33.61	13.29	12.16	4.96	0.98	25.99	18.70	6.27
15.5	12.97	33.05	15.27	13.13	4.69	0.97	26.38	18.68	6.20
16.0	13.09	32.64	16.99	13.40	4.49	0.96	25.65	18.92	6.14
16.5	13.09	32.54	16.38	16.32	4.54	0.99	24.46	18.86	6.18
17.0	12.82	32.25	14.01	14.73	4.43	0.99	23.96	18.75	6.26
17.5	12.28	32.36	11.04	14.16	4.56	1.02	25.22	17.66	6.53
18.0	11.61	32.73	9.41	13.02	4.89	1.04	26.41	17.33	6.87

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 5.25V, Id = 133.22mA @ Temperature = 85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
5.0	11.97	41.23	12.19	7.87	11.53	0.88	31.84	17.38	8.11
5.2	12.42	40.37	14.31	8.48	10.41	0.88	30.09	17.98	7.41
5.4	12.80	39.60	16.60	9.19	9.49	0.89	30.63	18.04	6.89
5.6	13.06	39.02	18.79	9.62	8.80	0.90	31.14	18.32	6.43
5.8	13.27	38.50	21.06	10.22	8.25	0.91	31.06	18.05	6.17
6.0	13.42	38.02	21.92	10.68	7.76	0.91	31.74	18.21	5.92
6.2	13.55	37.74	21.83	11.44	7.52	0.93	29.88	18.16	5.70
6.4	13.65	37.39	21.14	11.80	7.17	0.94	29.29	18.33	5.53
6.6	13.72	37.05	21.22	12.42	6.90	0.94	29.50	18.36	5.43
6.8	13.79	36.98	21.03	13.51	6.88	0.96	29.31	18.24	5.31
7.0	13.84	36.79	22.06	14.32	6.76	0.96	29.22	17.93	5.78
7.2	13.86	36.48	22.80	15.88	6.59	0.97	29.69	17.83	5.21
7.4	13.88	36.43	25.77	17.04	6.60	0.98	29.03	18.15	5.13
7.6	13.88	36.34	29.22	19.32	6.59	0.98	28.70	17.77	5.06
7.8	13.87	36.17	37.10	21.46	6.50	0.99	28.73	18.22	5.05
8.0	13.83	36.29	33.03	25.09	6.65	0.99	28.49	18.01	5.05
8.2	13.77	36.34	28.98	29.10	6.74	0.99	28.30	18.22	5.08
8.3	13.75	36.26	26.20	29.48	6.69	1.00	28.25	18.17	5.07
8.4	13.72	36.24	23.50	26.92	6.69	1.00	28.22	18.25	5.06
8.8	13.53	36.48	20.08	19.92	6.93	0.99	27.90	18.54	5.17
8.9	13.48	36.27	19.10	18.55	6.76	0.99	27.74	18.19	5.22
9.0	13.42	36.34	18.79	17.43	6.83	0.99	27.72	18.42	5.24
9.1	13.36	36.42	18.20	16.46	6.90	0.98	27.74	18.39	5.21
9.2	13.29	36.43	17.29	15.63	6.91	0.98	27.97	18.94	5.20
9.3	13.23	36.41	16.56	14.69	6.87	0.98	27.72	18.42	5.26
9.6	13.04	36.65	15.73	13.47	7.11	0.97	27.48	18.93	5.36
9.7	12.96	36.78	15.12	13.06	7.22	0.97	27.58	19.27	5.38
9.8	12.90	36.74	15.02	12.50	7.18	0.96	27.34	18.65	5.43
9.9	12.86	36.79	15.10	12.32	7.24	0.96	27.40	18.84	5.37
10.0	12.83	36.77	14.78	12.28	7.23	0.96	27.33	18.98	5.38
10.5	12.50	36.75	13.33	10.95	7.23	0.95	27.17	19.32	5.57
11.0	12.23	36.83	12.16	10.50	7.35	0.96	26.87	19.34	5.68
11.5	12.00	36.67	11.36	10.21	7.28	0.96	26.41	19.31	5.79
12.0	11.78	36.59	10.70	9.89	7.24	0.96	26.05	19.09	5.93
12.5	11.61	36.45	10.14	9.90	7.16	0.97	25.71	19.36	6.04
13.0	11.46	36.26	9.72	9.63	7.01	0.98	25.51	19.07	6.21
13.5	11.41	35.65	9.83	9.73	6.59	0.98	25.50	19.55	6.31
14.0	11.48	35.36	10.25	10.21	6.45	0.98	24.82	19.61	6.36
14.5	11.65	34.84	11.34	10.50	6.12	0.97	24.77	19.54	6.42
15.0	11.94	34.28	13.06	11.46	5.79	0.97	25.24	19.86	6.47
15.5	12.14	33.40	15.23	12.33	5.31	0.97	24.56	19.84	6.38
16.0	12.25	33.22	16.76	12.55	5.21	0.96	24.48	20.07	6.36
16.5	12.30	32.74	16.09	15.57	5.04	0.99	24.06	20.00	6.40
17.0	12.09	32.50	13.78	15.06	4.93	1.00	23.88	20.00	6.52
17.5	11.63	32.50	11.12	14.36	4.99	1.02	24.48	18.92	6.79
18.0	11.10	32.68	9.69	13.35	5.21	1.04	25.73	18.35	7.11


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
DQ849	.118 (3.00)	.118 (3.00)	.035 (0.89)	.008 (0.20)	.067 (1.70)	.067 (1.70)	.012 (0.30)	.046 (1.17)	.016 (0.41)	.026 (0.66)	.148 (3.76)	.148 (3.76)	.067 (1.70)

CASE #	P	Q	R	S	T	WT. GRAM
DQ849	.012 (0.30)	.031 (0.79)	.067 (1.70)	.061 (1.55)	.041 (1.04)	.02

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm.01$; 3 Pl. $\pm.004$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin plated. All models, (+) suffix. See Data sheet.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F104



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		7	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M125952	NEW RELEASE	01/08/10	MMG	RD
A	M132664	UPDATED PATTERN & COMPONENTS	12/16/11	PW	DJ
B	M135298	UPDATED DESCRIPTION & NOTE 2	01/11/12	AV	DJ

SUGGESTED MOUNTING CONFIGURATION FOR
DQ849 CASE STYLE, "08AM03" PIN CODE



- NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" $\pm$.001"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. 0402 AND 0805 CHIP COMPONENTS FOOTPRINTS ARE SHOWN FOR REFERENCE. VALUE OF COMPONENTS AS PER TB-547-X+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	MMG	01/06/10
	CHECKED	IL	01/08/10
	APPROVED	RD	01/08/10





Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 08AM03, DQ849, TB-547-X+

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.			
ASHEETA1.DWG REV:A DATE:01/12/95			

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-328	B
FILE:	98PL328	SCALE:	10:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



Schematic Diagram

NOTES:

1. SMA Female connectors.
2. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C or -45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	