



MMIC SURFACE MOUNT


Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

THE BIG DEAL

- Low Loss Bypass Mode Feature
- Low Noise Figure, Typ. 1.5 dB
- High OIP3, Typ. +33.6 dBm
- High P1dB, Typ. +22.9 dBm
- 3x3 mm 12-Lead QFN-Style Package




Generic photo used for illustration purposes only

APPLICATIONS

- Radar, EW, and ECM Defense Systems
- 5G Sub6, MIMO Wireless Infrastructure Systems
- Test & Measurement Equipment

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' TSY-83LN+ is a GaAs pHEMT based wide band, bypass mode capable, low noise MMIC amplifier with a combination of high IP3 and flat gain. Operating from 0.4 to 8 GHz, this amplifier features high dynamic range with 1.5 dB noise figure, 22 dB gain, +22.9 dBm P1dB, and +33.6 dBm OIP3. This combination of characteristics makes it ideal for sensitive, high dynamic range receiver applications where a gain stage may need to be quickly bypassed in the presence of high power RF signals. TSY-83LN+ operates on a single +5 V or +6 V supply, is well matched to 50Ω, and comes in a tiny, low profile 3x3 mm QFN-style package for ease of integration into dense circuit board layouts.

KEY FEATURES

| Feature | Advantages |
|--|---|
| Bypass Mode Feature | Allows the user to quickly switch to a low loss bypass path while keeping the power supply at constant voltage to reduce gain and protect the system in the presence of high power RF signals. |
| Low Noise Figure, Typ. 1.5 dB at 2 GHz | Extremely low noise figure provides minimal signal-to-noise degradation in amplification mode. |
| High OIP3, Typ. +33.6 dBm at 2 GHz | The combination of low noise figure and high IP3 makes this MMIC amplifier ideal for use in sensitive low noise receiver front ends where high dynamic range is of paramount importance. |
| Wide Bandwidth with Flat Gain: ±0.6 dB over 0.4 to 6 GHz | Enables a single amplifier to be used across many applications including aerospace and defense (Radar, SAT-COM, EW), broadband test instrumentation, telecommunications (5G Sub6), and more. |
| 3x3 mm 12-Lead QFN-Style Package | Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact with the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes. |

REV. OR
ECO-021311
TSY-83LN+
MCL NY
240326





MMIC SURFACE MOUNT

Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_{DD} = +6 V, AND Z₀ = 50Ω UNLESS NOTED OTHERWISE

| Parameter | Frequency (MHz) | Amplifier - ON | | | Amplifier - Bypass | Units |
|--|-------------------|----------------|-------|------|--------------------|-------|
| | | Min. | Typ. | Max. | Typ. | |
| Frequency Range | | 400 | | 8000 | 400-8000 | MHz |
| Gain | 400 | 21.0 | 21.8 | | -1.7 | dB |
| | 2000 | 21.4 | 22.3 | | -1.3 | |
| | 4000 | 21.2 | 22.3 | | -1.7 | |
| | 6000 | 22.1 | 23.0 | | -1.8 | |
| | 8000 ² | 18.9 | 21.0 | | -3.5 | |
| Input Return Loss | 400 | | 12.2 | | 9.3 | dB |
| | 2000 | | 16.4 | | 14.4 | |
| | 4000 | | 10.7 | | 13.3 | |
| | 6000 | | 16.3 | | 10.3 | |
| | 8000 ² | | 7.4 | | 5.8 | |
| Output Return Loss | 400 | | 14.3 | | 14.0 | dB |
| | 2000 | | 20.0 | | 15.3 | |
| | 4000 | | 15.8 | | 20.0 | |
| | 6000 | | 20.0 | | 10.9 | |
| | 8000 ² | | 16.9 | | 5.5 | |
| Isolation | 400-8000 | | 30.1 | | | dB |
| Output Power at 1 dB Compression (P _{1dB}) | 400 | | +22.4 | | +10.5 | dBm |
| | 2000 | | +22.9 | | +11.9 | |
| | 4000 | | +22.5 | | +13.8 | |
| | 6000 | | +20.0 | | +13.9 | |
| | 8000 ² | | +20.3 | | +14.1 | |
| Output Third-Order Intercept Point (P _{OUT} = 0 dBm/Tone) | 400 | | +32.2 | | +39.0 | dBm |
| | 2000 | | +33.6 | | +41.8 | |
| | 4000 | | +30.4 | | +41.6 | |
| | 6000 | | +26.2 | | +42.8 | |
| | 8000 ² | | +25.0 | | +41.0 | |
| Noise Figure | 400 | | 1.9 | | | dB |
| | 2000 | | 1.5 | | | |
| | 4000 | | 1.7 | | | |
| | 6000 | | 1.7 | | | |
| | 8000 ² | | 2.5 | | | |
| Device Operating Voltage (V _{DD}) | | | +6 | | +6 | V |
| Device Operating Current (I _{DD}) ³ | | | 104 | | 4 | mA |
| Enable Voltage (V _{EN}) ⁴ | | | +6 | | 0 | V |
| Enable Current (I _{EN}) | | | 4.6 | | 1.7 | mA |
| Device Current Adjust (I _{ADJ}) ⁵ | | | 13 | | 13 | μA |
| Device Current Variation Vs. Temperature ⁶ | | | -57 | | -57 | μA/°C |
| Device Current Variation Vs. Voltage ⁷ | | | 0.028 | | 0.028 | mA/mV |

1. Tested on Mini-Circuits Characterization Test Board TB-TSY-83LNC+. See Figure 2. Board loss de-embedded.

2. Tested on Mini-Circuits Characterization Test Board TB-TSY-832LNC+. See Figure 3. Board loss de-embedded.

3. Current at P_{IN} = -25 dBm. Increases to 150 mA at P_{1dB}.

4. V_{EN} must be equal to V_{DD} in Amplifier - ON mode.

5. I_{ADJ} is not intended as a voltage input port. Gain is nominal when I_{ADJ} is left open. When I_{ADJ} is open, there is a measured voltage of +1.4 V on the pin. To change the current, add a shunt resistor (see Figures 2 and 3).

6. (Current at +105°C - Current at -45°C) / (+150°C)

7. (Current at +6 V - Current at +5 V) / (+6 V - +5 V)





MMIC SURFACE MOUNT

Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

ELECTRICAL SPECIFICATIONS⁸ AT +25°C, V_{DD} = +5 V, AND Z₀ = 50Ω UNLESS NOTED OTHERWISE

| Parameter | Frequency (MHz) | Amplifier - ON | | | Amplifier - Bypass Typ. | Units |
|--|-------------------|----------------|-------|------|-------------------------|-------|
| | | Min. | Typ. | Max. | | |
| Frequency Range | | 400 | | 8000 | 400-8000 | MHz |
| Gain | 400 | 20.0 | 21.2 | | -1.6 | dB |
| | 2000 | 20.8 | 21.8 | | -1.3 | |
| | 4000 | 20.5 | 21.6 | | -1.6 | |
| | 6000 | 21.6 | 22.3 | | -1.8 | |
| | 8000 ⁹ | 18.5 | 20.6 | | -3.5 | |
| Input Return Loss | 400 | | 11.5 | | 9.3 | dB |
| | 2000 | | 15.2 | | 14.4 | |
| | 4000 | | 10.0 | | 13.5 | |
| | 6000 | | 15.2 | | 10.3 | |
| | 8000 ⁹ | | 7.4 | | 5.8 | |
| Output Return Loss | 400 | | 14.7 | | 13.8 | dB |
| | 2000 | | 20.0 | | 15.3 | |
| | 4000 | | 14.3 | | 20.0 | |
| | 6000 | | 18.5 | | 10.9 | |
| | 8000 ⁹ | | 16.8 | | 5.5 | |
| Isolation | 400-8000 | | 29.7 | | | dB |
| Output Power at 1 dB Compression (P1dB) | 400 | | +20.5 | | +10.9 | dBm |
| | 2000 | | +21.2 | | +12.2 | |
| | 4000 | | +20.5 | | +14.3 | |
| | 6000 | | +18.4 | | +14.4 | |
| | 8000 ⁹ | | +18.8 | | +14.9 | |
| Output Third-Order Intercept Point (P _{OUT} = 0 dBm/Tone) | 400 | | +31.4 | | +41.1 | dBm |
| | 2000 | | +31.5 | | +43.5 | |
| | 4000 | | +28.4 | | +42.5 | |
| | 6000 | | +24.3 | | +44.6 | |
| | 8000 ⁹ | | +24.6 | | +41.7 | |
| Noise Figure | 400 | | 1.8 | | | dB |
| | 2000 | | 1.5 | | | |
| | 4000 | | 1.6 | | | |
| | 6000 | | 1.7 | | | |
| | 8000 ⁹ | | 2.4 | | | |
| Device Operating Voltage (V _{DD}) | | | +5 | | +5 | V |
| Device Operating Current (I _{DD}) ¹⁰ | | | 76 | | 3 | mA |
| Enable Voltage (V _{EN}) ¹¹ | | | +5 | | 0 | V |
| Enable Current (I _{EN}) | | | 4.5 | | 1.7 | mA |
| Device Current Adjust (I _{ADJ}) ¹² | | | 13 | | 13 | μA |
| Device Current Variation Vs. Temperature ¹³ | | | -37 | | -37 | μA/°C |
| Device Current Variation Vs. Voltage ¹⁴ | | | 0.028 | | 0.028 | mA/mV |

8. Tested on Mini-Circuits Characterization Test Board TB-TSY-83LNC+. See Figure 2. Board loss de-embedded.

9. Tested on Mini-Circuits Characterization Test Board TB-TSY-832LNC+. See Figure 3. Board loss de-embedded.

10. Current at P_{IN} = -25 dBm. Increases to 140 mA at P1dB.11. V_{EN} must be equal to V_{DD} in Amplifier - ON mode.12. I_{ADJ} is not intended as a voltage input port. Gain is nominal when I_{ADJ} is left open. When I_{ADJ} is open, there is a measured voltage of +1.4 V on the pin. To change the current, add a shunt resistor (see Figures 2 and 3).

13. (Current at +105°C - Current at -45°C) / (+150°C)

14. (Current at +6 V - Current at +5 V) / (+6 V - +5 V)





MMIC SURFACE MOUNT







Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE






Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE






Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE





Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE





Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = V_{DD} = +6 V$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE






Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD} = +6 V$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE






Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = 0$ V and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = 0$ V and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE



Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = V_{DD} = +6 V$, and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = V_{DD} = +6 V$, and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





MMIC SURFACE MOUNT







Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





MMIC SURFACE MOUNT



Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V and $RI_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (Figure 2). All data taken at nominal conditions $V_{EN} = 0$ V, $V_{DD} = +6$ V, and $R_{ADJ} = \text{Open}$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 3). All data taken at nominal conditions $V_{EN} = 0\text{ V}$, $V_{DD} = +6\text{ V}$, and $R_{ADJ} = \text{Open}$ unless noted otherwise.



ABSOLUTE MAXIMUM RATINGS¹⁵

| Parameter | Ratings | |
|------------------------------------|--------------------|---------|
| Operating Temperature | -45°C to +105°C | |
| Storage Temperature | -65°C to +150°C | |
| Total Power Dissipation | 0.83 W | |
| Junction Temperature ¹⁶ | +150°C | |
| Input Power (CW) | Amplifier - ON | +22 dBm |
| | Amplifier - Bypass | +29 dBm |
| DC Voltage on RF-OUT | +14.5 V | |
| DC Voltage on RF-IN | +22 V | |
| DC Voltage on V _{DD} | +9 V | |
| Current I _{DD} | 180 mA | |
| DC Voltage on V _{EN} | +9 V | |
| Current I _{EN} | 60 mA | |
| Current I _{ADJ} | 10 mA | |

15. Permanent damage may occur if any of these are exceeded. Maximum ratings are not intended for continuous normal operations.

16. Peak temperature at top of Die.

THERMAL RESISTANCE

| Parameter | Ratings |
|--|----------|
| Thermal Resistance (θ_{JC}) ¹⁷ | 54.3°C/W |

17. θ_{JC} = (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

| | Class | Voltage Range | Reference Standard |
|-----|-------|------------------|-----------------------------|
| HBM | 1A | 250 V to < 500 V | ANSI/ESDA/JEDEC JS-001-2017 |
| CDM | C3 | ≥ 1000 V | JESD22-C101F |



ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C



MMIC SURFACE MOUNT

Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

FUNCTIONAL DIAGRAM




Figure 1. TSY-83LN+ Functional Diagram. Amplifier shown in ON mode.

PAD DESCRIPTION

| Function | Pad Number | Description (Refer to Figure 1) |
|--------------------------------|---------------|--|
| RF-IN | 2 | RF-IN Pad connects to RF-Input port. |
| RF-OUT | 8 | RF-OUT Pad connects to RF-Output port. |
| V _{DD} | 9 | DC Input Pad connects to device voltage input port. |
| V _{EN} | 11 | DC Input Pad connects to enable voltage input port. |
| I _{ADJ} ¹⁸ | 12 | Current Adjustment Pad connects to port, I _{ADJ} . Port left open for nominal operation. I _{ADJ} can be adjusted with the use of an external resistor (see Figures 2 and 3). |
| GND | Paddle, Index | Connects to ground. |
| NC | 1, 3-7, 10 | Not used internally. Connected to ground on test board. |

18. I_{ADJ} port not intended as a voltage input port. Permanent damage can occur with a voltage applied to this port.

CHARACTERIZATION BOARD




Figure 2. TSY-83LN+ Wide Band Characterization and Application Circuit. Used for characterization of device from 0.4 to 6 GHz

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X Microwave Network Analyzer.

Conditions:

1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/Tone at output.

Power ON/Power OFF Sequence


Caution: Permanent damage to the device will occur if the Power ON and Power OFF sequences are not followed.

Power ON:

- 1) Set V_{DD} = +5 or +6 V.
- 2) Set V_{EN} = +5 or +6 V for Amplifier-ON Mode or V_{EN} = 0 V for Bypass Mode.
- 3) Turn on V_{DD} and V_{EN}.
- 4) Apply RF signal.

Power OFF:

- 1) Turn off RF signal.
- 2) Turn off V_{DD} and V_{EN}.



| Component | Value | Size | Part Number | Manufacturer |
|---------------------------------|---------------|------|--------------------|--------------|
| C1 | 0.01 μF | 0402 | GRM155R71E103KA01D | Murata |
| C2 | 10 pF | 0402 | GJM1555C1H100JB01D | Murata |
| C3, C4 | 100 pF | 0402 | GRM1555C1H101JA01D | Murata |
| C5 | 0.4 pF | 0402 | GJM1555C1HR40WB01D | Murata |
| C6 | 0.3 pF | 0402 | GJM1555C1HR30WB01D | Murata |
| R1 | 0Ω | 0402 | RK73Z1ETTP | KOA Speer |
| RI _{ADJ} ¹⁹ | Not Populated | 0402 | -- | -- |
| L1 | 22 nH | 0402 | LQG15HS22NG02D | Murata |
| L2 | 39 nH | 0402 | 0402CS-39NXGRW | Coilcraft |

19. RI_{ADJ} resistor not needed for nominal operation. See I_{DD} versus RI_{ADJ} plot for typical current consumption.





CHARACTERIZATION BOARD




Figure 3. TSY-83LN+ Narrow Band Characterization and Application Circuit. Used for characterization of device from 5.5 to 8 GHz.

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X Microwave Network Analyzer.

Conditions:


1. Gain and Return Loss: $P_{IN} = -25$ dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/Tone at output.

| Component | Value | Size | Part Number | Manufacturer |
|-----------------------------|---------------|------|--------------------|--------------|
| C1 | 0.01 μ F | 0402 | GRM155R71E103KA01D | Murata |
| C2 | 10 pF | 0402 | GJM1555C1H100JB01D | Murata |
| C3, C4 | 100 pF | 0402 | GRM1555C1H101JA01D | Murata |
| C5 | 0.4 pF | 0402 | GJM1555C1HR40WB01D | Murata |
| C6 | 0.3 pF | 0402 | GJM1555C1HR30WB01D | Murata |
| R1 | 0 Ω | 0402 | RK73Z1ETTP | KOA Speer |
| $R_{I_{ADJ}}$ ²⁰ | Not Populated | 0402 | -- | -- |
| L1 | 2 nH | 0402 | 0402CS-2N0XGRW | Coilcraft |
| L2 | 5.6 nH | 0402 | 0402CS-5N6XGRW | Coilcraft |


²⁰ $R_{I_{ADJ}}$ resistor not needed for nominal operation. See I_{DD} versus $R_{I_{ADJ}}$ plot for typical current consumption.



CASE STYLE DRAWING



PCB Land Pattern




SUGGESTED LAYOUT, TOLERANCE TO BE WITHIN ±.002

Weight: .02 Grams

Dimensions are in inches [mm]. Tolerances in inches: 2 Pl. ±.01; 3 Pl.±.004

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MMIC SURFACE MOUNT

Low Noise Amplifier

TSY-83LN+

50Ω 0.4 to 8 GHz Bypass Mode Feature

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

| | |
|---|--|
| Performance Data and Graphs | Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style | DQ1225. Plastic package, exposed paddle, Lead Finish: Matte-Tin |
| RoHS Status | Compliant |
| Tape & Reel Standard quantities available on reel | F66 7" reels with 20, 50, 100, 200, 500, 1000, 2000, or 3000 devices |
| Suggested Layout for PCB Design | PL-775 |
| Evaluation Board | TB-TSY-83LNC+ (Wide Band, 0.4 to 6 GHz) TB-TSY-832LNC+ (Narrow Band, 5.5 to 8 GHz) Gerber File |
| Environmental Ratings | ENV08T1 |

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

