



Mini-Circuits

WIDEBAND


Low Noise Bypass Amplifier

TSS-53LNB+

50Ω 0.5 to 5 GHz

THE BIG DEAL

- Wideband: 0.5-5 GHz
- Built-in Bypass switching
- Low Noise figure: 1.4 dB typ. at 2.0 GHz
- High Gain: 21.7 dB typ. at 2 GHz
- Ultra Flat Gain: 0.7 dB from 0.7 to 2.1 GHz
- P1dB: +21 dBm typ. at 2.0 GHz
- Minimal matching components
- Specified over full band operation



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Wireless Base Station Systems
- Test and Measurement Systems
- Multi-Band Receivers

PRODUCT OVERVIEW

TSS-53LNB+ (RoHS compliant) is an advanced ultra-flat gain Low Noise wideband amplifier fabricated using E-PHEMT technology offering extremely high dynamic range over a broad frequency range. It has integrated switches enabling users to bypass the amplifier during high signal conditions. In addition, the TSS-53LNB+ has good input and output return loss over a broad frequency range without the need for external matching components. It is enclosed in a 12-lead 3x3 mm MCLP package for good thermal performance.

KEY FEATURES

Feature	Advantages
Ultra-wideband: 500 MHz – 5 GHz	Ideal for a wide range of receiver applications including military, commercial wireless, and instrumentation.
Very flat gain	Ideal for broadband or multi-band applications. Just one, cost-efficient model required for multiple frequency usage.
Minimal external matching components required. 15 dB return loss typ.	Minimizes the need for external matching networks, simplifying circuit designs, and enabling the amplifier to operate over multiple bands in a single application circuit.
High IP3: 48 dBm typ. (bypass mode)	Provides enhanced linearity over broad frequency range under high signal conditions.
Internal bypass switch feature	Unique design handles low to high signal levels with minimal noise distortion.
Built-in DC blocking cap at RF-Out port & separate pads for RF-Out & Vdd	Simplifies biasing eliminates need for Bias-Tee at output.
Compact size: 3 x 3 x 0.9 mm	Saves space in dense system layouts. Low inductance, repeatable transitions, and excellent thermal contact.



**WIDEBAND**

Low Noise Bypass Amplifier

TSS-53LNB+

Mini-Circuits®

ELECTRICAL SPECIFICATIONS¹ AT 25°C, ZO=50Ω AND VDD=5V, UNLESS OTHERWISE NOTED

Parameter	Condition (GHz)	Amplifier-ON			Amplifier-Bypass	Units
		Min.	Typ.	Max.	Typ.	
Frequency Range		0.5		5.0		GHz
Noise Figure	0.5		1.3		0.7	dB
	1.0		1.2		0.9	
	2.0		1.4		0.9	
	3.0		1.4		1.0	
	4.0		1.6		1.4	
	5.0		1.7		1.1	
Gain	0.5	—	22.8	—	-0.7	dB
	1.0	—	22.7	—	-0.7	
	2.0	19.5	21.7	23.9	-0.9	
	3.0	—	20.5	—	-1.0	
	4.0	—	19.5	—	-0.9	
	5.0	—	18.7	—	-1.0	
Gain Flatness	0.7 - 2.1		±0.7		±0.14	dB
Input Return Loss	0.5	—	16.0		25.8	dB
	1.0	—	15.1		18.5	
	2.0	10.5	14.5		12.3	
	3.0	—	13.1		11.1	
	4.0	—	14.5		14.5	
	5.0	—	16.9		16.9	
Output Return Loss	0.5		11.8		22.8	dB
	1.0		12.5		17.1	
	2.0		17.0		12.6	
	3.0		14.1		11.7	
	4.0		10.7		14.0	
	5.0		10.0		11.9	
Output Power @1dB compression AMP-ON ⁽²⁾ Input Power @1dB compression AMP-Bypass ⁽²⁾	0.5		21.1		32.0	dBm
	1.0		21.0		—	
	2.0		20.6		33.0	
	3.0		20.1		—	
	4.0		20.2		—	
	5.0		19.2		27.0	
Output IP3	0.5		35.1		48.0	
	1.0		34.5		48.4	
	2.0		33.9		45.2	
	3.0		32.7		42.9	
	4.0		33.4		42.0	
	5.0		30.9		40.8	
Device Operating Voltage (Vdd)		4.8	5.0	5.2	4.8-5.2 (5.0 typ.)	V
Device Operating Current (Id)			82	105	2	mA
Enable Voltage (Ve)			5.0		0	V
Enable Control Current (Ie)			2.0		0	mA
DC Current (Id) Variation Vs. Temperature ⁽³⁾			-19		—	μA/°C
DC Current (Id) Variation Vs. Voltage			0.008		—	mA/mV
Thermal Resistance, junction-to-ground lead			60		—	°C/W

(1) Measured on Mini-Circuits Characterization test board TB-780+. See Characterization Test Circuit (Fig. 1)

(2) Current increases at P1dB

(3) (Current at 85°C - Current at -45°C)/130)





WIDEBAND

Low Noise Bypass Amplifier

TSS-53LNB+

MAXIMUM RATINGS⁽⁵⁾

Parameter		Ratings
Operating Temperature (ground lead)		-40°C to 85°C
Storage Temperature		-65°C to 150°C
Total Power Dissipation		0.7 W
Input Power	Amplifier-ON	8 dBm (continuous), 19 dBm (5 min max.)
	Amplifier Bypass	16 dBm (continuous), 29 dBm (5 min max.)
DC Voltage Vdd		7.0 V
DC Voltage Enable		7.0 V
Max. Voltage on pad 8		15 V

(5) Permanent damage may occur if any of these limits are exceeded.
Electrical maximum ratings are not intended for continuous normal operation.


ENABLE VOLTAGE (VE) FIG. 1

	Min.	Typ.	Max.	Units
Amplifier-ON	4.5	5.0	5.5	V
Amplifier-Bypass	0	—	0.5	V

SWITCHING SPECIFICATIONS (RISE/FALL TIME)

Parameter		Min.	Typ.	Max.	Units
Amplifier ON to Bypass	OFF TIME (50% Control to 10% RF)	—	50	—	ns
	FALL TIME (90 to 10% RF)	—	12	—	
Amplifier Bypass to ON	ON TIME (50% Control to 90% RF)	—	740	—	ns
	RISE TIME (10% to 90% RF)	—	240	—	
Control Voltage Leakage		—	65	—	mV

SIMPLIFIED SCHEMATIC AND BONDING PAD DESCRIPTION



Function	Pad Number	Description (See Figure 2)
RF-IN	2	RF-Input pad. Connect to Ground Via L1. Add a DC blocking cap in series of appropriate value if required.
RF-OUT	8	RF-Output pad. No external DC blocking cap required.
Current Control	12	Control Current pad, voltage level on this pad sets the I _{dd} . Connect to pad 11 via 3.92 kΩ resistor.
Voltage Enable	11	Voltage Enable Pad. Voltage level on this pad determines Amplifier is ON or bypassed.
Vdd	9	Supply Voltage Pad. Connect to Vdd via L2.
Ground	1,3,4,5,6,7,10 Paddle	Connect to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.



Mini-Circuits

WIDEBAND

Low Noise Bypass Amplifier

TSS-53LNB+

CHARACTERIZATION TEST CIRCUIT




Fig 1. Block diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-780+)
Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.
3. Switching Time: Pin=-25 dBm at 500 MHz. Venable=4.5, 5.0, 5.5V at 10 kHz. Vd=4.75, 5.0 and 5.5V.

Component	Size	Value	Units
L1	0402	47	nH
L2	0402	56	nH
C1	0402	0.1	μF
C2	0402	10	pF
R1	0402	3.92	KΩ

RECOMMENDED APPLICATION CIRCUIT




Fig 2. Recommended Application Circuit.

Component	Size	Value	Units
L1	0402	47	nH
L2	0402	56	nH
R1	0402	3.92	kΩ
C1	0402	0.1	μF
C2	0402	10	pF
C3	0402	1000	pF
Schmitt Trigger	SN74LVC2G17DCKR Texas Instruments		—

PRODUCT MARKING



Marking may contain other features or characters for internal lot control





WIDEBAND

Low Noise Bypass Amplifier

TSS-53LNB+

Mini-Circuits

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle, terminal finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices
Suggested Layout for PCB Design	PL-421
Evaluation Board	TB-779+
Environmental Ratings	ENV12

ESD RATING


Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (pass 50V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = Ve = 5V, Id = 86.38 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.67	37.05	1.80	2.69	1.64	0.70	32.84	16.79	4.07
200.00	21.29	28.94	7.82	9.09	1.17	0.79	34.87	19.51	1.59
300.00	22.50	27.68	13.54	12.21	1.11	0.65	36.08	20.71	1.41
400.00	22.77	27.27	15.88	12.73	1.09	0.59	36.95	21.02	1.29
500.00	22.84	27.06	16.16	12.75	1.08	0.56	36.72	21.31	1.29
600.00	22.85	26.98	16.00	12.73	1.08	0.55	37.44	21.27	1.28
700.00	22.82	26.92	15.78	12.86	1.08	0.55	38.40	21.36	1.21
800.00	22.78	26.85	15.67	12.99	1.08	0.55	38.17	21.45	1.17
900.00	22.72	26.79	15.60	13.20	1.08	0.56	37.69	21.37	1.27
1000.00	22.65	26.82	15.59	13.47	1.08	0.57	36.34	21.23	1.18
1200.00	22.50	26.74	15.62	14.18	1.08	0.59	38.29	21.39	1.22
1400.00	22.32	26.68	15.74	15.04	1.09	0.62	36.43	21.23	1.21
1600.00	22.12	26.68	15.83	16.14	1.10	0.65	37.53	21.23	1.26
1800.00	21.92	26.67	15.89	17.33	1.11	0.68	36.42	20.97	1.28
2000.00	21.70	26.57	15.82	18.41	1.11	0.70	35.39	20.88	1.37
2200.00	21.47	26.61	15.69	18.99	1.13	0.73	35.16	21.10	1.34
2400.00	21.24	26.56	15.45	18.82	1.14	0.74	35.11	20.90	1.41
2600.00	20.99	26.55	15.22	18.08	1.15	0.76	34.29	20.59	1.46
2800.00	20.75	26.53	14.96	16.84	1.16	0.77	34.41	20.54	1.43
3000.00	20.53	26.55	14.67	15.62	1.17	0.77	33.99	20.28	1.43
3200.00	20.30	26.54	14.63	14.55	1.18	0.77	33.81	20.41	1.49
3400.00	20.08	26.48	14.73	13.69	1.19	0.77	34.11	20.34	1.50
3600.00	19.89	26.49	15.03	12.94	1.21	0.77	33.80	20.36	1.56
3800.00	19.69	26.54	15.46	12.39	1.23	0.77	34.20	20.61	1.56
4000.00	19.51	26.47	16.06	11.85	1.23	0.76	34.31	20.49	1.55
4200.00	19.34	26.53	17.03	11.58	1.25	0.77	33.98	20.38	1.58
4400.00	19.18	26.52	18.33	11.32	1.27	0.76	33.58	20.31	1.59
4800.00	18.85	26.56	19.64	11.07	1.29	0.78	33.15	19.95	1.71
5000.00	18.67	26.57	18.49	10.99	1.30	0.80	32.24	19.51	1.74
5200.00	18.44	26.76	16.42	11.03	1.32	0.83	32.74	19.53	1.86
5400.00	18.18	26.82	14.06	11.11	1.33	0.86	31.69	18.86	2.01
5600.00	17.84	27.12	11.87	11.14	1.36	0.91	31.15	18.50	2.12
5800.00	17.41	27.50	9.98	11.15	1.40	0.97	31.70	18.38	2.31
6000.00	16.83	28.04	8.38	11.09	1.46	1.04	31.13	18.10	2.67

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd =4.75V, Ve=5.0, Id =84.52 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.63	36.91	1.80	2.64	1.61	0.69	31.96	16.16	4.07
200.00	21.24	29.03	7.80	8.99	1.17	0.79	34.29	18.90	1.60
300.00	22.45	27.60	13.48	12.09	1.11	0.65	35.07	20.15	1.42
400.00	22.73	27.20	15.84	12.61	1.09	0.59	36.27	20.57	1.31
500.00	22.80	27.01	16.15	12.62	1.08	0.56	36.43	20.87	1.27
600.00	22.81	26.91	15.99	12.62	1.08	0.55	37.18	20.83	1.25
700.00	22.77	26.89	15.76	12.73	1.08	0.55	38.46	20.92	1.19
800.00	22.74	26.81	15.63	12.87	1.08	0.55	37.75	21.03	1.16
900.00	22.68	26.78	15.54	13.08	1.08	0.56	36.60	20.94	1.22
1000.00	22.61	26.73	15.51	13.36	1.08	0.57	36.07	20.81	1.19
1200.00	22.45	26.74	15.50	14.06	1.09	0.60	37.53	20.95	1.22
1400.00	22.28	26.67	15.59	14.91	1.09	0.62	35.96	20.81	1.22
1600.00	22.07	26.63	15.65	15.98	1.10	0.65	36.13	20.82	1.26
1800.00	21.86	26.66	15.68	17.13	1.11	0.68	35.89	20.56	1.25
2000.00	21.64	26.59	15.59	18.16	1.12	0.71	35.06	20.49	1.36
2200.00	21.41	26.56	15.48	18.71	1.13	0.73	34.72	20.71	1.33
2400.00	21.18	26.56	15.23	18.57	1.14	0.75	34.66	20.52	1.41
2600.00	20.93	26.53	15.04	17.85	1.15	0.76	33.98	20.20	1.47
2800.00	20.70	26.51	14.83	16.65	1.16	0.77	33.90	20.17	1.43
3000.00	20.47	26.50	14.59	15.46	1.17	0.78	33.86	19.91	1.40
3200.00	20.24	26.47	14.56	14.43	1.18	0.77	33.44	20.03	1.49
3400.00	20.02	26.44	14.69	13.56	1.19	0.77	33.97	19.96	1.50
3600.00	19.83	26.41	15.04	12.84	1.20	0.77	33.64	19.99	1.53
3800.00	19.62	26.44	15.50	12.31	1.22	0.77	33.98	20.22	1.56
4000.00	19.45	26.49	16.12	11.77	1.24	0.77	34.04	20.09	1.55
4200.00	19.27	26.49	17.06	11.47	1.25	0.77	33.47	20.01	1.57
4400.00	19.11	26.49	18.35	11.22	1.27	0.77	33.62	19.94	1.61
4800.00	18.78	26.46	19.37	10.95	1.28	0.78	33.01	19.60	1.68
5000.00	18.59	26.61	18.14	10.88	1.30	0.80	32.11	19.20	1.73
5200.00	18.36	26.71	16.07	10.90	1.32	0.83	32.42	19.20	1.84
5400.00	18.09	26.87	13.78	10.97	1.34	0.87	31.65	18.58	2.00
5600.00	17.74	27.11	11.65	10.99	1.36	0.92	30.85	18.16	2.10
5800.00	17.31	27.50	9.82	11.00	1.40	0.98	31.57	18.06	2.33
6000.00	16.73	28.06	8.27	10.93	1.47	1.04	30.73	17.77	2.66

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Ve=5.0V, Id = 88.2 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.68	37.17	1.80	2.78	1.68	0.72	32.98	17.26	4.40
200.00	21.30	29.08	7.83	9.30	1.18	0.80	34.78	20.02	1.60
300.00	22.51	27.61	13.56	12.49	1.11	0.65	35.87	21.15	1.43
400.00	22.77	27.35	15.90	13.00	1.10	0.60	36.07	21.42	1.32
500.00	22.84	27.09	16.17	13.00	1.09	0.57	37.22	21.70	1.30
600.00	22.85	27.04	16.02	12.99	1.08	0.56	37.38	21.64	1.29
700.00	22.82	26.98	15.81	13.11	1.08	0.56	38.68	21.73	1.21
800.00	22.79	26.94	15.71	13.23	1.08	0.56	37.89	21.81	1.18
900.00	22.73	26.92	15.67	13.46	1.08	0.57	37.72	21.74	1.22
1000.00	22.66	26.86	15.68	13.74	1.09	0.58	36.40	21.61	1.20
1200.00	22.51	26.79	15.74	14.46	1.09	0.60	38.64	21.75	1.24
1400.00	22.34	26.79	15.89	15.35	1.10	0.63	36.59	21.61	1.22
1600.00	22.13	26.70	16.02	16.47	1.10	0.65	37.19	21.59	1.29
1800.00	21.93	26.75	16.11	17.68	1.12	0.68	36.91	21.33	1.29
2000.00	21.71	26.68	16.05	18.82	1.12	0.70	35.64	21.24	1.40
2200.00	21.49	26.66	15.92	19.40	1.13	0.73	35.89	21.48	1.34
2400.00	21.26	26.60	15.67	19.20	1.14	0.74	35.58	21.23	1.45
2600.00	21.01	26.65	15.40	18.35	1.16	0.76	34.79	20.92	1.47
2800.00	20.78	26.60	15.09	17.05	1.17	0.77	34.66	20.90	1.42
3000.00	20.55	26.53	14.79	15.81	1.17	0.77	34.20	20.62	1.43
3200.00	20.33	26.64	14.68	14.72	1.19	0.78	33.82	20.75	1.48
3400.00	20.11	26.59	14.77	13.84	1.21	0.77	34.33	20.68	1.53
3600.00	19.91	26.57	15.05	13.09	1.22	0.77	34.36	20.72	1.58
3800.00	19.71	26.57	15.46	12.54	1.23	0.77	34.50	20.96	1.59
4000.00	19.54	26.54	16.01	12.03	1.24	0.76	34.46	20.82	1.58
4200.00	19.36	26.62	17.00	11.74	1.26	0.77	33.89	20.73	1.61
4400.00	19.21	26.56	18.33	11.48	1.27	0.77	33.84	20.63	1.61
4800.00	18.89	26.64	19.90	11.27	1.30	0.78	33.39	20.25	1.71
5000.00	18.71	26.77	18.86	11.19	1.32	0.80	32.62	19.78	1.77
5200.00	18.48	26.77	16.77	11.24	1.33	0.83	33.01	19.74	1.85
5400.00	18.22	26.99	14.33	11.33	1.36	0.87	32.04	19.02	2.02
5600.00	17.89	27.23	12.09	11.37	1.38	0.91	31.35	18.78	2.15
5800.00	17.46	27.57	10.14	11.36	1.41	0.97	32.00	18.71	2.36
6000.00	16.89	28.15	8.50	11.29	1.49	1.04	31.34	18.43	2.69

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = Ve = 5V, Id = 88.64 mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.19	36.68	1.65	2.30	1.49	0.62	40.69	16.82	3.58
200.00	21.01	28.70	8.06	7.70	1.15	0.71	39.60	19.29	1.16
300.00	22.12	27.47	13.26	9.45	1.10	0.58	40.47	20.53	1.09
400.00	22.31	27.13	13.47	9.34	1.09	0.52	40.36	20.97	0.98
500.00	22.36	26.97	12.83	9.28	1.08	0.50	42.54	21.27	1.00
600.00	22.37	26.87	12.45	9.27	1.07	0.48	47.11	21.25	0.99
700.00	22.36	26.83	12.27	9.37	1.07	0.49	42.88	21.36	0.92
800.00	22.34	26.76	12.29	9.50	1.07	0.49	47.56	21.44	0.88
900.00	22.31	26.75	12.36	9.70	1.08	0.50	43.30	21.31	0.85
1000.00	22.28	26.68	12.53	9.90	1.08	0.50	40.26	21.22	0.89
1200.00	22.18	26.60	12.90	10.33	1.08	0.52	43.39	21.39	0.89
1400.00	22.07	26.52	13.38	10.78	1.08	0.53	40.23	21.24	0.88
1600.00	21.94	26.48	14.06	11.50	1.09	0.56	41.76	21.23	0.97
1800.00	21.83	26.47	15.22	12.36	1.10	0.59	39.64	21.00	0.94
2000.00	21.69	26.34	16.22	13.43	1.11	0.61	37.71	20.87	0.99
2200.00	21.54	26.20	17.57	14.42	1.11	0.63	37.02	21.14	0.94
2400.00	21.39	26.19	18.93	15.52	1.12	0.65	36.80	20.95	1.03
2600.00	21.20	26.15	20.36	16.60	1.14	0.67	36.26	20.61	1.04
2800.00	21.03	26.12	21.49	17.41	1.15	0.69	35.51	20.56	1.02
3000.00	20.86	26.11	21.79	17.51	1.16	0.70	35.10	20.26	0.97
3200.00	20.68	26.09	22.12	17.05	1.17	0.71	34.83	20.32	1.02
3400.00	20.50	26.05	22.34	16.22	1.17	0.71	35.38	20.38	1.03
3600.00	20.32	25.99	22.42	15.35	1.18	0.71	34.90	20.30	1.11
3800.00	20.16	26.06	22.65	14.63	1.20	0.72	35.42	20.76	1.09
4000.00	20.01	26.05	23.43	13.93	1.21	0.72	35.55	20.68	1.09
4200.00	19.81	26.09	27.38	13.32	1.22	0.72	35.23	20.69	1.09
4400.00	19.69	26.05	33.92	12.93	1.23	0.72	35.03	20.63	1.09
4800.00	19.39	26.17	28.95	12.34	1.25	0.73	34.15	20.42	1.17
5000.00	19.26	26.26	23.12	12.20	1.26	0.75	33.21	19.90	1.23
5200.00	19.06	26.33	19.33	12.05	1.27	0.77	34.03	20.16	1.29
5400.00	18.85	26.52	16.45	11.99	1.29	0.80	32.91	19.58	1.44
5600.00	18.59	26.62	14.12	11.92	1.30	0.84	32.16	19.10	1.49
5800.00	18.30	26.96	12.09	12.18	1.33	0.90	32.88	18.91	1.67
6000.00	17.92	27.39	10.21	12.44	1.37	0.96	32.45	18.69	1.94

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Ve = 5.0V, Id = 86.26 mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.14	36.86	1.66	2.27	1.51	0.62	40.39	16.24	3.60
200.00	20.95	28.66	8.04	7.65	1.15	0.71	38.46	18.66	1.15
300.00	22.07	27.31	13.28	9.41	1.10	0.57	38.45	19.90	1.09
400.00	22.26	27.11	13.54	9.30	1.09	0.52	38.43	20.44	0.99
500.00	22.30	26.94	12.90	9.23	1.08	0.50	40.43	20.78	1.01
600.00	22.32	26.83	12.51	9.25	1.07	0.49	48.67	20.78	0.97
700.00	22.30	26.74	12.33	9.33	1.07	0.48	44.44	20.89	0.92
800.00	22.29	26.68	12.35	9.47	1.07	0.48	44.47	20.98	0.87
900.00	22.26	26.64	12.43	9.67	1.07	0.49	50.04	20.86	1.30
1000.00	22.22	26.63	12.58	9.87	1.07	0.50	39.43	20.77	0.87
1200.00	22.13	26.54	12.94	10.30	1.08	0.52	43.50	20.94	0.92
1400.00	22.02	26.51	13.42	10.75	1.09	0.54	38.61	20.80	0.89
1600.00	21.89	26.41	14.07	11.46	1.09	0.56	39.83	20.79	0.96
1800.00	21.77	26.30	15.18	12.32	1.10	0.58	39.00	20.58	0.91
2000.00	21.63	26.22	16.14	13.38	1.10	0.61	36.92	20.46	1.00
2200.00	21.48	26.21	17.42	14.34	1.12	0.63	37.17	20.72	0.92
2400.00	21.33	26.13	18.75	15.44	1.12	0.65	36.43	20.54	1.01
2600.00	21.14	26.10	20.02	16.48	1.13	0.67	35.31	20.18	1.04
2800.00	20.97	26.10	21.04	17.23	1.15	0.69	35.01	20.12	1.00
3000.00	20.80	26.00	21.40	17.31	1.15	0.70	35.04	19.87	0.97
3200.00	20.62	26.00	21.74	16.82	1.16	0.71	34.79	19.91	1.03
3400.00	20.44	25.94	22.07	16.01	1.17	0.71	35.09	19.96	1.01
3600.00	20.26	26.00	22.23	15.15	1.18	0.72	34.87	19.87	1.09
3800.00	20.11	26.01	22.60	14.44	1.19	0.72	35.13	20.33	1.09
4000.00	19.95	25.98	23.44	13.73	1.20	0.71	35.47	20.25	1.08
4200.00	19.75	26.10	27.55	13.17	1.23	0.72	34.95	20.22	1.09
4400.00	19.63	26.02	34.74	12.77	1.23	0.72	34.45	20.18	1.14
4800.00	19.33	26.11	28.18	12.18	1.25	0.73	34.17	20.03	1.18
5000.00	19.19	26.23	22.67	12.05	1.26	0.75	33.17	19.64	1.21
5200.00	18.99	26.24	19.03	11.90	1.27	0.77	33.80	19.82	1.29
5400.00	18.78	26.42	16.20	11.84	1.28	0.80	32.41	19.27	1.43
5600.00	18.52	26.67	13.91	11.77	1.30	0.85	31.85	18.78	1.51
5800.00	18.22	26.89	11.90	12.02	1.32	0.90	32.39	18.50	1.67
6000.00	17.84	27.37	10.07	12.27	1.37	0.97	32.15	18.27	1.97

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Ve =5.0V, Id = 90.87 mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.22	36.82	1.66	2.38	1.54	0.64	40.83	17.35	3.62
200.00	21.03	28.83	8.05	7.84	1.16	0.73	40.94	19.84	1.17
300.00	22.15	27.56	13.24	9.62	1.11	0.59	44.19	21.04	1.12
400.00	22.33	27.19	13.44	9.49	1.09	0.53	41.32	21.43	0.99
500.00	22.38	27.05	12.78	9.42	1.08	0.51	42.90	21.71	1.03
600.00	22.39	26.95	12.41	9.43	1.08	0.50	47.09	21.67	0.99
700.00	22.37	26.92	12.23	9.53	1.08	0.50	40.39	21.76	0.93
800.00	22.36	26.89	12.26	9.65	1.08	0.50	45.09	21.86	0.89
900.00	22.33	26.81	12.34	9.85	1.08	0.50	45.66	21.72	5.51
1000.00	22.30	26.73	12.50	10.07	1.08	0.51	41.81	21.64	0.93
1200.00	22.20	26.71	12.86	10.48	1.09	0.53	42.34	21.80	0.91
1400.00	22.09	26.65	13.39	10.94	1.09	0.55	40.79	21.65	0.90
1600.00	21.96	26.54	14.10	11.65	1.10	0.57	42.71	21.64	0.98
1800.00	21.85	26.52	15.27	12.54	1.11	0.60	41.64	21.39	0.95
2000.00	21.72	26.44	16.30	13.62	1.12	0.62	37.82	21.26	1.01
2200.00	21.56	26.35	17.69	14.61	1.12	0.64	37.80	21.54	0.96
2400.00	21.41	26.24	19.16	15.76	1.13	0.65	36.87	21.34	1.01
2600.00	21.22	26.27	20.63	16.86	1.14	0.68	36.37	20.98	1.06
2800.00	21.06	26.19	21.88	17.70	1.15	0.69	36.12	20.94	1.04
3000.00	20.89	26.16	22.14	17.82	1.16	0.70	35.51	20.64	0.99
3200.00	20.70	26.12	22.39	17.32	1.17	0.71	35.26	20.72	1.01
3400.00	20.52	26.08	22.55	16.47	1.18	0.71	35.56	20.78	1.04
3600.00	20.35	26.16	22.45	15.57	1.19	0.72	35.26	20.68	1.11
3800.00	20.19	26.14	22.61	14.83	1.20	0.72	35.61	21.17	1.10
4000.00	20.03	26.11	23.25	14.13	1.21	0.72	35.66	21.11	1.09
4200.00	19.83	26.16	27.01	13.52	1.23	0.72	35.43	21.04	1.13
4400.00	19.72	26.18	32.75	13.13	1.24	0.72	34.82	20.89	1.12
4800.00	19.42	26.23	29.90	12.54	1.26	0.74	34.52	20.45	1.19
5000.00	19.28	26.32	23.64	12.41	1.27	0.75	33.45	19.92	1.22
5200.00	19.09	26.40	19.75	12.26	1.28	0.77	34.06	20.19	1.29
5400.00	18.89	26.54	16.76	12.20	1.30	0.80	33.04	19.58	1.45
5600.00	18.63	26.71	14.36	12.14	1.31	0.84	32.27	19.11	1.54
5800.00	18.34	27.05	12.28	12.41	1.34	0.90	32.87	19.07	1.68
6000.00	17.97	27.40	10.35	12.68	1.38	0.96	32.70	18.77	1.97

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = Ve = 5V, Id = 84.93 mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.82	36.92	1.84	2.96	1.67	0.75	31.13	16.51	4.69
200.00	21.35	29.12	7.44	9.99	1.18	0.83	33.40	19.42	1.92
300.00	22.62	27.71	12.97	14.46	1.11	0.69	34.09	20.47	1.60
400.00	22.92	27.23	15.86	15.70	1.09	0.62	35.24	20.76	1.47
500.00	23.00	27.16	16.87	16.03	1.09	0.60	35.50	21.06	1.46
600.00	23.01	26.97	17.08	16.06	1.08	0.58	35.87	21.02	1.42
700.00	22.97	26.95	16.95	16.26	1.08	0.59	36.29	21.09	1.37
800.00	22.92	26.89	16.82	16.57	1.08	0.59	36.06	21.20	1.32
900.00	22.85	26.87	16.57	17.04	1.08	0.60	35.87	21.12	1.36
1000.00	22.77	26.80	16.33	17.58	1.08	0.61	35.17	20.99	1.37
1200.00	22.57	26.77	15.83	18.75	1.08	0.64	36.48	21.14	1.38
1400.00	22.36	26.78	15.26	20.01	1.09	0.67	35.34	20.98	1.38
1600.00	22.09	26.77	14.74	21.09	1.10	0.70	35.23	21.01	1.47
1800.00	21.85	26.82	14.09	21.59	1.11	0.73	35.11	20.75	1.48
2000.00	21.58	26.78	13.68	21.08	1.12	0.75	34.44	20.69	1.60
2200.00	21.30	26.75	13.19	19.70	1.13	0.77	34.30	20.84	1.57
2400.00	21.03	26.73	12.77	18.12	1.14	0.79	33.90	20.66	1.65
2600.00	20.73	26.75	12.49	16.68	1.15	0.80	33.72	20.34	1.69
2800.00	20.46	26.72	12.17	15.26	1.16	0.81	33.62	20.28	1.65
3000.00	20.20	26.75	11.93	14.06	1.18	0.81	33.51	20.05	1.63
3200.00	19.96	26.84	11.88	13.09	1.20	0.82	33.20	20.13	1.79
3400.00	19.72	26.67	11.98	12.37	1.20	0.81	33.33	20.07	1.81
3600.00	19.51	26.70	12.24	11.75	1.22	0.80	33.16	20.04	1.85
3800.00	19.32	26.69	12.58	11.29	1.23	0.80	33.24	20.10	1.88
4000.00	19.11	26.71	13.07	10.89	1.25	0.79	33.58	19.96	1.86
4200.00	18.93	26.73	13.85	10.71	1.27	0.80	33.20	19.76	1.90
4400.00	18.77	26.65	14.73	10.54	1.28	0.79	32.87	19.65	1.90
4800.00	18.40	26.69	15.60	10.31	1.31	0.81	32.10	18.99	1.98
5000.00	18.19	26.79	15.10	10.24	1.32	0.83	31.16	18.50	2.07
5200.00	17.91	26.91	13.74	10.23	1.34	0.86	31.36	18.29	2.19
5400.00	17.57	27.09	11.98	10.24	1.36	0.90	30.53	17.74	2.39
5600.00	17.15	27.44	10.30	10.14	1.40	0.95	29.65	17.28	2.52
5800.00	16.62	27.87	8.75	10.00	1.45	1.01	30.03	17.19	2.78
6000.00	15.93	28.50	7.43	9.83	1.55	1.06	29.14	16.77	3.20

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Ve =5.0V, Id = 83.15 mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.79	37.05	1.84	2.91	1.69	0.75	30.60	16.00	4.77
200.00	21.30	29.10	7.42	9.89	1.18	0.83	33.10	18.89	1.90
300.00	22.58	27.60	12.90	14.28	1.11	0.68	34.05	20.01	1.61
400.00	22.88	27.24	15.78	15.52	1.09	0.62	34.76	20.36	1.46
500.00	22.96	27.05	16.77	15.86	1.08	0.60	34.69	20.66	1.43
600.00	22.97	26.95	16.96	15.92	1.08	0.59	35.31	20.62	1.39
700.00	22.93	26.90	16.86	16.12	1.08	0.59	36.01	20.69	1.35
800.00	22.88	26.83	16.69	16.41	1.08	0.59	35.79	20.81	1.33
900.00	22.81	26.75	16.40	16.87	1.07	0.60	35.03	20.74	1.37
1000.00	22.73	26.77	16.14	17.40	1.08	0.61	34.56	20.59	1.37
1200.00	22.52	26.79	15.63	18.54	1.09	0.64	36.14	20.74	1.37
1400.00	22.31	26.75	15.07	19.75	1.09	0.67	34.85	20.62	1.38
1600.00	22.04	26.68	14.53	20.80	1.10	0.70	34.84	20.61	1.47
1800.00	21.79	26.78	13.91	21.25	1.11	0.73	35.13	20.39	1.49
2000.00	21.52	26.67	13.50	20.75	1.11	0.75	34.18	20.29	1.60
2200.00	21.24	26.71	13.04	19.44	1.13	0.78	33.99	20.46	1.56
2400.00	20.97	26.69	12.64	17.96	1.14	0.79	34.08	20.28	1.68
2600.00	20.67	26.79	12.37	16.54	1.16	0.81	33.22	19.98	1.70
2800.00	20.40	26.68	12.10	15.14	1.16	0.81	33.26	19.92	1.66
3000.00	20.14	26.75	11.86	13.96	1.18	0.82	33.02	19.71	1.62
3200.00	19.90	26.76	11.84	13.01	1.19	0.82	32.57	19.78	1.76
3400.00	19.65	26.69	11.97	12.27	1.20	0.81	33.22	19.72	1.80
3600.00	19.45	26.65	12.24	11.67	1.21	0.80	32.83	19.67	1.84
3800.00	19.25	26.73	12.61	11.20	1.24	0.80	33.26	19.76	1.85
4000.00	19.04	26.70	13.12	10.80	1.25	0.80	33.52	19.63	1.87
4200.00	18.86	26.58	13.89	10.62	1.26	0.79	33.04	19.44	1.88
4400.00	18.70	26.62	14.78	10.43	1.28	0.79	32.99	19.33	1.92
4800.00	18.32	26.61	15.52	10.19	1.30	0.81	31.77	18.71	1.99
5000.00	18.10	26.73	14.94	10.14	1.32	0.83	30.97	18.19	2.07
5200.00	17.82	26.82	13.55	10.11	1.33	0.86	31.14	18.07	2.20
5400.00	17.47	27.05	11.81	10.09	1.36	0.90	30.54	17.54	2.38
5600.00	17.04	27.40	10.15	10.00	1.40	0.95	29.57	17.08	2.52
5800.00	16.51	27.80	8.64	9.88	1.44	1.01	29.87	16.89	2.77
6000.00	15.82	28.39	7.35	9.70	1.53	1.06	29.03	16.50	3.20

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 5.25V, Ve = 5.0V, Id = 86.69 mA @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
100.00	13.82	37.21	1.83	3.06	1.74	0.78	31.27	16.94	4.58
200.00	21.35	29.14	7.45	10.23	1.19	0.84	33.27	19.84	1.90
300.00	22.62	27.67	13.00	14.79	1.11	0.69	34.68	20.85	1.63
400.00	22.92	27.26	15.95	16.06	1.09	0.62	35.51	21.12	1.50
500.00	23.00	27.21	16.91	16.38	1.09	0.61	35.14	21.39	1.46
600.00	23.01	27.11	17.14	16.42	1.09	0.60	36.35	21.35	1.43
700.00	22.97	27.03	17.08	16.60	1.08	0.60	36.12	21.41	1.37
800.00	22.92	26.97	16.93	16.92	1.08	0.60	36.36	21.53	1.33
900.00	22.85	26.89	16.68	17.39	1.08	0.60	35.78	21.48	1.37
1000.00	22.77	26.90	16.47	17.97	1.09	0.62	35.10	21.32	1.39
1200.00	22.58	26.91	16.01	19.14	1.09	0.65	36.37	21.45	1.39
1400.00	22.37	26.81	15.48	20.47	1.10	0.67	35.33	21.30	1.39
1600.00	22.11	26.84	14.93	21.59	1.11	0.70	35.70	21.31	1.49
1800.00	21.86	26.87	14.30	22.10	1.12	0.73	35.76	21.09	1.51
2000.00	21.60	26.81	13.87	21.52	1.12	0.75	34.52	20.99	1.62
2200.00	21.33	26.82	13.35	19.97	1.14	0.77	34.28	21.14	1.59
2400.00	21.05	26.77	12.92	18.35	1.14	0.79	34.34	20.97	1.66
2600.00	20.75	26.87	12.61	16.86	1.17	0.81	33.93	20.65	1.71
2800.00	20.49	26.78	12.27	15.41	1.17	0.81	33.92	20.58	1.70
3000.00	20.23	26.83	11.99	14.21	1.19	0.82	33.80	20.38	1.67
3200.00	19.99	26.85	11.92	13.22	1.20	0.81	33.15	20.46	1.77
3400.00	19.75	26.79	12.02	12.50	1.21	0.81	33.52	20.40	1.83
3600.00	19.54	26.79	12.24	11.89	1.23	0.80	33.35	20.34	1.87
3800.00	19.35	26.76	12.59	11.41	1.24	0.80	33.70	20.40	1.88
4000.00	19.14	26.69	13.05	11.03	1.25	0.79	33.69	20.21	1.90
4200.00	18.96	26.75	13.84	10.87	1.28	0.80	33.42	20.05	1.92
4400.00	18.80	26.73	14.74	10.70	1.29	0.79	33.03	19.87	1.93
4800.00	18.44	26.73	15.70	10.49	1.32	0.81	32.08	19.23	2.03
5000.00	18.23	26.82	15.27	10.43	1.33	0.83	31.16	18.69	2.09
5200.00	17.96	26.96	13.94	10.43	1.35	0.86	31.20	18.39	2.20
5400.00	17.62	27.16	12.16	10.44	1.38	0.90	30.54	17.83	2.40
5600.00	17.20	27.52	10.45	10.34	1.42	0.95	29.73	17.42	2.53
5800.00	16.67	27.91	8.85	10.21	1.47	1.00	30.10	17.37	2.77
6000.00	15.99	28.52	7.51	10.03	1.56	1.06	29.10	16.97	3.19


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000


Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION		REVISIONS				
	REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
	OR	M146226	NEW RELEASE	05/05/14	ITG	SK


**SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12AM01" PIN CODE**



NOTES:



1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" $\pm$.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-779+.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235			
DIMENSIONS ARE IN INCHES		DRAWN	ITG	04/28/14		PL, 12AM01, DQ1225, TB-779+			
TOLERANCES ON:		CHECKED	IL	04/30/14					
2 PL DECIMALS ±		APPROVED	SK	05/05/14					
3 PL DECIMALS ± .005									
ANGLES ±									
FRACTIONS ±						SIZE A CODE IDENT 15542 DRAWING NO: 98-PL-421 REV: OR			
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.		ASHEETA1.DWG REV:A		DATE:01/12/95		FILE: 98PL421 SCALE: 12:1 SHEET: 1 OF 1			

Evaluation Board and Circuit



Schematic Diagram

COMPONENT		VALUE	SIZE
DUT		TSS-53LNB+	
C1		.1 uF	0402
C2		10 pF	
C3		.001 uF	
L1		47 nH	
L2		56 nH	
R1		3.92 kOhm	0603
R2,R3		10 kOhm	
R4		1 kOhm	
D1	MCL	B40-28-5230B+	
	ON SEMI	MMSZ5230BT1G	
D2	MCL	B43-4101PT1+	
	ON SEMI	NTS4101PT1G	
D3	MCL	B40-ESD7L5+	
	ON SEMI	ESD7L5.0DT5G	
Q2	MCL	B49-SN74-17+	
	TEXAS INSTRUMENT	SN74LVC2G17DCKR	

Notes:

- 50 Ohm SMA Female connectors.
- PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D