

Low Noise, Medium Current, High IP3


E-PHEMT Transistor Die

TAV2-501-D+

50Ω 0.4 to 3.9 GHz

The Big Deal

- Single Positive Supply Voltage
- Low Noise Figure, 0.6 dB at 0.9 GHz
- Gain, 15 dB at 2 GHz
- High Output IP3, 43 dBm at 2 GHz
- P1dB, 30.6 dBm at 0.9 GHz, 27.7 dBm at 2 GHz
- External biasing and matching required



Product Overview

Mini-Circuits' TAV2-501-D+ is a MMIC E-PHEMT* transistor die with an operating frequency range from 0.4 to 3.9 GHz. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding cellular infrastructure.

Key Features

Feature	Advantages
Wideband, 0.4 to 3.9 GHz	A single device covers many wireless communications bands including cellular, ISM, GSM, WCDMA, WiMax, WLAN, and more.
High IP3 vs. DC power consumption • +42.9 dBm at 0.9 GHz • +42.9 dBm at 2 GHz • +43.9 dBm at 3.9 GHz For additional data, see Tables 1-4 on Page 5	The TAV2-501-D+ matches industry leading IP3 performance relative to device size and power consumption. Enhanced linearity over a broad frequency range makes the device ideal for use in: • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems
High P1dB • +30.6 dBm at 0.9 GHz • +27.7 dBm at 2 GHz • +30.0 dBm at 3.9 GHz For additional data, see Tables 1-4 on Page 5	Results in a very dynamic range preventing amplifier saturation under strong interfering signals.
Combines high gain (23.5 dB) with very low Noise Figure (0.6 dB)	The unique combination of high gain and low Noise Figure results in lower overall system noise.
Unpackaged Die	Enables the user to integrate the amplifier directly into hybrids

* Enhancement mode Pseudomorphic High Electron Mobility Transistor.



Low Noise, Medium Current, High IP3 E-PHEMT Transistor Die


TAV2-501-D+

Product Features

- Single Positive Supply Voltage
- Low Noise Figure, 0.6 dB at 0.9 GHz
- Gain, 15 dB at 2 GHz
- High Output IP3, 42.9 dBm at 2 GHz
- P1dB, 30.6 dBm at 0.9 GHz, 27.7 dBm at 2 GHz
- External biasing and matching required

Typical Applications

- Cellular
- ISM
- GSM
- WCDMA
- WiMax
- WLAN



+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

General Description


Mini-Circuits' TAV2-501-D+ is a MMIC E-PHEMT* transistor die with an operating frequency range from 0.4 to 3.9 GHz. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding cellular infrastructure.

Simplified Schematic and Pad description



Pad#	Description
1 & 5	GATE used for RF-IN
2 & bottom of die	SOURCE Terminal, normally connected to ground
3 & 4	DRAIN used for RF-OUT

Bonding Pad Position



Dimensions in μm , Typical

L1	L2	L3	L4	H1	H2	H3
154	475	759	950	84	446	530

Thickness	Die size	Pad Size 1 & 3	Pad size 2	Pad Size 4 & 5
100	950 x 530	144 x 69	301 x 69	59 x 64

Electrical Specifications at $T_{AMB}=25^{\circ}\text{C}$

Symbol	Parameter	Condition	Min.	Typ.	Max.	Units
DC Specifications						
V_{TH}	Threshold Voltage	$V_{DS}=4.5\text{V}$, $I_{DS}=28\text{ mA}$		0.38		V
I_{DSS}	Saturated Drain Current	$V_{DS}=4.5\text{V}$, $V_{GS}=0\text{ V}$	—	0.5	—	μA
G_M	Transconductance	$=4.5\text{V}$, $G_m = \Delta I_{DS} / \Delta V_{GS}$, $\Delta V_{GS} = V_{GS1} - V_{GS2}$, $V_{GS1} = V_{GS\text{ typ}} - 0.05$, $V_{GS2} = V_{GS\text{ typ}} + 0.05$	—	2600	—	mS
I_{GSS}	Gate leakage Current	$V_{GD}=V_{GS}=-6.7\text{V}$	—	65		μA



RF & DC Specifications, $Z_0=50\text{ Ohms}$					
Parameter	Condition (GHz)	$V_{DS} = 4.5\text{V}$, $I_{DS} = 280\text{mA}$			Units
		Min.	Typ.	Max.	
Gain	0.9		23.5 ^{2,4}		dB
	2.0		15.1 ³		
P1dB	0.9		30.6 ^{2,4}		dBm
	2.0		27.7 ³		
OIP3 Pout=0dBm/Tone	0.9		42.9 ^{2,5}		dBm
	2.0		42.9 ³		
Noise Figure	0.9		0.6 ¹		dB
	2.0		1.3 ³		
Power Added Efficiency	0.9		45 ^{2,4}		dB
	2.0		45 ³		
I_{DS}	DC		280		mA
V_{GS}	DC	0.39	0.52	0.65	V

- For measurements at 0.9 GHz, die is packaged in 2x2mm, 8-lead MCLP package and soldered on Mini-Circuits characterization board TB-TAV2-501+ with no optimization.
- For measurements at 0.9 GHz, die is packaged in 2x2 mm, 8-lead MCLP package and soldered on Mini-Circuits characterization board TB-TAV2-501+ with load and source pull test (See Fig. 1).
- For measurements at 2 GHz, die is packaged in 2x2 mm, 8-lead MCLP package and soldered on Mini-Circuits matching circuit test board TB-TAV2-501M+ (See Fig. 2).
- Measurements at 0.9 GHz obtained for optimized P1dB. Die is packaged in 2x2mm, 8-lead MCLP package and soldered on Mini-Circuits characterization board TB-TAV2-501+.
- Measurements at 0.9 GHz obtained for optimized IP3. Die is packaged in 2x2mm, 8-lead MCLP package and soldered on Mini-Circuits characterization board TB-TAV2-501+.

Absolute Maximum Ratings^{1,2,3,6}

Symbol	Parameter	Max.	Units
V_{DS} ⁷	Drain-Source Voltage	7	V
V_{GS} ⁷	Gate-Source Voltage at $V_{DS}=4.5\text{V}$	-5 to +0.8	V
I_{DS} ⁷	Drain Current at $V_{DS}=4\text{V}$	500	mA
I_{GS}	Gate Current	60	μA
P_{DISS}	Total Dissipated Power	2.4	mW
P_{IN} ⁸	RF Input Power	28	dBm
T_{CH}	Channel Temperature	150	$^{\circ}\text{C}$
T_{OP}	Operating Temperature	-40 to 85	$^{\circ}\text{C}$
T_{STD}	Storage Temperature	-65 to 150	$^{\circ}\text{C}$
θ_{JC}	Thermal Resistance	23	$^{\circ}\text{C/W}$

- Operation of this device above any one of these parameters may cause permanent damage.
- Assumes DC quiescent conditions.
- I_{GS} is limited to 60 μA during test.



VDS, V (nom)	4.5
IDS, mA (nom)	280
R1	15 Ω
C1	2.4 pF
C2	2.4 pF
C3	2.2 μ F
C4	2.2 μ F
L1	1.2 nH
L2	1.5 nH
L3	15 nH
L4	47 nH

Table 1: Optimum OIP3 at 4.5 V, 280 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	45.11	19.98	29.85	49.66	0.694 $\angle$ - 114.29°	0.693 $\angle$ - 91.12°
2.0	46.32	14.22	28.68	48.82	0.842 $\angle$ 29.84°	0.715 $\angle$ 35.13°
2.4	44.64	11.23	27.44	42.12	0.724 $\angle$ 123.43°	0.638 $\angle$ 75.56°
3.9	43.89	11.00	27.83	42.76	0.884 $\angle$ - 108.07°	0.679 $\angle$ - 114.78°

Table 2: Optimum P1dB at 4.5 V, 280 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	40.18	22.77	30.03	52.30	0.658 $\angle$ - 87.51°	0.690 $\angle$ - 73.64°
2.0	41.52	17.02	30.23	56.73	0.743 $\angle$ 39.55°	0.715 $\angle$ 43.14°
2.4	41.11	15.10	30.52	53.56	0.742 $\angle$ 92.52°	0.720 $\angle$ 93.56°
3.9	39.53	11.72	29.95	46.67	0.759 $\angle$ - 95.66°	0.687 $\angle$ - 96.87°


Table 3: Optimum OIP3 at 4.5 V, 400 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	47.67	16.84	29.54	50.28	0.645 $\angle$ - 138.14°	0.602 $\angle$ - 69.95°
2.0	45.77	15.97	29.23	50.14	0.649 $\angle$ 40.96°	0.613 $\angle$ 40.33°
2.4	48.05	13.40	29.66	48.74	0.803 $\angle$ 112.01°	0.619 $\angle$ 92.12°
3.9	46.32	11.40	29.57	46.28	0.884 $\angle$ - 108.07°	0.684 $\angle$ - 105.84°

Table 4: Optimum P1dB at 4.5 V, 400 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	42.99	23.04	30.01	45.83	0.658 $\angle$ -87.51°	0.785 $\angle$ - 87.47°
2.0	42.01	18.53	30.68	48.45	0.833 $\angle$ 43.23°	0.827 $\angle$ 42.17°
2.4	44.45	17.26	30.16	55.62	0.874 $\angle$ 94.67°	0.726 $\angle$ 86.88°
3.9	43.13	12.90	30.83	49.36	0.875 $\angle$ -101.14°	0.784 $\angle$ - 99.28°

Assembly Diagram



Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC E-PHEMT transistor dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

Additional Detailed Technical Information*additional information is available on our dash board.*

Performance Data	Data Table	
	Swept Graphs	
	S-Parameter (S2P Files) Data Set	
Case Style	Die	
Die Ordering and packaging information	Quantity, Package	Model No.
	Small, Gel - Pak: 5,10,50,100 KGD*	TAV2-501-DG+
	Medium†, Partial wafer: KGD*<2160	TAV2-501-DP+
	Large†, Full Wafer	TAV2-501-DF+
	†Available upon request contact sales representative	
	Refer to AN-60-067	
Environmental Ratings	ENV80	

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria ($V_{DS} = 2V$, $I_D = 214$ mA) and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1B (500V to <1000V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard 2x2 mm, 8-Lead MCLP package.

Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bond and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 281mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability	
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure
400	20.17	37.00	0.50	2.30	0.20	0.76
450	19.15	37.03	0.51	2.31	0.25	0.76
500	18.22	37.28	0.53	2.31	0.29	0.76
550	17.39	37.25	0.53	2.31	0.32	0.76
600	16.64	36.94	0.54	2.32	0.34	0.76
650	15.94	37.14	0.56	2.32	0.37	0.76
700	15.29	37.05	0.58	2.33	0.41	0.76
750	14.69	36.86	0.57	2.36	0.44	0.77
800	14.13	37.09	0.59	2.36	0.48	0.77
850	13.62	37.13	0.59	2.34	0.51	0.77
900	13.12	37.25	0.59	2.38	0.56	0.77
950	12.65	36.96	0.60	2.38	0.57	0.77
1000	12.21	37.07	0.61	2.38	0.61	0.77
1050	11.78	36.84	0.62	2.38	0.61	0.78
1100	11.37	36.96	0.63	2.39	0.69	0.78
1150	11.00	36.77	0.63	2.41	0.70	0.78
1200	10.62	36.58	0.64	2.42	0.72	0.78
1250	10.28	36.66	0.64	2.42	0.76	0.78
1300	9.95	36.73	0.65	2.42	0.80	0.78
1350	9.61	36.53	0.66	2.44	0.84	0.78
1400	9.31	36.78	0.65	2.44	0.88	0.79
1450	9.01	36.37	0.66	2.45	0.88	0.79
1500	8.73	36.55	0.67	2.46	0.95	0.79
1550	8.46	36.17	0.67	2.46	0.93	0.79
1600	8.20	36.29	0.67	2.46	0.95	0.79
1650	7.95	36.63	0.68	2.47	1.04	0.79
1700	7.71	36.23	0.68	2.47	1.03	0.79
1750	7.46	36.06	0.67	2.47	1.05	0.79
1800	7.24	36.24	0.68	2.47	1.07	0.79
1850	7.02	36.19	0.68	2.48	1.11	0.79
1900	6.80	35.80	0.68	2.48	1.09	0.79
1950	6.60	35.94	0.68	2.49	1.14	0.79
2000	6.40	35.77	0.68	2.48	1.13	0.79
2050	6.21	35.77	0.68	2.48	1.15	0.79
2100	6.02	35.66	0.68	2.50	1.16	0.80
2150	5.84	35.65	0.68	2.48	1.20	0.79
2200	5.67	35.40	0.67	2.49	1.16	0.80
2250	5.49	35.32	0.67	2.50	1.20	0.80
2300	5.32	35.46	0.66	2.50	1.21	0.80
2350	5.15	35.16	0.67	2.50	1.21	0.80
2400	5.00	35.23	0.66	2.49	1.24	0.80
2450	4.84	35.31	0.66	2.51	1.27	0.80
2500	4.70	35.05	0.66	2.49	1.26	0.80
2550	4.54	35.10	0.65	2.49	1.28	0.80
2600	4.41	35.01	0.65	2.49	1.28	0.80
2650	4.25	34.84	0.65	2.49	1.28	0.80
2700	4.11	34.86	0.66	2.50	1.33	0.80
2750	3.99	34.93	0.65	2.50	1.34	0.80
2800	3.84	34.73	0.65	2.49	1.33	0.80
2850	3.71	34.52	0.65	2.49	1.34	0.79
2900	3.58	34.46	0.65	2.50	1.33	0.80
2950	3.45	34.48	0.64	2.49	1.34	0.80
3000	3.32	34.42	0.66	2.48	1.35	0.80
3050	3.19	34.48	0.64	2.50	1.38	0.80
3100	3.06	34.38	0.65	2.49	1.40	0.80
3150	2.96	34.12	0.64	2.50	1.36	0.80
3200	2.82	34.07	0.65	2.50	1.40	0.80
3250	2.69	34.13	0.66	2.51	1.44	0.80
3300	2.58	34.03	0.65	2.51	1.44	0.80
3350	2.45	33.98	0.67	2.50	1.49	0.80
3400	2.33	33.91	0.66	2.52	1.47	0.80
3450	2.22	33.80	0.66	2.51	1.48	0.80
3500	2.08	33.82	0.68	2.52	1.54	0.80
3550	1.96	33.66	0.69	2.53	1.54	0.80
3600	1.86	33.61	0.68	2.52	1.55	0.80
3650	1.72	33.82	0.71	2.53	1.65	0.80
3700	1.62	33.57	0.69	2.54	1.61	0.80
3750	1.49	33.44	0.71	2.55	1.63	0.80
3800	1.39	33.41	0.71	2.55	1.67	0.80
3850	1.27	33.57	0.72	2.55	1.71	0.81
3900	1.14	33.34	0.73	2.56	1.72	0.81
3950	1.03	33.40	0.74	2.57	1.77	0.81
4000	0.91	33.26	0.75	2.56	1.81	0.80

Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP pack.



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 227mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability	
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure
400	20.43	37.02	0.49	2.41	0.21	0.79
450	19.42	36.84	0.50	2.41	0.25	0.78
500	18.49	36.91	0.52	2.41	0.26	0.79
550	17.67	36.98	0.53	2.41	0.30	0.79
600	16.92	36.95	0.53	2.42	0.32	0.79
650	16.21	36.96	0.55	2.42	0.33	0.80
700	15.57	37.01	0.57	2.43	0.40	0.79
750	14.97	36.75	0.56	2.45	0.41	0.80
800	14.41	36.66	0.58	2.46	0.45	0.79
850	13.90	36.84	0.57	2.44	0.48	0.79
900	13.39	36.69	0.58	2.47	0.49	0.80
950	12.93	36.64	0.58	2.48	0.52	0.80
1000	12.48	36.46	0.60	2.47	0.56	0.80
1050	12.06	36.63	0.61	2.48	0.60	0.80
1100	11.65	36.70	0.62	2.49	0.62	0.80
1150	11.27	36.48	0.62	2.50	0.66	0.80
1200	10.90	36.47	0.63	2.51	0.68	0.81
1250	10.55	36.51	0.63	2.51	0.70	0.81
1300	10.22	36.42	0.64	2.52	0.75	0.81
1350	9.88	36.19	0.65	2.53	0.78	0.81
1400	9.58	36.59	0.64	2.54	0.83	0.81
1450	9.28	36.25	0.65	2.55	0.84	0.81
1500	9.00	36.29	0.66	2.55	0.86	0.81
1550	8.73	36.19	0.66	2.54	0.91	0.81
1600	8.47	36.18	0.66	2.55	0.92	0.81
1650	8.21	35.83	0.67	2.56	0.93	0.81
1700	7.97	36.13	0.67	2.56	0.96	0.82
1750	7.73	35.88	0.66	2.56	0.96	0.82
1800	7.50	35.96	0.67	2.56	1.00	0.82
1850	7.28	35.82	0.67	2.57	1.02	0.82
1900	7.06	35.95	0.66	2.57	1.04	0.82
1950	6.86	35.85	0.67	2.58	1.06	0.82
2000	6.66	35.61	0.67	2.57	1.06	0.82
2050	6.47	35.59	0.66	2.56	1.09	0.82
2100	6.28	35.60	0.66	2.59	1.11	0.82
2150	6.09	35.55	0.66	2.56	1.12	0.82
2200	5.93	35.45	0.66	2.58	1.14	0.82
2250	5.75	35.26	0.66	2.59	1.15	0.82
2300	5.58	35.37	0.65	2.59	1.17	0.82
2350	5.41	35.23	0.66	2.58	1.17	0.82
2400	5.26	34.84	0.65	2.58	1.15	0.82
2450	5.10	35.10	0.65	2.59	1.19	0.82
2500	4.95	34.88	0.64	2.58	1.19	0.82
2550	4.80	35.01	0.64	2.57	1.22	0.82
2600	4.66	34.82	0.63	2.58	1.20	0.82
2650	4.52	34.74	0.63	2.57	1.21	0.82
2700	4.37	34.65	0.64	2.58	1.23	0.82
2750	4.24	34.60	0.63	2.58	1.25	0.82
2800	4.10	34.70	0.63	2.57	1.27	0.82
2850	3.97	34.46	0.64	2.57	1.26	0.82
2900	3.84	34.55	0.63	2.57	1.28	0.82
2950	3.71	34.35	0.62	2.57	1.26	0.82
3000	3.58	34.24	0.63	2.56	1.28	0.82
3050	3.45	34.24	0.62	2.58	1.28	0.82
3100	3.32	34.16	0.63	2.58	1.30	0.82
3150	3.21	34.12	0.61	2.58	1.30	0.82
3200	3.07	34.05	0.62	2.58	1.33	0.82
3250	2.95	34.00	0.64	2.59	1.36	0.82
3300	2.84	33.93	0.63	2.59	1.35	0.82
3350	2.70	33.90	0.64	2.58	1.39	0.82
3400	2.59	33.82	0.64	2.59	1.39	0.82
3450	2.48	33.74	0.63	2.58	1.39	0.82
3500	2.34	33.77	0.65	2.59	1.43	0.82
3550	2.23	33.65	0.66	2.61	1.46	0.82
3600	2.11	33.46	0.66	2.59	1.45	0.82
3650	1.98	33.58	0.67	2.61	1.52	0.82
3700	1.88	33.53	0.67	2.62	1.52	0.83
3750	1.75	33.41	0.68	2.61	1.54	0.82
3800	1.64	33.56	0.69	2.62	1.60	0.82
3850	1.53	33.30	0.68	2.63	1.58	0.83
3900	1.40	33.36	0.69	2.64	1.61	0.83
3950	1.29	33.14	0.70	2.63	1.63	0.83
4000	1.17	33.19	0.72	2.64	1.67	0.83

Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCL P pack



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 309mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability	
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure
400	19.97	37.02	0.49	2.41	0.23	0.75
450	18.95	36.84	0.50	2.41	0.26	0.75
500	18.02	37.51	0.54	2.26	0.31	0.75
550	17.19	37.20	0.55	2.27	0.35	0.74
600	16.44	37.56	0.55	2.27	0.37	0.75
650	15.74	37.14	0.57	2.27	0.39	0.75
700	15.09	37.20	0.58	2.29	0.45	0.75
750	14.49	37.33	0.58	2.31	0.48	0.76
800	13.93	37.26	0.60	2.32	0.49	0.76
850	13.42	37.28	0.60	2.30	0.53	0.76
900	12.92	37.18	0.60	2.33	0.57	0.76
950	12.45	37.03	0.61	2.34	0.58	0.77
1000	12.01	36.97	0.62	2.33	0.63	0.76
1050	11.59	37.15	0.63	2.34	0.67	0.76
1100	11.18	36.93	0.64	2.35	0.69	0.76
1150	10.81	36.82	0.64	2.37	0.72	0.77
1200	10.43	36.93	0.65	2.38	0.77	0.77
1250	10.09	36.87	0.65	2.38	0.80	0.77
1300	9.76	36.82	0.66	2.38	0.84	0.77
1350	9.42	36.90	0.67	2.40	0.88	0.78
1400	9.13	36.65	0.66	2.40	0.90	0.77
1450	8.83	36.55	0.67	2.41	0.92	0.78
1500	8.54	36.45	0.68	2.42	0.96	0.78
1550	8.27	36.40	0.68	2.42	0.98	0.78
1600	8.02	36.60	0.68	2.42	1.01	0.78
1650	7.76	36.56	0.69	2.43	1.06	0.78
1700	7.52	36.38	0.69	2.43	1.08	0.78
1750	7.28	36.43	0.69	2.44	1.11	0.78
1800	7.06	36.21	0.69	2.44	1.12	0.78
1850	6.84	36.14	0.69	2.45	1.14	0.78
1900	6.62	36.23	0.69	2.44	1.16	0.78
1950	6.42	35.76	0.70	2.46	1.14	0.79
2000	6.22	35.70	0.69	2.44	1.17	0.78
2050	6.03	35.97	0.69	2.46	1.23	0.79
2100	5.84	35.83	0.69	2.47	1.24	0.79
2150	5.65	35.72	0.69	2.45	1.24	0.79
2200	5.49	35.49	0.69	2.46	1.24	0.79
2250	5.31	35.75	0.69	2.47	1.31	0.79
2300	5.14	35.53	0.68	2.47	1.27	0.79
2350	4.97	35.39	0.69	2.47	1.31	0.79
2400	4.82	35.36	0.69	2.47	1.30	0.79
2450	4.66	35.17	0.68	2.48	1.33	0.79
2500	4.52	35.14	0.68	2.48	1.32	0.79
2550	4.36	35.00	0.68	2.47	1.34	0.79
2600	4.23	34.91	0.67	2.47	1.31	0.79
2650	4.07	34.99	0.67	2.47	1.36	0.79
2700	3.92	34.85	0.68	2.48	1.38	0.79
2750	3.80	35.01	0.67	2.48	1.39	0.79
2800	3.65	34.74	0.68	2.47	1.41	0.79
2850	3.52	34.57	0.68	2.47	1.41	0.79
2900	3.39	34.75	0.68	2.48	1.45	0.79
2950	3.26	34.35	0.67	2.47	1.40	0.79
3000	3.13	34.41	0.69	2.47	1.44	0.79
3050	3.00	34.23	0.67	2.49	1.43	0.79
3100	2.87	34.30	0.68	2.49	1.48	0.79
3150	2.76	34.37	0.67	2.48	1.47	0.79
3200	2.62	34.11	0.68	2.49	1.48	0.79
3250	2.49	34.06	0.69	2.50	1.51	0.79
3300	2.38	34.08	0.69	2.50	1.53	0.80
3350	2.25	34.12	0.71	2.49	1.58	0.79
3400	2.13	33.86	0.70	2.50	1.57	0.80
3450	2.02	33.83	0.70	2.50	1.58	0.79
3500	1.88	33.87	0.72	2.50	1.64	0.79
3550	1.76	33.62	0.73	2.52	1.65	0.80
3600	1.65	33.56	0.73	2.51	1.65	0.79
3650	1.51	33.86	0.75	2.53	1.76	0.80
3700	1.41	33.61	0.74	2.54	1.73	0.80
3750	1.28	33.55	0.76	2.53	1.78	0.80
3800	1.17	33.48	0.76	2.55	1.80	0.80
3850	1.06	33.23	0.76	2.55	1.79	0.80
3900	0.93	33.44	0.77	2.56	1.86	0.80
3950	0.81	33.39	0.78	2.57	1.90	0.80
4000	0.69	33.45	0.80	2.57	1.97	0.80

Note: Test data of Die nacked in industry standard 8-lead 2x2mm MCL P pack



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 281mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
400	-44.12	84.21	0.08	0.09	481.91	0.04	-	-	-
450	-40.62	72.55	0.09	0.10	110.82	0.05	-	-	-
500	-37.67	70.71	0.10	0.11	69.97	0.05	-6.66	-22.23	32.89
550	-35.20	69.75	0.11	0.11	55.55	0.05	-6.82	-19.75	30.95
600	-32.58	73.58	0.10	0.11	63.04	0.05	3.28	-17.95	30.96
650	-30.16	74.62	0.08	0.11	43.32	0.05	2.33	-14.46	21.88
700	-28.16	70.71	0.12	0.16	42.43	0.07	5.73	-12.60	21.49
750	-25.80	73.08	0.13	0.17	47.36	0.07	9.86	-10.81	20.33
800	-23.62	72.22	0.13	0.19	38.61	0.08	15.74	-8.09	15.64
850	-21.52	70.39	0.14	0.21	29.31	0.09	15.84	-5.89	12.94
900	-19.44	72.17	0.15	0.24	34.66	0.10	19.37	-4.29	12.65
950	-17.39	70.16	0.16	0.27	24.87	0.12	19.53	-3.92	11.87
1000	-15.34	60.39	0.17	0.30	7.90	0.13	23.07	-2.94	8.36
1050	-13.32	61.69	0.18	0.36	9.28	0.16	27.97	0.58	7.79
1100	-11.29	59.78	0.21	0.44	7.91	0.19	27.46	3.72	7.78
1150	-9.23	56.36	0.24	0.53	5.54	0.22	30.72	4.27	6.20
1200	-7.17	54.32	0.27	0.66	4.54	0.27	32.56	4.46	5.89
1250	-5.08	52.22	0.33	0.82	4.06	0.33	34.74	6.94	5.75
1300	-2.94	50.15	0.38	1.04	3.64	0.41	35.48	9.00	5.37
1350	-0.78	47.35	0.47	1.34	2.85	0.51	34.76	11.80	5.48
1400	1.39	44.43	0.59	1.75	2.38	0.63	35.52	14.49	5.02
1450	3.56	41.57	0.76	2.30	2.03	0.77	34.62	15.34	4.18
1500	5.73	39.20	0.99	3.04	1.83	0.93	34.40	16.43	3.63
1550	7.80	37.09	1.32	4.02	1.78	1.09	35.97	18.56	3.13
1600	9.79	34.49	1.75	5.17	1.56	1.21	37.88	22.87	2.78
1650	11.66	32.24	2.34	6.37	1.45	1.27	37.55	24.95	2.37
1700	13.39	30.25	3.18	7.52	1.38	1.25	37.42	26.06	2.06
1750	14.98	28.35	4.43	8.63	1.31	1.16	38.41	27.11	1.96
1800	16.30	26.76	6.33	10.38	1.28	1.05	37.16	28.00	1.63
1850	17.16	25.51	8.29	14.51	1.23	0.99	40.89	28.57	1.56
1900	17.26	25.10	7.47	34.61	1.21	1.02	39.45	29.36	1.29
1950	16.50	25.61	4.90	15.44	1.20	1.10	39.89	29.07	1.27
2000	15.19	26.59	3.07	9.68	1.19	1.14	40.86	27.63	1.24
2050	13.66	27.80	2.02	7.02	1.19	1.14	37.72	27.10	1.31
2100	12.15	29.07	1.43	5.51	1.19	1.10	40.02	26.63	1.24
2150	10.73	30.18	1.08	4.54	1.20	1.04	40.44	26.11	1.62
2200	9.44	31.22	0.86	3.90	1.21	0.99	38.15	25.45	1.36
2250	8.28	32.06	0.71	3.43	1.21	0.94	36.71	24.49	1.38
2300	7.21	33.02	0.62	3.08	1.25	0.89	36.71	24.16	1.56
2350	6.26	33.43	0.54	2.80	1.22	0.84	36.69	22.31	1.64
2400	5.40	34.28	0.49	2.59	1.26	0.81	34.74	20.82	2.44
2450	4.60	34.66	0.45	2.43	1.26	0.78	33.46	19.87	2.61
2500	3.89	35.17	0.42	2.27	1.29	0.74	37.15	18.72	2.34
2550	3.25	35.33	0.39	2.15	1.26	0.72	35.09	17.75	2.28
2600	2.64	35.94	0.37	2.07	1.30	0.70	33.57	16.71	2.64
2650	2.08	36.56	0.34	1.98	1.32	0.68	33.45	16.07	3.19
2700	1.58	36.45	0.34	1.91	1.33	0.66	35.94	15.70	2.99
2750	1.12	36.88	0.33	1.84	1.39	0.65	32.23	15.28	3.02
2800	0.67	36.65	0.32	1.80	1.35	0.63	36.72	15.39	3.48
2850	0.27	37.15	0.32	1.74	1.39	0.62	33.20	15.69	3.66
2900	-0.09	37.11	0.31	1.70	1.39	0.61	34.43	15.35	3.57
2950	-0.44	37.20	0.30	1.67	1.40	0.60	34.10	13.86	3.79
3000	-0.77	37.49	0.30	1.66	1.44	0.60	34.46	13.81	4.27
3050	-1.04	37.42	0.29	1.62	1.42	0.59	34.09	12.99	3.98
3100	-1.31	37.47	0.30	1.61	1.44	0.59	32.87	11.98	4.25
3150	-1.57	37.79	0.30	1.58	1.51	0.58	36.11	12.28	4.05
3200	-1.82	37.32	0.30	1.58	1.49	0.58	34.35	11.14	4.75
3250	-2.02	37.95	0.30	1.55	1.54	0.57	33.64	17.38	4.12
3300	-2.22	37.50	0.31	1.54	1.54	0.56	33.75	17.65	5.43
3350	-2.40	37.45	0.31	1.56	1.57	0.57	33.46	17.11	4.74
3400	-2.59	37.50	0.32	1.55	1.64	0.57	33.52	17.28	5.27
3450	-2.71	37.61	0.31	1.54	1.61	0.57	33.97	17.05	5.12
3500	-2.87	37.40	0.32	1.53	1.63	0.56	32.31	17.13	5.07
3550	-3.00	37.34	0.33	1.55	1.68	0.57	33.55	16.61	4.69
3600	-3.13	37.17	0.33	1.55	1.67	0.57	33.74	16.97	5.88
3650	-3.22	37.30	0.34	1.55	1.70	0.57	33.85	16.48	5.83
3700	-3.32	37.09	0.35	1.55	1.72	0.57	32.27	15.85	5.44
3750	-3.39	37.12	0.35	1.56	1.75	0.57	33.99	16.64	5.09
3800	-3.46	37.16	0.35	1.57	1.76	0.58	34.07	15.77	6.13
3850	-3.53	36.29	0.38	1.58	1.76	0.57	31.88	15.60	5.12
3900	-3.58	36.70	0.37	1.59	1.81	0.58	33.94	16.53	5.33
3950	-3.61	36.44	0.38	1.59	1.79	0.58	31.98	15.84	5.89
4000	-3.64	36.39	0.39	1.62	1.83	0.59	33.61	16.32	5.25

Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 182mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
400	-43.29	84.21	0.08	0.09	75.94	0.04	-	-	-
450	-40.80	72.55	0.09	0.10	68.09	0.05	-	-	-
500	-37.54	73.45	0.09	0.11	91.30	0.05	-8.56	-22.57	30.85
550	-34.82	83.03	0.11	0.12	257.32	0.05	-3.81	-19.09	28.87
600	-32.33	65.81	0.10	0.12	26.12	0.05	-2.49	-19.09	28.89
650	-29.98	79.24	0.10	0.13	99.59	0.06	2.45	-14.10	20.53
700	-27.71	66.59	0.12	0.16	25.30	0.07	4.92	-11.95	20.23
750	-25.43	68.40	0.13	0.16	26.52	0.07	7.80	-11.10	17.95
800	-23.27	62.34	0.12	0.16	9.84	0.07	13.00	-8.46	17.50
850	-21.17	68.25	0.14	0.21	21.16	0.09	13.90	-5.80	14.09
900	-19.11	72.43	0.14	0.22	30.44	0.10	24.54	-4.79	13.51
950	-17.06	68.83	0.15	0.25	18.36	0.11	20.82	-4.25	12.80
1000	-15.09	66.93	0.18	0.31	16.44	0.13	24.37	-4.42	11.30
1050	-13.05	62.78	0.18	0.35	9.62	0.15	24.71	0.81	8.19
1100	-11.01	58.53	0.20	0.42	5.93	0.18	27.15	3.40	8.00
1150	-8.99	55.45	0.24	0.50	4.58	0.21	28.82	4.55	7.21
1200	-6.92	53.85	0.26	0.63	3.80	0.26	31.09	5.11	5.57
1250	-4.85	50.82	0.30	0.79	2.89	0.32	34.16	6.82	5.37
1300	-2.73	48.35	0.35	0.99	2.25	0.39	34.46	8.90	4.64
1350	-0.61	46.43	0.45	1.28	2.21	0.49	33.29	11.84	4.26
1400	1.52	44.35	0.56	1.69	2.06	0.62	32.91	13.39	3.45
1450	3.64	41.79	0.73	2.22	1.87	0.76	31.34	15.37	3.19
1500	5.75	39.38	0.93	2.92	1.66	0.91	31.69	16.65	2.87
1550	7.80	37.03	1.21	3.80	1.50	1.06	30.81	17.85	2.40
1600	9.76	34.44	1.61	4.80	1.35	1.18	33.24	20.91	2.00
1650	11.63	32.13	2.12	5.82	1.23	1.24	32.28	21.74	1.77
1700	13.37	30.23	2.85	6.75	1.20	1.23	33.53	23.42	1.48
1750	14.99	28.23	3.93	7.65	1.15	1.15	34.60	25.00	1.36
1800	16.43	26.48	5.51	9.04	1.11	1.05	34.47	28.28	1.31
1850	17.47	25.15	7.31	12.25	1.09	0.98	36.31	29.70	1.14
1900	17.73	24.61	6.99	22.58	1.08	1.01	36.08	30.22	0.85
1950	17.08	24.88	4.73	17.87	1.06	1.10	40.59	29.53	0.78
2000	15.78	25.92	2.93	10.53	1.06	1.16	40.85	25.83	0.80
2050	14.23	27.25	1.90	7.48	1.07	1.16	40.06	27.25	0.82
2100	12.66	28.47	1.33	5.79	1.07	1.13	38.96	26.39	0.77
2150	11.22	29.66	1.01	4.75	1.09	1.07	37.20	25.50	1.00
2200	9.90	30.77	0.81	4.06	1.11	1.01	36.50	24.70	0.94
2250	8.69	31.57	0.67	3.57	1.11	0.96	38.51	23.42	0.98
2300	7.62	32.50	0.59	3.21	1.14	0.91	36.08	21.84	1.04
2350	6.67	33.04	0.52	2.93	1.15	0.87	36.20	22.09	1.26
2400	5.77	33.70	0.48	2.71	1.17	0.83	33.64	21.59	1.50
2450	5.00	34.26	0.43	2.52	1.16	0.80	33.93	19.60	1.91
2500	4.27	35.02	0.40	2.37	1.23	0.77	36.67	18.61	1.75
2550	3.60	35.24	0.40	2.23	1.25	0.74	34.92	17.50	1.69
2600	3.01	35.80	0.37	2.13	1.27	0.72	33.69	16.50	2.10
2650	2.44	35.96	0.35	2.05	1.27	0.70	35.49	16.27	2.37
2700	1.94	36.18	0.35	1.98	1.31	0.68	32.23	15.76	2.42
2750	1.48	36.55	0.34	1.91	1.33	0.66	34.08	16.65	2.71
2800	1.03	36.86	0.33	1.86	1.33	0.65	33.31	16.47	2.56
2850	0.63	36.84	0.32	1.81	1.34	0.64	33.98	16.39	3.15
2900	0.27	36.95	0.32	1.76	1.34	0.63	34.15	15.53	3.04
2950	-0.08	37.37	0.31	1.73	1.40	0.62	34.58	13.76	3.22
3000	-0.39	37.08	0.32	1.69	1.38	0.61	35.15	13.96	3.59
3050	-0.68	37.41	0.31	1.66	1.42	0.60	33.36	13.82	2.88
3100	-0.95	37.56	0.30	1.64	1.43	0.60	35.15	13.54	3.08
3150	-1.20	37.70	0.30	1.63	1.44	0.59	34.75	12.47	2.85
3200	-1.44	37.67	0.30	1.62	1.49	0.59	32.28	11.53	2.80
3250	-1.65	37.27	0.30	1.60	1.46	0.58	32.73	18.09	3.60
3300	-1.85	37.90	0.31	1.59	1.53	0.58	32.85	17.95	2.97
3350	-2.03	37.38	0.31	1.57	1.47	0.58	34.33	17.44	4.13
3400	-2.19	37.24	0.31	1.57	1.50	0.58	32.96	17.28	4.02
3450	-2.35	37.38	0.32	1.56	1.54	0.57	33.11	16.04	4.12
3500	-2.48	37.28	0.32	1.56	1.51	0.57	33.86	16.45	3.37
3550	-2.62	37.31	0.32	1.57	1.58	0.58	33.70	16.61	3.73
3600	-2.73	37.18	0.33	1.58	1.56	0.58	34.29	16.06	3.86
3650	-2.86	36.79	0.34	1.57	1.58	0.58	33.39	16.33	4.56
3700	-2.94	37.36	0.34	1.57	1.66	0.57	33.44	16.25	3.71
3750	-3.03	36.84	0.37	1.58	1.69	0.57	32.92	16.01	4.24
3800	-3.10	36.67	0.35	1.59	1.65	0.58	34.16	15.69	4.76
3850	-3.16	36.79	0.37	1.59	1.69	0.58	32.19	15.57	4.85
3900	-3.22	36.50	0.37	1.61	1.64	0.59	32.55	16.15	4.21
3950	-3.28	36.43	0.37	1.61	1.69	0.58	34.61	16.51	4.94
4000	-3.33	36.08	0.39	1.64	1.71	0.59	32.21	16.03	3.87

Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

I/F/R/MICROWAVE COMPONENTS

 REV. OR
 TAV2-501-D+
 12/15/2020
 Page 5 of 6

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)









Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 364mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
400	-43.41	84.21	0.08	0.09	172.22	0.06	-	-	-
450	-40.86	72.55	0.09	0.10	170.18	0.07	-	-	-
500	-37.66	75.86	0.12	0.16	240.94	0.07	-10.29	-22.91	32.56
550	-35.17	78.84	0.14	0.18	312.75	0.08	-2.66	-19.51	29.87
600	-32.65	69.97	0.14	0.18	87.75	0.08	4.71	-19.51	30.40
650	-30.35	77.65	0.14	0.19	170.88	0.08	-1.21	-14.52	22.22
700	-28.08	69.00	0.16	0.22	61.50	0.10	9.11	-12.36	21.72
750	-25.82	64.94	0.17	0.23	33.69	0.10	8.60	-11.51	18.58
800	-23.70	67.16	0.16	0.23	33.79	0.10	10.38	-8.85	18.45
850	-21.56	68.03	0.18	0.28	37.59	0.12	14.16	-6.17	14.97
900	-19.51	66.06	0.19	0.30	26.44	0.13	19.60	-5.16	14.66
950	-17.44	76.95	0.20	0.32	84.24	0.14	22.42	-4.61	13.57
1000	-15.43	65.40	0.22	0.39	22.88	0.17	25.07	-4.77	13.27
1050	-13.38	64.45	0.23	0.44	19.57	0.19	30.13	0.48	11.71
1100	-11.36	61.93	0.25	0.52	13.99	0.22	29.47	3.11	8.46
1150	-9.30	56.76	0.29	0.60	8.00	0.25	29.68	4.27	8.36
1200	-7.22	53.77	0.32	0.73	5.69	0.30	31.81	4.84	8.14
1250	-5.12	51.66	0.36	0.90	4.74	0.36	37.31	6.58	7.83
1300	-2.98	49.69	0.42	1.11	3.95	0.43	38.70	8.71	6.99
1350	-0.83	47.08	0.52	1.42	3.36	0.53	35.58	11.72	6.36
1400	1.33	44.50	0.65	1.84	2.85	0.65	37.23	13.34	5.47
1450	3.50	41.70	0.83	2.41	2.43	0.79	36.02	15.45	4.97
1500	5.65	39.50	1.06	3.16	2.19	0.94	36.29	16.79	4.40
1550	7.73	36.99	1.38	4.13	1.91	1.10	36.74	18.14	3.81
1600	9.72	34.65	1.84	5.28	1.75	1.21	37.00	21.54	3.34
1650	11.59	32.40	2.47	6.48	1.59	1.26	37.84	24.59	2.86
1700	13.31	30.56	3.39	7.62	1.54	1.23	37.41	26.22	2.51
1750	14.85	28.61	4.79	8.78	1.45	1.14	39.30	26.91	2.48
1800	16.12	26.96	6.89	10.65	1.38	1.03	43.08	27.85	2.08
1850	16.90	25.82	8.95	15.13	1.33	0.98	39.87	29.15	1.70
1900	16.90	25.56	7.72	34.68	1.31	1.03	39.82	29.43	1.63
1950	16.08	26.15	4.96	14.97	1.31	1.12	40.87	28.75	1.59
2000	14.75	27.03	3.13	9.64	1.29	1.16	37.92	27.16	1.61
2050	13.25	28.22	2.10	7.05	1.29	1.15	39.77	26.99	1.67
2100	11.75	29.51	1.50	5.56	1.30	1.11	40.26	26.35	1.70
2150	10.36	30.40	1.15	4.62	1.29	1.05	37.43	25.82	2.00
2200	9.09	31.54	0.94	3.98	1.33	1.00	39.64	24.54	2.00
2250	7.91	32.47	0.79	3.52	1.36	0.95	36.80	23.07	2.14
2300	6.88	33.04	0.69	3.17	1.37	0.90	37.26	21.50	2.25
2350	5.94	33.71	0.61	2.91	1.38	0.86	36.44	21.81	2.52
2400	5.07	34.43	0.57	2.69	1.43	0.83	35.33	21.30	2.90
2450	4.31	34.90	0.52	2.52	1.44	0.79	34.10	19.22	3.19
2500	3.60	35.52	0.49	2.37	1.48	0.77	37.56	18.15	2.84
2550	2.93	36.19	0.47	2.26	1.55	0.74	35.99	17.02	3.77
2600	2.36	36.30	0.45	2.16	1.54	0.72	34.33	15.98	3.75
2650	1.80	36.70	0.43	2.07	1.58	0.70	35.64	15.77	4.23
2700	1.30	36.69	0.42	1.99	1.57	0.68	32.51	15.25	4.27
2750	0.84	36.84	0.41	1.94	1.61	0.67	35.27	16.18	4.51
2800	0.40	37.21	0.40	1.88	1.65	0.65	33.92	16.00	4.52
2850	0.01	37.31	0.39	1.84	1.65	0.65	36.57	15.92	4.91
2900	-0.35	37.30	0.39	1.80	1.70	0.63	34.49	15.03	4.94
2950	-0.69	37.37	0.38	1.77	1.71	0.63	35.31	13.22	5.08
3000	-1.00	37.60	0.38	1.74	1.75	0.62	35.53	13.42	5.54
3050	-1.29	37.57	0.38	1.71	1.75	0.61	34.16	13.27	5.11
3100	-1.55	37.59	0.36	1.69	1.76	0.61	36.54	12.99	5.44
3150	-1.81	37.94	0.37	1.69	1.83	0.61	35.26	11.91	5.24
3200	-2.03	37.66	0.38	1.67	1.84	0.60	32.58	10.95	5.15
3250	-2.24	37.80	0.37	1.66	1.86	0.60	35.11	17.75	5.74
3300	-2.44	37.56	0.37	1.64	1.86	0.59	33.84	17.60	5.53
3350	-2.61	37.77	0.38	1.64	1.91	0.59	36.66	17.07	6.27
3400	-2.78	37.53	0.38	1.64	1.93	0.59	33.59	16.90	6.41
3450	-2.93	37.65	0.40	1.63	1.98	0.59	33.08	15.62	6.39
3500	-3.07	37.27	0.39	1.63	1.96	0.59	35.25	16.04	5.77
3550	-3.19	37.60	0.40	1.65	2.04	0.59	33.92	16.21	6.09
3600	-3.30	37.40	0.40	1.66	2.05	0.60	34.70	15.65	6.11
3650	-3.42	37.25	0.42	1.66	2.07	0.60	33.70	15.93	6.76
3700	-3.49	37.02	0.42	1.66	2.08	0.59	35.55	15.86	6.40
3750	-3.58	36.58	0.44	1.68	2.08	0.60	32.27	15.61	6.61
3800	-3.64	36.87	0.43	1.68	2.11	0.60	35.39	15.28	7.31
3850	-3.69	36.65	0.45	1.69	2.13	0.60	33.86	15.17	7.18
3900	-3.74	36.45	0.45	1.70	2.13	0.61	32.55	15.77	6.63
3950	-3.78	36.54	0.46	1.72	2.19	0.61	36.71	16.14	7.31
4000	-3.83	36.09	0.48	1.75	2.21	0.62	33.61	15.66	6.75









Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package

Typical Performance Curves










Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package

Typical Performance Curves



Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package

Typical Performance Curves



Note: Test data of Die packaged in industry standard 8-lead 2x2mm MCLP package



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment	20° to 35° C and 40 to 60% humidity (In Factory Shipped Package)	Individual Model Data Sheet